

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190700042

Status:

Active

Description:

InsulKrimp™ Ring Tongue Terminal for 18-22 AWG Wire


Documents:

Drawing (PDF)

Product Specification PS-19902-009 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19070
Mil-Spec	N/A
Product Name	InsulKrimp™
Type	Ring
Physical	
Barrel Type	Closed
Flammability	94V-2
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Adhesive Tape on Reel
Stud Size	5-6 (M3-3.5)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.70mm (.145") max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.35 - 0.80
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	AA-232-06XT
Reference - Drawing Numbers	
Product Specification	PS-19902-009
Sales Drawing	SD-19070-003



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19070Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880023
Mini-Mac™ Applicator	0638851300

This document was generated on 02/02/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION