



REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130054 WAS 128070	EL	11/14/11
E	128533C WAS 128643C. ADDED 128488	JJC	08/03/12

NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-1 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128643C ASSEMBLY CONSISTS OF 128533C COLLET AND 128488 DRAWBAR.

(E)	128488	1	DRAWBAR	9
	126748-1	1	UNITIZED DEFLECTOR	8
(E)	128533C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122912	1	BARBED RETAINER	4
	130054	1	UNITIZED CHUCK JAW	3
	127582	1	TOP GUARD	2
	127294C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH	HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401		
ITAR/ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -07 GP LONG		
SCH B#: 8467.99.0190	FINAL ASSY: -		
HTS: 8467.99.0190	ENG: MVM CK: B	DATE: 11/01/04	SCALE: 2:1
	99-3777-1C		