




PART NUMBERS									MARKERS PER CARD	CARDS PER PKG	LEGEND
(STYLE 1) BLACK ON YELLOW			(STYLE 2) YELLOW ON BLACK			(STYLE 2) YELLOW ON BLACK					
"A" DIM. (CENTERED)	"B" DIM. 	"C" DIM.	"A" DIM. (CENTERED)	"B" DIM. 	"C" DIM.	"A" DIM. (CENTERED)	"B" DIM. 	"C" DIM.			
1.00 (25.4)	1.13 (28.7)	1.63 (41.4)	1.50 (38.1)	1.38 (35.1)	1.88 (47.8)	2.50 (63.5)	1.75 (44.5)	2.88 (73.2)			
PRL100BY-0 THRU PRL100BY-9			PRL150YB-0 THRU PRL150YB-9			PRL250YB-0 THRU PRL250YB-9			1	25	0 THRU 9
PRL100BY-A THRU PRL100BY-Z			PRL150YB-A THRU PRL150YB-Z			PRL250YB-A THRU PRL250YB-Z			1	25	A THRU Z
PRL100BY-DSH (SEE NOTE 2)			PRL150YB-DSH (SEE NOTE 3)			PRL250YB-DSH (SEE NOTE 4)			1	25	- (DASH)
PRL100BY-BLNK			N/A			N/A			1	25	(BLANK)
PRL100BY-18KIT			N/A			N/A			1	900	0 THRU 9, A THRU D, L, P, R, S
PRL100BY-36KIT (SEE NOTE 2)			N/A			N/A			1	950	0 THRU 9, A THRU Z, - (DASH), BLANK

NOTES:

1. MILLIMETERS ARE IN ().
2. "A" DIM. FOR DASH IS .375.
3. "A" DIM. FOR DASH IS .343.
4. "A" DIM. FOR DASH IS .50.

CAD FILENAME/LAYERS										100923NC_DC_C10672/01D	
PANDUIT										CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING										PRL***-* REFLECTIVE MARKERS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XX) ± .062										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU										SCALE NTS	
DATE 3/25/08										DRAWING NO. C10672	
CHK'D										DWG A SIZE	

3	6/15/09	RVU		1.13 was 1.130, 1.38 was 1.380, & 1.75 was 1.750. Remove 5°.	5768	R				
2	6/04/09			VOID						
1	11/21/08	RVU		ADD NOTES 2, 3, 4. ADD "SEE NOTE 2, 3, 4, 5" ON TABLE.	5613	R				
0	3/25/08	RVU		DRAWING RELEASE	5368	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PRL100BY-A](#) [PRL100BY-C](#) [PRL100BY-V](#) [PRL100BY-4](#) [PRL100BY-J](#) [PRL100BY-P](#) [PRL100BY-7](#) [PRL100BY-M](#)
[PRL100BY-S](#) [PRL100BY-BLNK](#) [PRL100BY-DSH](#) [PRL100BY-G](#) [PRL100BY-F](#) [PRL100BY-0](#) [PRL100BY-T](#)
[PRL100BY-R](#) [PRL100BY-U](#) [PRL100BY-2](#) [PRL100BY-X](#) [PRL100BY-B](#) [PRL100BY-W](#) [PRL100BY-D](#) [PRL100BY-Z](#)
[PRL100BY-18KIT](#) [PRL100BY-36KIT](#) [PRL100BY-E](#) [PRL100BY-H](#) [PRL100BY-1](#) [PRL100BY-K](#) [PRL100BY-I](#)
[PRL100BY-6](#) [PRL100BY-L](#) [PRL100BY-8](#) [PRL100BY-N](#) [PRL100BY-5](#) [PRL100BY-Q](#) [PRL100BY-9](#) [PRL100BY-O](#)
[PRL100BY-Y](#) [PRL100BY-3](#) [PRL150YB-7](#) [PRL250YB-T](#) [PRL250YB-D](#) [PRL150YB-N](#) [PRL250YB-W](#) [PRL150YB-Q](#)
[PRL250YB-Q](#) [PRL250YB-I](#) [PRL150YB-T](#) [PRL250YB-E](#) [PRL250YB-Y](#) [PRL250YB-H](#) [PRL250YB-2](#) [PRL150YB-E](#)
[PRL150YB-V](#) [PRL250YB-C](#) [PRL250YB-F](#) [PRL150YB-W](#) [PRL250YB-V](#) [PRL150YB-1](#) [PRL150YB-H](#) [PRL250YB-7](#)
[PRL250YB-K](#) [PRL150YB-4](#) [PRL150YB-5](#) [PRL150YB-I](#) [PRL250YB-5](#) [PRL150YB-Y](#) [PRL150YB-F](#) [PRL150YB-D](#)
[PRL150YB-J](#) [PRL150YB-6](#) [PRL150YB-C](#) [PRL250YB-1](#) [PRL150YB-S](#) [PRL150YB-K](#) [PRL250YB-N](#) [PRL150YB-O](#)
[PRL250YB-G](#) [PRL150YB-3](#) [PRL250YB-U](#) [PRL250YB-P](#) [PRL250YB-S](#) [PRL250YB-4](#) [PRL250YB-L](#) [PRL150YB-8](#)
[PRL250YB-B](#) [PRL150YB-X](#) [PRL250YB-J](#) [PRL250YB-6](#) [PRL150YB-M](#) [PRL150YB-P](#) [PRL150YB-G](#) [PRL250YB-3](#)
[PRL250YB-M](#) [PRL150YB-R](#) [PRL250YB-8](#) [PRL150YB-B](#) [PRL150YB-U](#) [PRL250YB-R](#)