



Pass & Seymour

Turnlok® Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC

4710, 4700, 4792, 4560, 4550, 4760, 4750, L520, CRL520, L620, L720, L530, CRL530, L630, L730

Quality construction for maximum durability.

Choose from a broad range of capacities in both single and duplex receptacle designs. They feature high-quality, brass contacts for rock-solid electrical connections and long service life. Single-piece, solid brass or steel straps and impact-resistant nylon face and body help them shrug off hard use.



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Side and external screw-pressure-plate back wire capability.
Accepts #14 — #10 AWG.

Clearly marked NEMA configuration, rating and third party listing on each unit's face.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands. 15 Amp mounting strap is steel.



Field Uses/Vertical Markets

- | | | | |
|--------------|---------------|-----------------------|-----------------|
| ■ Industrial | ■ Health Care | ■ Education | ■ Institutional |
| ■ Retail | ■ Office | ■ Hospitality/Lodging | |

SF1701R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

Turnlok® Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC

Ordering Information

Catalog Number	Rating A. V.	Description/Color	NEMA Config. No.
Receptacles Back & Side Wire			
4710	15 125	Single Receptacle	L5-15R
4700	15 125	Duplex Receptacle	L5-15R
4792	15 125	Combination Straight Blade and Locking	5-15R and L5-15R
4560	15 250	Single Receptacle	L6-15R
4550†	15 250	Duplex Receptacle	L6-15R
4760	15 277*	Single Receptacle	L7-15R
4750	15 277*	Duplex Receptacle	L7-15R
L520-R	20 125	Single Receptacle	L5-20R
CRL520-R	20 125	Single Receptacle, Corrosion-Resistant	L5-20R
L620-R	20 250	Single Receptacle	L6-20R
L720-R	20 277*	Single Receptacle	L7-20R
L530-R	30 125	Single Receptacle	L5-30R
CRL530-R	30 125	Single Receptacle, Corrosion-Resistant	L5-30R
L630-R	30 250	Single Receptacle	L6-30R
L730-R	30 277*	Single Receptacle	L7-30R

*AC only.

†Not designed for split circuits.



NEMA
L5-15R



NEMA
L6-15R



NEMA
L7-15R



NEMA
L5-20R



NEMA
L6-20R



NEMA
L7-20R



NEMA
L5-30R



NEMA
L6-30R



NEMA
L7-30R



NEMA
5-15R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Turnlok® Locking Devices Heavy-Duty Receptacles 15, 20 & 30A; 125 & 250V, 277VAC



Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles.
Federal Specification WC596.
CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.
Conforms to NEMA WD-1.

Performance

Electrical

Dielectric Withstand Voltage	2000V minimum
Maximum Working Voltage	600VAC
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C max. after 50 cycles at 150% rated current

Mechanical

Terminal Accommodation	#14 AWG min. – #10 AWG max.
Product Identification	Amperage, Voltage, NEMA Configuration molded into face

Environmental


Flammability	UL94 V2
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact

Materials


	Standard	Corrosion-Resistant
Front Body	Nylon	Nylon
Back Body	Nylon	Nylon
Mounting Strap	15A = Steel, 20 & 30A = Brass	Nickel-Plated Brass
Pressure Plate	Brass	Nickel-Plated Brass
Contacts	Brass	Nickel-Plated Brass
Terminal Clamps	Brass	Nickel-Plated Brass
Terminal Screws	Brass	Brass
Mounting Screws	Zinc-Plated Steel	Stainless Steel

Warranty


1 Year




Dimensions for 4700




Dimensions for 4792




Dimensions for 4550




Dimensions for 4760




Dimensions for 4560




Dimensions for
20 Amp Receptacle



Dimensions for
30 Amp Receptacle



Dimensions for 4710



Dimensions for 4750

Complementary Devices & Accessories



TURNLOK® LOCKING DEVICES

- Extra-Hard Use Plugs & Connectors
- Heavy-Duty Flanged Inlets & Outlets



GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® II



TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- | | | | |
|--------------------------|------------------------------|-------------------------------|----------------------------|
| ■ Light Almond Devices | ■ PlugTail™ Devices | ■ GFCIs | ■ Flexcor® Wire Mesh Grips |
| ■ Decorator Devices | ■ Switches | ■ Weatherproof Boxes & Covers | ■ Configurable Solutions |
| ■ Hospital Grade Devices | ■ Straight Blade Receptacles | ■ IEC 309 Industrial Products | |



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca