






PRODUCT NO.	DIM.M
61125-005CA/005CALF	10.0
61125-025CA/025CALF	6.55
61125-045CA/045CALF	6.55
61125-055CA/055CALF	6.55
61125-025CAC/025CACLF	6.55
61125-045CAC/045CACLF	6.55
61125-055CAC/055CACLF	6.55



ABOVE P.C.B.
RIGHT PUSH ROD
(CAN'T BE USED FOR SINGLE DECK)



PRODUCT NO.	DIM.M
61125-020CA/020CALF	-0.3
61125-220CA/220CALF	2.15
61125-040CA/040CALF	-0.3
61125-050CA/050CALF	-0.3
61125-050CAN/050CANLF	-0.3
61125-020CAC/020CACLF	-0.3
61125-040CAC/040CACLF	-0.3
61125-050CAC/050CACLF	-0.3





ABOVE P.C.B.
RIGHT PUSH ROD
(CAN BE USED FOR SINGLE DECK)

mat'l. code				surface	tolerance	projection	product family		
ISO1302				ISO1101	ISO406	MM	PCMCIA		
l'tecn nodr				date			title		
J	N05-0063	WB	03/04/05	angle			EJECTOR HEADER ASS'Y		
K	N05-0140	WB	05/31/05	±0.30			3.3V, SMT TYPE 1/2/3		
L	EX-N-011397	ZK	04/02/12	0°±2'			scale 1.2		
				dr	WENDY CHEN	07/11/95	dwg no		
				engr	JOSEPH HSIA	07/11/95	sheet 1 of 6		
				chr	JOSEPH HSIA	07/11/95	size		
				appd	JENN TSAO	07/11/95	A4		
							type Product Customer Drawing		
sheet	revision	L	L	L	L	L			
index	sheet	1	2	3	4	5			

PRODUCT NO.	DIM.M
61125-105CA/105CALF	10.0
61125-125CA/125CALF	6.55
61125-145CA/145CALF	6.55
61125-155CA/155CALF	6.55







PRODUCT NO.	DIM.M
61125-120CA/120CALF	-0.3
61125-140CA/140CALF	-0.3
61125-150CA/150CALF	-0.3



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection MM	product family PCMCIA
ltr ecn nodr date	tolerances unless otherwise specified	angle 0°±2'	scale 1.2	EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3
L	dr WENDY CHEN 07/11/95	engr JOSEPH HSIA 07/11/95	dwg no	sheet 2 of 6
	chr JOSEPH HSIA 07/11/95	appd JENN TSAO 07/11/95	61125	A4
sheet index	revision sheet		type	Product Customer Drawing

PRODUCT NO.	DIM.M
61125-620CA/620CALF	-0.3
61125-640CA/640CALF	-0.3
61125-650CA/650CALF	-0.3





BELOW P.C.B.
LEFT PUSH ROD



(CAN BE USED FOR SINGLE DECK)

mat'l. code		surface		tolerance		projection		product family	
		ISO1302 ✓		ISO1101 ISO406				PCMCIA	
ltr ecn nodr		date		tolerances unless other		wise specified		title	
L				angle		MM		EJECTOR HEADER ASS'Y	
				±0.30				3.3V, SMT TYPE 1/2/3	
				0°±2'		scale 1.2			
		dr		WENDY CHEN		07/11/95		dwg no	
		engr		JOSEPH HSIA		07/11/95		sheet 3 of 6	
		chr		JOSEPH HSIA		07/11/95		61125	
		appd		JENN TSAO		07/11/95		A4	
sheet		revision						type	
index		sheet						Product Customer Drawing	

PRODUCT NO.	DIM.M
61125-505CA/505CALF	10.0
61125-525CA/525CALF	6.55
61125-545CA/545CALF	6.55
61125-555CA/555CALF	6.55



PRODUCT NO.	DIM.M	DIM.S
61125-520CA/520CALF	-0.3	13.0
61125-540CA/540CALF	-0.3	13.0
61125-550CA/550CALF	-0.3	15.6
61125-520DA/520DALF	-0.3	21.0
61125-520FA/520FALF	-0.3	21.0



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection ASME Y14.5	product family PCMCIA
ltr ecn nodr date	tolerances unless otherwise specified			EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3
L	angle 0°±2'	±0.30	MM	scale 1.2
dr	WENDY CHEN	07/11/95	FCI	dwg no
eng	JOSEPH HSIA	07/11/95		sheet 4 of 6
chr	JOSEPH HSIA	07/11/95		size A4
app	JENN TSAO	07/11/95	type Product Customer Drawing	
sheet index	revision sheet			

NOTES:

- 8mm MIN. CARD EJECT.
- EJECT TRAVEL: 9.5mm
- PUSH ROD LOCATION AND P.C.B. SIDE ARE AS APPEARS INSTALLED.

4. MATERIAL

4.1 HEADER ASS'Y:

PLASTIC : HOUSING ...HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : PHOSPHOR BRONZE
PCB : FR4

4.2 EJECT MECHANISM ASS'Y:

PLASTIC : GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
: BUTTON: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PLATE AND PUSH ROD : STAINLESS
EMI CONTACT: PHOSPHOR BRONZE

5. FINISH (PIN)

UNDER PLATING : 0.5μm MIN. Ni
CONTACT AREA : 0.076 μm MIN. GOLD

SOLDER TAIL (FOR TIN LEAD OPTION) : 2.5μm MIN. Sn-Pb
SOLDER TAIL (FOR LEAD FREE OPTION) : 2.5μm MIN. PURE TIN

6. DIM "X"

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68

7. FOR P/N: 61125-050CAN AND 61125-050CANLF:

- TIGHTENING TORQUE OF SCREW: 1.5 ~ 2.0 Kgf-cm
- LUBRICANT SHOULD BE SPREAD TO MATING AREA OF PINS.

- IF LEAD FREE P.N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N. THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- PART NUMBER 61125-***CAC, -***CACLIF IS FOR CISCO
- PRODUCT SPEC: 110-263



ORDERING INFORMATION

NAME	PART NO.		Q'TY
Ⓐ EJECT HEADER ASS'Y	61125-*****	61125-*****LF	1
Ⓑ MATING RECEPTACLE	91931-31169	91931-31169LF	1

mat'l. code				surface		tolerance		projection		product family					
				ISO1302 ✓		ISO1101 ISO406				PCMCIA					
ltr ecn nodr date				tolerances unless otherwise specified				title							
L				angle		linear		MM		EJECTOR HEADER ASS'Y 3.3V, SMT TYPE 1/2/3					
						±0.30									
				0°±2'				scale 1.2							
				dr		WENDY CHEN		07/11/95		dwg no		sheet 5 of 6		size	
				engr		JOSEPH HSIA		07/11/95				61125		A4	
				chr		JOSEPH HSIA		07/11/95							
				appd		JENN TSAO		07/11/95							
sheet		revision								type		Product Customer Drawing			
index		sheet													


DESCRIPTION : ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEW BY USER.

LOWER DECK					Ⓑ MATING RECEPTACLE	MOUNT STYLE TO PCB AND PUSH ROD SIDE
Ⓐ PRODUCT NO.	STAND-OFF HIGH DIM. L	PUSH ROD LOCATION ⓐ	P.C.B. SIDE ⓐ	P.C.B LAYOUT RECOMMENDED		
61125-020CA/020CALF	2.2	RIGHT	ABOVE	P/N: TA-1056	↑ RECEPTACLE PART NUMBER: 91931-31169 91931-31169LF ↓	
61125-220CA/220CALF	2.2	RIGHT	ABOVE	SEE PAGE 6		
61125-040CA/040CALF	4.3	RIGHT	ABOVE	SEE DRAWING P/N: TA-1056		
61125-050CA/050CALF	5.0					
61125-050CAN/050CANLF	5.0					
61125-020CAC/020CACL	2.2					
61125-040CAC/040CACL	4.3					
61125-050CAC/050CACL	5.0					
61125-120CA/120CALF	2.2	LEFT				
61125-140CA/140CALF	4.3					
61125-150CA/150CALF	5.0					
61125-520CA/520CALF	2.2	RIGHT	BELOW	SEE DRAWING P/N: TA-1056		
61125-520FA/520FALF	2.2					
61125-520DA/520DALF	2.2					
61125-540CA/540CALF	4.3					
61125-550CA/550CALF	5.0					
61125-620CA/620CALF	2.2					LEFT
61125-640CA/640CALF	4.3					
61125-650CA/650CALF	5.0					

UPPER DECK					
Ⓐ PRODUCT NO.	JOINT WITH LOWER DECK STAND-OFF HIGH(DIM. L)	PUSH ROD LOCATION ③	P.C.B. SIDE ③	Ⓑ MATING RECEPTACLE	MOUNT STYLE TO PCB AND PUSH ROD SIDE
61125-005CA/005CALF	0.0	RIGHT	ABOVE		
61125-025CA/025CALF	2.2				
61125-045CA/045CALF	4.3				
61125-055CA/055CALF	5.0				
61125-025CAC/025CACLIF	2.2				
61125-045CAC/045CACLIF	4.3				
61125-055CAC/055CACLIF	5.0	LEFT		RECEPTACLE PART NUMBER: 91931-31169 91931-31169LF	
61125-105CA/105CALF	0.0				
61125-125CA/125CALF	2.2				
61125-145CA/145CALF	4.3				
61125-155CA/155CALF	5.0				
61125-505CA/505CALF	0.0				
61125-525CA/525CALF	2.2	RIGHT	BELOW		
61125-545CA/545CALF	4.3				
61125-555CA/555CALF	5.0				
61125-605CA/605CALF	0.0				
61125-625CA/625CALF	2.2	LEFT			
61125-645CA/645CALF	4.3				
61125-655CA/655CALF	5.0				

NOTES:

- IT CAN'T BE USED FOR SINGLE DECK.
- IT MUST BE ASSEMBLED BY USER FOR DOUBLE DECK APPLICATION.(PLEASE REFER TO P/N 61124)



BOARD VIEW FROM CONNECTOR MOUNTED SIDE
TOP OF BOARD IN APPLICATION

FOR 61125-220CA/220CALF ONLY

mat'l. code	surface	tolerance	projection	product family
ISO1302	ISO1101	ISO406	MM	PCMCIA
tolerances unless otherwise specified	angle	±0.30	scale 1.2	EJECTOR HEADER ASS'Y
date	dr	WENDY CHEN	07/11/95	3.3V, SMT TYPE 1/2/3
engr	JOSEPH HSIA	07/11/95		dwg no
chr	JOSEPH HSIA	07/11/95		sheet 6 of 6
appd	JENN TSAO	07/11/95		size
sheet index	revision sheet			A4
				type Product Customer Drawing