


Home: [Ring and Spade Terminals](#)>

Part Number: 50852-7112

Ring Tongue Terminal for 20-24 AWG, Closed Un-insulated Brazed Barrel, Stud Size 2 (M2), Oxygen-Free Copper, Length 12.50mm



Series image - Reference only

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	50852
Category:	Ring and Spade Terminals

[CHECK DISTRIBUTOR INVENTORY](#)

- [Add to My Parts](#)
- [Email this page](#)

Go to [Part Detail](#) ▼

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

- [EU ELV](#): Not Reviewed
- [EU RoHS](#): Not Reviewed
- [China RoHS](#): Not Reviewed
- [REACH SVHC](#): Not Reviewed
- [Low-Halogen Status](#): Not Reviewed

[PDF](#) RoHS Certificate of Compliance (PDF)

[PDF](#) Multiple Part Product Compliance Form

Part Detail

[COLLAPSE ALL](#)

▼ **General**

Status	Obsolete
Category	Ring and Spade Terminals
Series	50852
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800754839334

▼ **Physical**

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	2 (M2)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	20, 22, 24
Wire Size mm ²	0.20 - 0.50

▼ **Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E134962
----	---------

▼ **Material Info**

▼ **Reference - Drawing Numbers**

Product Specification	PS-50852-001
Sales Drawing	SD-50852-001

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan Description	Product #
Hand Crimper For JIS Terminal	57343-5001

Crimp Quality Equipment

[Molex also offers wire strippers, pull testers, shut-height gauges, micro-meters and more](#)

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Molex Connectors

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Optical Solutions
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting
- Application Tooling
- Noise Suppression Sheets

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- California Supply Chains Act
- Careers
- Compliance
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

Other Info

- Feedback
- Help
- Legal Disclaimer
- Trademarks
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex:

