



PTC thermistors for overcurrent protection

Leaded disks, coated, 63 V

Series/Type: **B599*0**

Date: February 2012

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B59930C0080A070	B59930C0120A070 or B59950C0120A070	2013-05-03	2014-06-01	2014-09-01

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

© EPCOS AG 2012. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Overcurrent protection**Leaded disks, coated, 63 V****C910 ... C990****Applications**

- Overcurrent protection
- Short circuit protection

Features


- Lead-free terminals
- Wide range of rated currents:
30 mA up to 1 A
- Marking: Type, manufacturer's logo, reference temperature in °C and date code YYWW (except B59980C0130C* and B59990C*)
- UL approval for $T_{ref} = 120$ °C and 130 °C to UL 1434 with $V_{max} = 65$ V and $V_R = 63$ V (file number E69802)
- UL approval for $T_{ref} = 80$ °C to UL 1434 with $V_{max} = 63$ V and $V_R = 50$ V (file number E69802)
- VDE approval for selected types (license number 104843 E)
- RoHS-compatible

Options

- Leadless disks and leaded disks without coating available on request
- Thermistors with diameter $w \leq 11.0$ mm are also available on tape (to IEC 60286-2)

Delivery mode

- Cardboard strips (standard)
- Cardboard tape reeled or in Ammo pack on request

Dimensional drawing**Dimensions (mm)**

Type	T_{ref} °C	w_{max}	h_{max}	$\emptyset d$
C910	130	22.0	25.5	0.8
C930	80	22.0	25.5	0.6
C930	120	22.0	25.5	0.6
C930	130	17.5	21.0	0.8
C940	80	17.5	21.0	0.6
C940	120	17.5	21.0	0.6
C950	80	13.5	17.0	0.6
C950	120	13.5	17.0	0.6
C950	130	11.0	14.5	0.6
C960	80	11.0	14.5	0.6
C960	120	11.0	14.5	0.6
C960	130	9.0	12.5	0.6
C970	80	9.0	12.5	0.6
C970	120	9.0	12.5	0.6
C970	130	6.5	10.0	0.6
C980	80	6.5	10.0	0.6
C980	120	6.5	10.0	0.6
C980	130	4.0	7.5	0.6
C990	80	4.0	7.5	0.5
C990	120	4.0	7.5	0.5

Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

General technical data

Max. operating voltage	(T _A = 60 °C)	V _{max}	80	V DC or V AC
Rated voltage		V _R	63	V DC or V AC
Switching cycles		N	100	
Tolerance of R _R	(T _{ref} = 80 °C or 120 °C)	ΔR _R	±25	%
Tolerance of R _R	(T _{ref} = 130 °C)	ΔR _R	±20	%
Operating temperature range	(V = 0)	T _{op}	-40/+125	°C
Operating temperature range	(V = V _{max} , T _{ref} = 80 °C)	T _{op}	-40/+85	°C
Operating temperature range	(V = V _{max} , T _{ref} = 120 °C/130 °C)	T _{op}	-40/+125	°C

Electrical specifications and ordering codes

Type	I _R	I _S	I _{Smax} (V = V _{max})	I _r (typ.) (V = V _{max})	T _{ref} (typ.) (V = V _{max})	R _R	R _{min}	Approvals	Ordering code
	mA	mA	A	mA	°C	Ω	Ω		
C910	1000	1500	10.0	60	130	1.2	0.8	X	-
C930	700	1400	10.0	50	120	1.65	1.1	X	-
C930	700	1100	8.0	50	130	2.2	1.5	X	-
C940	450	900	8.0	40	120	2.3	1.5	X	-
C930	340	700	10.0	35	80	1.65	1.1	X	-
C950	320	640	5.5	30	120	3.7	2.4	X	-
C950	320	500	4.3	25	130	4.9	3.2	X	-
C960	250	500	4.3	25	120	5.6	3.7	X	-
C960	250	380	3.0	20	130	8.0	5.2	X	-
C940	245	500	8.0	25	80	2.3	1.5	X	X
C950	170	350	5.5	20	80	3.7	2.4	X	X
C970	150	300	3.0	20	120	9.4	6.2	X	-
C970	150	240	1.0	18	130	20	13.2	X	X
C960	130	265	4.3	15	80	5.6	3.7	X	X
C970	90	190	3.0	11	80	9.4	6.2	X	X
C980	85	170	1.0	16	120	25	16.5	X	-
C980	85	130	0.7	15	130	62	40.9	X	X
C980	50	110	1.0	8	80	25	16.5	X	X
C990	50	100	0.7	12	120	55	36.3	X	-
C990	30	60	0.7	5	80	55	36.3	X	X

Overcurrent protection
Leaded disks, coated, 63 V
C910 ... C990
Reliability data

Test	Standard	Test conditions	$ \Delta R_{25}/R_{25} $
Electrical endurance, cycling	IEC 60738-1	Room temperature, I_{Smax} ; V_{max} Number of cycles: 100	< 25%
Electrical endurance, constant	IEC 60738-1	Storage at $V_{max} / T_{op,max}$ (V_{max}) Test duration: 1000 h	< 25%
Damp heat	IEC 60738-1	Temperature of air: 40 °C Relative humidity of air: 93% Duration: 56 days Test according to IEC 60068-2-78	< 10%
Rapid change of temperature	IEC 60738-1	$T_1 = T_{op,min}$ (0 V), $T_2 = T_{op,max}$ (0 V) Number of cycles: 5 Test duration: 30 min Test according to IEC 60068-2-14, test Na	< 10%
Vibration	IEC 60738-1	Frequency range: 10 to 55 Hz Displacement amplitude: 0.75 mm Test duration: 3 × 2 h Test according to IEC 60068-2-6, test Fc	< 5%
Shock	IEC 60738-1	Acceleration: 390 m/s ² Pulse duration: 6 ms; 6 × 4000 pulses	< 5%
Climatic sequence	IEC 60738-1	Dry heat: $T = T_{op,max}$ (0 V) Test duration: 16 h Damp heat first cycle Cold: $T = T_{op,min}$ (0 V) Test duration: 2 h Damp heat 5 cycles Tests performed according to IEC 60068-2-30	< 10%





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 80^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 80^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 120^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 120^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 130^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)





Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Characteristics (typical) for $T_{ref} = 130^\circ\text{C}$ PTC resistance R_{PTC} versusPTC temperature T_{PTC}

(measured at low signal voltage)

Switching time t_s versus switching current I_s
(measured at 25 °C in still air)PTC current I_{PTC} versus PTC voltage V_{PTC}
(measured at 25 °C in still air)Rated current I_R versus ambient temperature T_A
(measured in still air)

Overcurrent protection

Leaded disks, coated, 63 V

C910 ... C990

Cautions and warnings

General

- EPCOS thermistors are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with EPCOS during the design-in-phase.
- Ensure suitability of thermistor through reliability testing during the design-in phase. The thermistors should be evaluated taking into consideration worst-case conditions.

Storage

- Store thermistors only in original packaging. Do not open the package before storage.
- Storage conditions in original packaging: storage temperature $-25^{\circ}\text{C} \dots +45^{\circ}\text{C}$, relative humidity $\leq 75\%$ annual mean, maximum 95%, dew precipitation is inadmissible.
- Avoid contamination of thermistors surface during storage, handling and processing.
- Avoid storage of thermistor in harmful environment with effect on function or function on long-term operation (examples given under operation precautions).
- Use thermistor within the following period after delivery:
 - Through-hole devices (housed and leaded PTCs): 24 months
 - Motor protection sensors, glass-encapsulated sensors and probe assemblies: 24 months
 - Telecom pair and quattro protectors (TPP, TQP): 24 months
 - Leadless PTC thermistors for pressure contacting: 12 months
 - Leadless PTC thermistors for soldering: 6 months
 - SMDs in EIA sizes 3225 and 4032, and for PTCs with metal tags: 24 months
 - SMDs in EIA sizes 0402, 0603, 0805 and 1210: 12 months

Handling

- PTCs must not be dropped. Chip-offs must not be caused during handling of PTCs.
- Components must not be touched with bare hands. Gloves are recommended.
- Avoid contamination of thermistor surface during handling.

Soldering (where applicable)

- Use rosin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended.
- Complete removal of flux is recommended.
- Standard PTC heaters are not suitable for soldering.

Overcurrent protection**Leaded disks, coated, 63 V****C910 ... C990****Mounting**

- Electrode must not be scratched before/during/after the mounting process.
- Contacts and housing used for assembly with thermistor have to be clean before mounting. Especially grease or oil must be removed.
- When PTC thermistors are encapsulated with sealing material, the precautions given in chapter "Mounting instructions", "Sealing and potting" must be observed.
- When the thermistor is mounted, there must not be any foreign body between the electrode of the thermistor and the clamping contact.
- The minimum force of the clamping contacts pressing against the PTC must be 10 N.
- During operation, the thermistor's surface temperature can be very high. Ensure that adjacent components are placed at a sufficient distance from the thermistor to allow for proper cooling at the thermistors.
- Ensure that adjacent materials are designed for operation at temperatures comparable to the surface temperature of thermistor. Be sure that surrounding parts and materials can withstand this temperature.
- Avoid contamination of thermistor surface during processing.

Operation

- Use thermistors only within the specified temperature operating range.
- Use thermistors only within the specified voltage and current ranges.
- Environmental conditions must not harm the thermistors. Use thermistors only in normal atmospheric conditions. Avoid use in deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas etc), corrosive agents, humid or salty conditions. Contact with any liquids and solvents should be prevented.
- Be sure to provide an appropriate fail-safe function to prevent secondary product damage caused by abnormal function (e.g. use VDR for limitation of overvoltage condition).

Overcurrent protection**Leaded disks, coated, 63 V****C910 ... C990****Symbols and terms**

A	Area
C	Capacitance
C _{th}	Heat capacity
f	Frequency
I	Current
I _{max}	Maximum current
I _R	Rated current
I _{res}	Residual current
I _{PTC}	PTC current
I _r	Residual current
I _{r,oil}	Residual current in oil (for level sensors)
I _{r,air}	Residual current in air (for level sensors)
I _{RMS}	Root-mean-square value of current
I _s	Switching current
I _{smax}	Maximum switching current
LCT	Lower category temperature
N	Number (integer)
N _c	Operating cycles at V _{max} , charging of capacitor
N _f	Switching cycles at V _{max} , failure mode
P	Power
P ₂₅	Maximum power at 25 °C
P _{el}	Electrical power
P _{diss}	Dissipation power
R _G	Generator internal resistance
R _{min}	Minimum resistance
R _R	Rated resistance
ΔR _R	Tolerance of R _R
R _P	Parallel resistance
R _{PTC}	PTC resistance
R _{ref}	Reference resistance
R _S	Series resistance
R ₂₅	Resistance at 25 °C
R _{25,match}	Resistance matching per reel/ packing unit at 25 °C
ΔR ₂₅	Tolerance of R ₂₅
T	Temperature
t	Time
T _A	Ambient temperature
t _a	Thermal threshold time

Overcurrent protection**Leaded disks, coated, 63 V****C910 ... C990**

T_c	Ferroelectric Curie temperature
t_e	Settling time (for level sensors)
T_r	Rated temperature
T_{sense}	Sensing temperature
T_{op}	Operating temperature
T_{PTC}	PTC temperature
t_r	Response time
T_{ref}	Reference temperature
T_{Rmin}	Temperature at minimum resistance
t_s	Switching time
T_{surf}	Surface temperature
UCT	Upper category temperature
V or V_{el}	Voltage (with subscript only for distinction from volume)
$V_{c(max)}$	Maximum DC charge voltage of the surge generator
$V_{F,max}$	Maximum voltage applied at fault conditions in protection mode
V_{RMS}	Root-mean-square value of voltage
V_{BD}	Breakdown voltage
V_{ins}	Insulation test voltage
$V_{link,max}$	Maximum link voltage
V_{max}	Maximum operating voltage
$V_{max,dyn}$	Maximum dynamic (short-time) operating voltage
V_{meas}	Measuring voltage
$V_{meas,max}$	Maximum measuring voltage
V_r	Rated voltage
V_{PTC}	Voltage drop across a PTC thermistor
α	Temperature coefficient
Δ	Tolerance, change
δ_{th}	Dissipation factor
τ_{th}	Thermal cooling time constant
λ	Failure rate
$\square e$	Lead spacing (in mm)

Abbreviations / Notes**SMD** Surface-mount devices

* To be replaced by a number in ordering codes, type designations etc.

+ To be replaced by a letter

All dimensions are given in mm.

The commas used in numerical values denote decimal points.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SiMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.