

DF005M thru DF10M

Reverse Voltage: 50 to 1000V


Forward Current: 1.0A

Features

- Plastic package used has Underwriters Laboratory Flammability Classification 94V-0
- Glass passivated chip junction
- High surge overload rating of 50 Amperes peak
- High temperature soldering guaranteed:
260°C/10 seconds, at 5 lbs. (2.3kg) tension

Mechanical Data

- Case: Molded plastic body over passivated junctions
- Terminals: Plated leads solderable per MIL-STD-750, Method 2026
- Mounting Position: Any
- Weight: 0.014 oz., 0.4 g



Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	DF 005M	DF 01M	DF 02M	DF 04M	DF 06M	DF 08M	DF 10M	Unit
Device Marking Code		DF005	DF01	DF02	DF04	DF06	DF08	DF10	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Max. average forward output rectified current at $T_A=40^\circ\text{C}$	$I_{F(AV)}$	1.0							A
Peak forward surge current single sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	50							A
Rating for fusing ($t < 8.3\text{ms}$)	I^2t	10							A ² sec
Typical thermal resistance per leg (NOTE 1)	$R_{\theta JA}$ $R_{\theta JL}$	40 15							°C/W
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +150							°C

Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	DF 005M	DF 01M	DF 02M	DF 04M	DF 06M	DF 08M	DF 10M	Unit
Maximum instantaneous forward voltage drop per leg at 1.0A	V_F	1.1							V
Maximum reverse current $T_A = 25^\circ\text{C}$ at rated DC blocking voltage per leg $T_A = 125^\circ\text{C}$	I_R	5.0 500							μA
Typical junction capacitance per leg at 4.0V, 1MHz	C_J	25							pF

Note: (1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.5 x 0.5" (13 x 13mm) copper pads

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Leg




Fig. 3 - Typical Forward Characteristics Per Leg




Fig. 4 - Typical Reverse Leakage Characteristics Per Leg




Fig. 5 - Typical Junction Capacitance Per Leg




Fig. 6 - Typical Transient Thermal Impedance

