


PART NUMBER	MATERIAL	A HEIGHT	IMPRINT AREA B	LABELS PER ROW	ROWS PER FANFOLD	STANDARD PKG. QTY.
S100X075VAD	GMV3	0.750 (19.1)	0.25 +/- .031 (6.35)	8	12	5000
S100X125VAD	GMV3	1.250 (31.8)	0.38 +/- .031 (9.53)	8	8	5000
S100X150VAD	GMV3	1.500 (38.1)	0.50 +/- .031 (12.7)	8	6	5000
S100X400VAD	GMV3	4.000 (101.6)	1.00 +/- .031 (25.4)	8	2	1000
S100X075TAD	GMT1	0.750 (19.1)	0.25 +/- .031 (6.35)	8	12	5000
S100X125TAD	GMT1	1.250 (31.8)	0.38 +/- .031 (9.53)	8	8	5000
S100X150TAD	GMT1	1.500 (38.1)	0.50 +/- .031 (12.7)	8	6	5000
S100X400TAD	GMT1	4.000 (101.6)	1.00 +/- .031 (25.4)	8	2	1000
S100X075VADY	GMV3	0.750 (19.1)	0.25 +/- .031 (6.35)	8	12	5000
S100X125VADY	GMV3	1.250 (31.8)	0.38 +/- .031 (9.53)	8	8	5000
S100X150VADY	GMV3	1.500 (38.1)	0.50 +/- .031 (12.7)	8	6	5000
S100X400VADY	GMV3	4.000 (101.6)	1.00 +/- .031 (25.4)	8	2	1000



- NOTES:
1. ALL LABELS TO BE EQUALLY SPACED AS SHOWN.
 2. MILLIMETERS ARE IN ().
 3. SEE MFG. DWG. A61148.

100472LM-C10377-S100xxxVADTAD-00.prt									
PANDUIT CORP. TIMLEY PARK, ILLINOIS									
CUSTOMER DRAWING									
OPTIMUM SELF-LAM. S100X***VAD, S100X***VADY, AND S100X***TAD COMPUTER PRINTABLE LABELS									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.1X) ± .031 (1.00X) ± .005 (1.00X) ± .015 ANGLES ± 1°									
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION									
SCALE: NTS									
SEE TABLE									
C10377									
C									

Q	8-7-08	RVU	RELEASED TO PRODUCTION.	4162	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP