




COIL: @ +25 °C

RESISTANCE 1030 OHMS ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 11.4 VDC

MUST RELEASE 1.1 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 20 g's

SHOCK 50 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX.

RELEASE 5 MS MAX.

CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 3/9/95 CK. 3/9/95

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. C.I.I. STD.

CUST. NO.

TYPE 'HMS' RELAY

HMS1201S004