




DO NOT SCALE

DIMENSIONS IN mm



METRIC

THIRD ANGLE
PROJECTION


STRIP



LOOSE-PIECE



SECTION A-A



SECTION B-B

WIRE RANGE : 0,03-0,09 mm² (32-28 AWG)
INSUL. RANGE : 0,4 -0,8 mm (.016-.030)

NOTES :

- 1 FOR CRIMPDETAILS SEE AMP-SPEC. 114-19.000 .
- 2 MEETS PRODUCTSPECIFICATION 108-10042.

NOTES	MATERIAL	THICKNESS	AREA
20	TIN	2,0 µm	ALL OVER
21	NICKEL GOLD TIN/LEAD	0,8 µm	ALL OVER CONTACT AREA BARREL
22	NICKEL GOLD GOLD	0,8 µm	ALL OVER CONTACT AREA ALL OVER
23	NICKEL GOLD GOLD	1,2 µm	ALL OVER CONTACT AREA ALL OVER
24	NICKEL SILVER TIN/LEAD	2,5 µm	ALL OVER CONTACT AREA BARREL
25	SILVER	0,5 µm	ALL OVER
26	SILVER	2,5 µm	ALL OVER

DIRECTION OFF TOP OF REEL

AMPOMATOR + MINI-APPL.
107-3-F16.1

107-3-F16.2

TERMINAL "U" UP.

CUSTOMER
DRAWINGFOR REFERENCE ONLY
WILL NOT BE UPDATED

DR.	DATE
L.V.D.HEYDEN	19.08.1987
CHK.	DATE
P.V.D.HAGEN	
APP.	DATE
L.V.SOEST	

1-166971-1	A		BRASS	ECON.GOLD	21
1-166971-0	B	1-166978-0	BRASS	ECON.GOLD	21
166971-5	A		BRASS	EL.TIN	20
166971-4	A		BRASS	SEL.GOLD	22
166971-2	B	166978-2	BRASS	SEL.GOLD	22
166971-1	B	166978-1	BRASS	EL.TIN	20
PARTNUMBER	DIRECTION OF REEL	LOOSE-PIECE	MATERIAL	PLATING	

AMP

AMP-HOLLAND B.V.

's-Hertogenbosch, The Netherlands.

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION AUG., 1987

© COPYRIGHT 1987 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.

WIRE RANGE	NAME	REV. DATE
-	SOCKET TYPE III CONTACT	D M Y
INSUL. RANGE	SIZE 16	02 08 04
SIZE A3	SHEET 1 OF 1	REV. LTR. E
DWG. No.	C-166971	