



FLEXSTRIP* JUMPERS


+CONDUCTOR PITCH "A"			MARGIN C (min.)		THICKNESS D (MAX.)		PIN DIAMETER E ±0,025 (±.001")		NUMBER OF CONDUCTORS		
Cat.Ref. mm (inch)			mm (inch.)		mm (inch.)		mm (inch.)		min. max.		
1	1,27	.050"	0,25	.010"	0,64	.025"	0,320	.0126"	2	- 30	
6	1,90	.075"	0,38	.015"	0,84	.033"	0,404	.0159"	2	- 30	
2	2,54	.100"	0,51	.020"	0,84	.033"	0,511	.0201"	2	- 30	
3	3,18	.125"	1,52	.060"	0,84	.033"	0,511	.0201"	2	- 25	
4	3,81	.150"	1,52	.060"	0,84	.033"	0,511	.0201"	2	- 20	
5	5,08	.200"	1,52	.060"	0,84	.033"	0,511	.0201"	2	- 15	

Dimensions are shown in mm (inches.)
+ Tolerance on Pitch ±0,25 (0.01") non-cumulative.


INSULATION LENGTH B ±1.57 (±0.062")		
mm	(inch)	Cat. Ref.
25.4	1	1
38.1	1½	1.5
50.8	2	2
63.5	2½	2.5
76.2	3	3
88.9	3½	3.5
101.6	4	4
114.3	4½	4.5
127	5	5
139.7	5½	5.5
152.4	6	6

PROPERTIES :-
Insulation Material - Nomex#
Temperature Rating - 105°C
Current Rating - 2 amps
U.L. Style Number - 5188

NOTES:-
*Trademark of Thomas & Betts Corporation
*Registered trademark of E.I. Du Pont de Nemours



CATALOGUE NUMBERING SYSTEM




EXAMPLE:-
FSN -22A - 15
FSN - Flexstrip Jumper With Nomex Insulation
2 - Conductor Pitch 2.54 (0.100)
2 - Insulation Length 50.8 (2)
A - Straight Pin
15 - Number of Conductors 15

T&B THOMAS & BETTS INTERNATIONAL
EUROPEAN ENGINEERING DIVISION

DRG. N°
3S-10018

IMPERIAL DIMENSIONS
SHOWN THUS []
TOLERANCES
0000 EQUALS ±.0002
000 EQUALS ±.003
00 EQUALS ±.015



THIRD ANGLE PROJECTION

PART NAME			
PRODUCT CODE			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
MATERIAL	HEAT TREAT	FINISH	SCALE
DR.	CH.	APP.	REV
DESCRIPTION			
DATE			
BY			

FSN-24A-10
tyco Electronics 4-1437145-8
REV 0 SH71 of 1