



Features:


- High Quality Minature Audio Transformers
- Low Distortion
- Encapsulated PCB mounting
- Various winding ratios
- Impedance matching
- UL94-V0 rated materials
- RoHS Compliant
- Custom variations




Dimensions:
 Height : 12.7mm
 Width : 18.0mm
 Length : 18.0mm
 Weight : 0.015kg




X: Year Code
WW: Week of Manufacture



Pin View (Bottom)



PCB Layout



Electrical Schematic VTX-101-16##

Part No	Ratio	Imp. Pri Z (Ω)	Imp. Sec Z (Ω)	Imp. Pri Series Z (Ω)	Imp. Sec Series Z (Ω)	Pri DCR Ω +/-10%	Sec DCR Ω +/-10%	Freq. Range	Isolation Voltage
VTX-101-1601	1CT : 1 CT	600 CT	600 CT			33+35	32+34	60~ 25KHz	1.5KVac
VTX-101-1602	1 : 1	600	600			68	68	60~ 25KHz	
VTX-101-1603	1 : 2 CT	600	2.4K CT			70	200	60~ 25KHz	
VTX-101-1604	1 : 1 CT	600	600 CT			68	32+34	60~ 25KHz	
VTX-101-1605	1 : 2 CT	200	800 CT			50	120	30~ 25KHz	
VTX-101-1606	1 : 1 CT	800	800 CT			105	134	60~ 25KHz	
VTX-101-1607	1: 6.3 CT	600	10K CT			70	230+250	30~ 25KHz	
VTX-101-1608	1 CT : 1 CT	10K CT	10K CT			225+225	225+225	30 ~ 25KHz	
VTX-101-1609	1 : 1 CT	10K	10K CT			450	225+225	30 ~ 25KHz	1200V
VTX-101-1617	4.07 : 1	10K	600			254	21.5	60~ 25KHz	
VTX-101-1634	1+1 : 2	150+150	600	600	600	31	33	60~ 25KHz	500V
VTX-101-1654	1:2	150	600			18	70	60-25KHz	4.2KVac
VTX-101-1655	1:4.3	8	150			1	25	200- 20KHz	1.5KVac

Products can be altered to suit custom requirements. Please contact Vigortronix for your specific requirements.
 The information contained in this document is subject to change without notice.

Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK

Tel. +44 (0)1993 777570 Fax. +44 (0)1993 777580 Web. www.vigortronix.com E-mail: sales@vigortronix.com

Vigortronix is a trading name of Vigortronix (UK) Limited

Vigortronix.com

Performance parameters for Part VTX-101-1604

Part No	VTX-101-1604			Unit
Suitable for modem speed up to:	V.34			-----
Reflects 600 ohms at PRI with R load =	600			ohms
D.C. Resistance, +/-15%,PRI	109			ohms
D.C. Resistance,+/-15%,SEC	134			ohms
Frequency Response, 30 to 25KHz	+/-0.5			dB
Insertion Loss at 2kHz,(ref 600Ω Load),max.	1.5 Max			dB
Return Loss vs.600 ohms at 100~4kHz	15 Min			dB
Dielectric Test PRI-SEC (50Hz)	1500 Min			V rms
Direct Current PRI, maximum	none			mA DC
Turns Ratio (PRI:SEC),+/-2%	1:1			-----
Longitudinal Balance, 200 to 4000 Hz,min.	90			dB
Total Harmonic Distortion, 75Hz ,10dBm T.H.D 30Hz to 11kHz at 0dBm.	<1% <1%			dBm
Saturation	10Vrms (65V Peak)			V rms
Operating temperature range:	-20°C to + 70°C			°C
Storage temperature range:	-40°C to +125°C			°C

Note: Recommended maximum 100uA DC current.