






LOC	DIST	REVISIONS				
		REV	DATE	BY	CHKD	APPD
CM	00	C3	23AUG12	KH	SM	


- 1 PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 2 WIRE RANGE: 3-5.5 mm² [12-10 AWG].
- 3 INSULATION DIAMETER: 5.08 [.200] MAX.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00508 [.000200] MIN BRIGHT TIN-LEAD.
- 6 0.00508 [.000200] MIN HALT TIN.




SECTION D-D




3.76 [.148]	10
3.18 [.125]	12
A	AWG



SECTION A-A




SECTION B-B



SECTION C-C

6	3-794037-1
5	794037-1
FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER	22AUG2003	 TE Connectivity					
DIMENSIONS: INCHES		CHK J. ELLIS	22AUG2003						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. ELLIS	22AUG2003	NAME				
	0 PLC ±		PRODUCT SPEC		TERMINAL, AMP-IN				
	1 PLC ±		APPLICATION SPEC						
	2 PLC ± 0.13 [.005]		SIZE			CAGE CODE	DRAWING NO	RESTRICTED TO	
	3 PLC ±		A1			00779	C	794037	—
4 PLC ±		WEIGHT		CUSTOMER DRAWING					
ANGLES ±		SCALE		10:1		SHEET	1 of 1	REV	C3
FINISH		MATERIAL		0.198 [.0078] PH BRZ					

METRIC