

HONEYWELL PART NUMBER
1SX48-H58
PRODUCT CODE VDA4298

REV	DOCUMENT	CHANGED BY	CHECK
7	0038446	KVB 20MAY08	BLR

B



A

A

B

A

A



NOTES



1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
2 PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES.

- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
4 - SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION. ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE

RELEASE NO.	PR-11856
REPLACES	

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 	DRAWN	SPK	03DEC07	Honeywell			
OPERATING FORCE — — — 5 OZ MAX	CONTACT ARRANGEMENT SPDT				CHECK	RJ	03DEC07				
RELEASE FORCE— — — — 1 OZ MIN	28 VOLTS DC RATING				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .005 MAX		SEA LEVEL	50,000 FT								
OVERTRAVEL — — — — — .010 MIN	INDUCTIVE	4 AMP	2.5 AMP								
	RESISTIVE	7 AMP	7 AMP		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
	MAXIMUM INRUSH 24 AMP				RASTER			B	I	1SX48-H58	7
	APPROVALS	KEMA, CE	7A 250V~ T125 5E4 					WEIGHT:.003 LB MAX			SHEET 1 OF 1
		UL, CSA	7A 250 VAC   BRAND L7								