

Surface Mount Multilayer Ceramic Chip Capacitors MIL Qualified, Type CDR



FEATURES

- Military qualified products
- Federal stock control number, CAGE CODE 2770A
- High reliability tested per MIL-PRF-55681
- Tin / lead termination codes "W", "Z", and "U"
- Lead (Pb)-free termination codes "Y" and "M"
- Wet build process
- Reliable Noble Metal Electrode (NME) system
- Material categorization: for definitions of compliance please see www.vishay.com/doc299912



Available
RoHS*
Available
**HALOGEN
FREE**

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

APPLICATIONS

- Avionic systems
- Sonar systems
- Satellite systems
- Missiles applications
- Geographical information systems
- Global positioning systems

ELECTRICAL SPECIFICATIONS

Note

- Electrical characteristics at +25 °C unless otherwise specified

Operating Temperature: -55 °C to +125 °C

Capacitance Range: 1.0 pF to 470 nF

Voltage Range: 6.3 V_{DC} to 100 V_{DC}

Temperature Coefficient of Capacitance (TCC):

BP: 0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C, with 0 V_{DC} applied
0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C, with 100 % rated V_{DC} applied

BX: ± 15 % from -55 °C to +125 °C, with 0 V_{DC} applied

BX: +15 %, -25 % from -55 °C to +125 °C, with 100 % rated V_{DC} applied

BR: ± 15 % from -55 °C to +125 °C, with 0 V_{DC} applied
+15 %, -40 % -55 °C to +125 °C, with 100 % rated V_{DC} applied

Dissipation Factor (DF):

BP: 0.15 % maximum

BX: 2.50 % maximum

BR: ≤ 25 V: 3.5 % maximum

> 25 V: 2.5 % maximum

Test frequency:

1 MHz ± 50 kHz for BP capacitors ≤ 1000 pF

and for BX capacitors ≤ 100 pF

All other BP, BX, and BR at 1 kHz ± 50 Hz

Aging Rate:

BP: 0 % maximum per decade

BX, BR: 1 % maximum per decade

Insulation Resistance (IR):

at +25 °C and rated voltage 100 000 MΩ minimum or 1000 ΩF, whichever is less

Dielectric Strength Test:

performed per method 103 of EIA-198-2-E.

Applied test voltages:

≤ 100 V_{DC}-rated: 250 % of rated voltage



QUICK REFERENCE DATA

DIELECTRIC	STYLE (CASE)	MAXIMUM VOLTAGE (V)	CAPACITANCE	
			MINIMUM	MAXIMUM
BP	CDR01 (0805)	100	10 pF	180 pF
BX	CDR01 (0805)	100	120 pF	4.7 nF
BP	CDR02 (1805)	100	220 pF	270 pF
BX	CDR02 (1805)	100	3.9 nF	22 nF
BP	CDR03 (1808)	100	330 pF	1.0 nF
BX	CDR03 (1808)	100	12 nF	68 nF
BP	CDR04 (1812)	100	1.2 nF	3.3 nF
BX	CDR04 (1812)	100	39 nF	180 nF
BX	CDR06 (2225)	50	390 nF	470 nF
BP	CDR31 (0805)	100	1.0 pF	680 pF
BX	CDR31 (0805)	100	470 pF	18 nF
BP	CDR32 (1206)	100	1.0 pF	2.2 nF
BX	CDR32 (1206)	100	4.7 nF	39 nF
BP	CDR33 (1210)	100	1.0 nF	3.3 nF
BX	CDR33 (1210)	100	15 nF	100 nF
BP	CDR34 (1812)	100	2.2 nF	10 nF
BX	CDR34 (1812)	100	27 nF	180 nF
BP	CDR35 (1825)	100	4.7 nF	22 nF
BX	CDR35 (1825)	100	56 nF	470 nF
BP	CDR36 (0603)	100	1.0 pF	1000 pF
BX	CDR36 (0603)	100	100 pF	56 nF
BR	CDR36 (0603)	100	100 pF	100 nF
BP	CDR37 (0402)	100	1.0 pF	150 pF
BX	CDR37 (0402)	50	100 pF	8.2 nF
BR	CDR37 (0402)	50	100 pF	10 nF

Note


- Detail ratings see selection chart

ORDERING INFORMATION - MILITARY

CDR31	BX	102	A	K	Y	S	A	T
MILITARY STYLE	DIELECTRIC	CAPACITANCE NOMINAL CODE	DC VOLTAGE RATING ⁽¹⁾	CAPACITANCE TOLERANCE ⁽²⁾	TERMINATION	FAILURE RATE	MARKING	PACKAGING
CDR01 CDR02 CDR03 CDR04 CDR06 CDR31 CDR32 CDR33 CDR34 CDR35 CDR36 CDR37	BP BR BX	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. Examples: 102 = 1000 pF 1R8 = 1.8 pF	W = 6.3 V X = 10 V Y = 16 V Z = 25 V A = 50 V B = 100 V	C = ± 0.25 pF D = ± 0.5 pF F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % M = ± 20 %	M = silver palladium ⁽³⁾ Y = Ni barrier with 100 % tin W, Z = Ni barrier with tin / lead plate min. 4 % lead U = Ni barrier solder coated (min. of 4 % lead)	M = 1.0 % P = 0.1 % R = 0.01 % S = 0.001 % Consult factory for failure rate status	A = unmarked	T = 7" reel / plastic tape J = 7" reel (low quantity) C = 7" reel / paper tape R = 11 1/4" / 13" reel / plastic tape P = 11 1/4" / 13" reel / paper tape B = bulk

Notes

- ⁽¹⁾ DC voltage rating should not be exceeded in application. Other application factors may affect the MLCC performance.
Consult for questions: mlcc@vishay.com
- ⁽²⁾ Available tolerances please see rating chart
- ⁽³⁾ M termination not available for CDR36 and CDR37 parts

DIMENSIONS in inches (millimeters)


MIL-PRF-55681	STYLE	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERM. (P)	
					MINIMUM	MAXIMUM
/1	CDR01	0.080 ± 0.015 (2.03 ± 0.38)	0.050 ± 0.015 (1.27 ± 0.38)	0.055 (1.40)	0.010 (0.25)	0.030 (0.75)
	CDR02	0.180 ± 0.015 (4.57 ± 0.38)	0.050 ± 0.015 (1.27 ± 0.38)	0.055 (1.40)	0.010 (0.25)	0.030 (0.75)
	CDR03	0.180 ± 0.015 (4.57 ± 0.38)	0.080 ± 0.015 (2.03 ± 0.38)	0.080 (2.03)	0.010 (0.25)	0.030 (0.75)
	CDR04	0.180 ± 0.015 (4.57 ± 0.38)	0.125 ± 0.015 (3.20 ± 0.38)	0.080 (2.03)	0.010 (0.25)	0.030 (0.75)
/3	CDR06	0.225 ± 0.020 (5.72 ± 0.51)	0.250 ± 0.020 (6.35 ± 0.51)	0.080 (2.03)	0.010 (0.25)	0.030 (0.75)
/7	CDR31	0.078 ± 0.008 (2.00 ± 0.20)	0.049 ± 0.008 (1.25 ± 0.20)	0.051 (1.30)	0.012 (0.30)	0.028 (0.70)
/8	CDR32	0.125 ± 0.008 (3.20 ± 0.20)	0.062 ± 0.008 (1.60 ± 0.20)	0.051 (1.30)	0.012 (0.30)	0.028 (0.70)
/9	CDR33	0.125 ± 0.010 (3.20 ± 0.25)	0.098 ± 0.010 (2.50 ± 0.25)	0.049 (1.25)	0.010 (0.25)	0.030 (0.75)
/10	CDR34	0.176 ± 0.010 (4.50 ± 0.25)	0.125 ± 0.010 (3.20 ± 0.25)	0.059 (1.50)	0.010 (0.25)	0.030 (0.75)
/11	CDR35	0.176 ± 0.012 (4.50 ± 0.30)	0.250 ± 0.012 (6.40 ± 0.30)	0.059 (1.50)	0.008 (0.20)	0.032 (0.80)
/12	CDR36	0.063 ± 0.006 (1.60 ± 0.15)	0.032 ± 0.006 (0.81 ± 0.15)	0.036 (0.91)	0.008 (0.20)	0.020 (0.51)
/13	CDR37	0.040 ± 0.004 (1.02 ± 0.10)	0.020 ± 0.004 (0.51 ± 0.10)	0.024 (0.61)	0.004 (0.10)	0.016 (0.41)

MIL-C-55681 QUALIFIED, TYPE CDR

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR01BP						
CDR01BP100B_ _ _	100	10	J, K	BP	100	
CDR01BP120BJ_ _ _	120	12	J	BP	100	
CDR01BP150B_ _ _	150	15	J, K	BP	100	
CDR01BP180BJ_ _ _	180	18	J	BP	100	
CDR01BP220B_ _ _	220	22	J, K	BP	100	
CDR01BP270BJ_ _ _	270	27	J	BP	100	
CDR01BP330B_ _ _	330	33	J, K	BP	100	
CDR01BP390BJ_ _ _	390	39	J	BP	100	
CDR01BP470B_ _ _	470	47	J, K	BP	100	
CDR01BP560BJ_ _ _	560	56	J	BP	100	
CDR01BP680B_ _ _	680	68	J, K	BP	100	
CDR01BP820BJ_ _ _	820	82	J	BP	100	
CDR01BP101B_ _ _	101	100	J, K	BP	100	
CDR01BP121B_ _ _	121	120	J, K	BP	100	
CDR01BP151B_ _ _	151	150	J, K	BP	100	
CDR01BP181B_ _ _	181	180	J, K	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR01BX						
CDR01BX121B_ _ _	121	120	J, K	BX	100	
CDR01BX151B_ _ _	151	150	J, K	BX	100	
CDR01BX181B_ _ _	181	180	J, K	BX	100	
CDR01BX221B_ _ _	221	220	K, M	BX	100	
CDR01BX271BK_ _	271	270	K	BX	100	
CDR01BX331B_ _ _	331	330	K, M	BX	100	
CDR01BX391BK_ _	391	390	K	BX	100	
CDR01BX471B_ _ _	471	470	K, M	BX	100	
CDR01BX561BK_ _	561	560	K	BX	100	
CDR01BX681B_ _ _	681	680	K, M	BX	100	
CDR01BX821BK_ _	821	820	K	BX	100	
CDR01BX102B_ _ _	102	1000	K, M	BX	100	
CDR01BX122BK_ _	122	1200	K	BX	100	
CDR01BX152B_ _ _	152	1500	K, M	BX	100	
CDR01BX182BK_ _	182	1800	K	BX	100	
CDR01BX222B_ _ _	222	2200	K, M	BX	100	
CDR01BX272BK_ _	272	2700	K	BX	100	
CDR01BX332B_ _ _	332	3300	K, M	BX	100	
CDR01BX392AK_ _	392	3900	K	BX	50	
CDR01BX472A_ _ _	472	4700	K, M	BX	50	
CDR02BP						
CDR02BP221B_ _ _	221	220	J, K	BP	100	
CDR02BP271BJ_ _	271	270	J	BP	100	
CDR02BX						
CDR02BX392BK_ _	392	3900	K	BX	100	
CDR02BX472B_ _ _	472	4700	K, M	BX	100	
CDR02BX562BK_ _	562	5600	K	BX	100	
CDR02BX682B_ _ _	682	6800	K, M	BX	100	
CDR02BX822BK_ _	822	8200	K	BX	100	
CDR02BX103B_ _ _	103	10 000	K, M	BX	100	
CDR02BX123AK_ _	123	12 000	K	BX	50	
CDR02BX153A_ _ _	153	15 000	K, M	BX	50	
CDR02BX183AK_ _	183	18 000	K	BX	50	
CDR02BX223A_ _ _	223	22 000	K, M	BX	50	
CDR03BP						
CDR03BP331B_ _ _	331	330	J, K	BP	100	
CDR03BP391BJ_ _	391	390	J	BP	100	
CDR03BP471B_ _ _	471	470	J, K	BP	100	
CDR03BP561BJ_ _	561	560	J	BP	100	
CDR03BP681B_ _ _	681	680	J, K	BP	100	
CDR03BP821BJ_ _	821	820	J	BP	100	
CDR03BP102B_ _ _	102	1000	J, K	BP	100	
CDR03BX						
CDR03BX123BK_ _	123	12 000	K	BX	100	
CDR03BX153B_ _ _	153	15 000	K, M	BX	100	
CDR03BX183BK_ _	183	18 000	K	BX	100	
CDR03BX223B_ _ _	223	22 000	K, M	BX	100	
CDR03BX273BK_ _	273	27 000	K	BX	100	
CDR03BX333B_ _ _	333	33 000	K, M	BX	100	
CDR03BX393AK_ _	393	39 000	K	BX	50	
CDR03BX473A_ _ _	473	47 000	K, M	BX	50	
CDR03BX563AK_ _	563	56 000	K	BX	50	
CDR03BX683A_ _ _	683	68 000	K, M	BX	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR04BP						
CDR04BP122BJ_ _	122	1200	J	BP	100	
CDR04BP152B_ _ _	152	1500	J, K	BP	100	
CDR04BP182BJ_ _	182	1800	J	BP	100	
CDR04BP222B_ _ _	222	2200	J, K	BP	100	
CDR04BP272BJ_ _	272	2700	J	BP	100	
CDR04BP332B_ _ _	332	3300	J, K	BP	100	
CDR04BX						
CDR04BX393BK_ _	393	39 000	K	BX	100	
CDR04BX473B_ _ _	473	47 000	K, M	BX	100	
CDR04BX563BK_ _	563	56 000	K	BX	100	
CDR04BX823AK_ _	823	82 000	K	BX	50	
CDR04BX104A_ _ _	104	100 000	K, M	BX	50	
CDR04BX124AK_ _	124	120 000	K	BX	50	
CDR04BX154A_ _ _	154	150 000	K, M	BX	50	
CDR04BX184AK_ _	184	180 000	K	BX	50	
CDR06BX						
CDR06BX394AK_ _	394	390 000	K	BX	50	
CDR06BX474A_ _ _	474	470 000	K, M	BX	50	
CDR31BP						
CDR31BP1R0B_ _ _	1R0	1.0	C	BP	100	
CDR31BP1R1B_ _ _	1R1	1.1	C	BP	100	
CDR31BP1R2B_ _ _	1R2	1.2	C	BP	100	
CDR31BP1R3B_ _ _	1R3	1.3	C	BP	100	
CDR31BP1R5B_ _ _	1R5	1.5	C	BP	100	
CDR31BP1R6B_ _ _	1R6	1.6	C	BP	100	
CDR31BP1R8B_ _ _	1R8	1.8	C	BP	100	
CDR31BP2R0B_ _ _	2R0	2.0	C	BP	100	
CDR31BP2R2B_ _ _	2R2	2.2	C	BP	100	
CDR31BP2R4B_ _ _	2R4	2.4	C	BP	100	
CDR31BP2R7B_ _ _	2R7	2.7	C, D	BP	100	
CDR31BP3R0B_ _ _	3R0	3.0	C, D	BP	100	
CDR31BP3R3B_ _ _	3R3	3.3	C, D	BP	100	
CDR31BP3R6B_ _ _	3R6	3.6	C, D	BP	100	
CDR31BP3R9B_ _ _	3R9	3.9	C, D	BP	100	
CDR31BP4R3B_ _ _	4R3	4.3	C, D	BP	100	
CDR31BP4R7B_ _ _	4R7	4.7	C, D	BP	100	
CDR31BP5R1B_ _ _	5R1	5.1	C, D	BP	100	
CDR31BP5R6B_ _ _	5R6	5.6	C, D	BP	100	
CDR31BP6R2B_ _ _	6R2	6.2	C, D	BP	100	
CDR31BP6R8B_ _ _	6R8	6.8	C, D	BP	100	
CDR31BP7R5B_ _ _	7R5	7.5	C, D	BP	100	
CDR31BP8R2B_ _ _	8R2	8.2	C, D	BP	100	
CDR31BP9R1B_ _ _	9R1	9.1	C, D	BP	100	
CDR31BP100B_ _ _	100	10	F, J, K	BP	100	
CDR31BP110B_ _ _	110	11	F, J, K	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR31BP						
CDR31BP120B_	120	12	F, J, K	BP	100	
CDR31BP130B_	130	13	F, J, K	BP	100	
CDR31BP150B_	150	15	F, J, K	BP	100	
CDR31BP160B_	160	16	F, J, K	BP	100	
CDR31BP180B_	180	18	F, J, K	BP	100	
CDR31BP200B_	200	20	F, J, K	BP	100	
CDR31BP220B_	220	22	F, J, K	BP	100	
CDR31BP240B_	240	24	F, J, K	BP	100	
CDR31BP270B_	270	27	F, J, K	BP	100	
CDR31BP300B_	300	30	F, J, K	BP	100	
CDR31BP330B_	330	33	F, J, K	BP	100	
CDR31BP360B_	360	36	F, J, K	BP	100	
CDR31BP390B_	390	39	F, J, K	BP	100	
CDR31BP430B_	430	43	F, J, K	BP	100	
CDR31BP470B_	470	47	F, J, K	BP	100	
CDR31BP510B_	510	51	F, J, K	BP	100	
CDR31BP560B_	560	56	F, J, K	BP	100	
CDR31BP620B_	620	62	F, J, K	BP	100	
CDR31BP680B_	680	68	F, J, K	BP	100	
CDR31BP750B_	750	75	F, J, K	BP	100	
CDR31BP820B_	820	82	F, J, K	BP	100	
CDR31BP910B_	910	91	F, J, K	BP	100	
CDR31BP101B_	101	100	F, J, K	BP	100	
CDR31BP111B_	111	110	F, J, K	BP	100	
CDR31BP121B_	121	120	F, J, K	BP	100	
CDR31BP131B_	131	130	F, J, K	BP	100	
CDR31BP151B_	151	150	F, J, K	BP	100	
CDR31BP161B_	161	160	F, J, K	BP	100	
CDR31BP181B_	181	180	F, J, K	BP	100	
CDR31BP201B_	201	200	F, J, K	BP	100	
CDR31BP221B_	221	220	F, J, K	BP	100	
CDR31BP241B_	241	240	F, J, K	BP	100	
CDR31BP271B_	271	270	F, J, K	BP	100	
CDR31BP301B_	301	300	F, J, K	BP	100	
CDR31BP331B_	331	330	F, J, K	BP	100	
CDR31BP361B_	361	360	F, J, K	BP	100	
CDR31BP391B_	391	390	F, J, K	BP	100	
CDR31BP431B_	431	430	F, J, K	BP	100	
CDR31BP471B_	471	470	F, J, K	BP	100	
CDR31BP511A_	511	510	F, J, K	BP	50	
CDR31BP561A_	561	560	F, J, K	BP	50	
CDR31BP621A_	621	620	F, J, K	BP	50	
CDR31BP681A_	681	680	F, J, K	BP	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR31BX						
CDR31BX471B_ _ _	471	470	K, M	BX	100	
CDR31BX561B_ _ _	561	560	K, M	BX	100	
CDR31BX681B_ _ _	681	680	K, M	BX	100	
CDR31BX821B_ _ _	821	820	K, M	BX	100	
CDR31BX102B_ _ _	102	1000	K, M	BX	100	
CDR31BX122B_ _ _	122	1200	K, M	BX	100	
CDR31BX152B_ _ _	152	1500	K, M	BX	100	
CDR31BX182B_ _ _	182	1800	K, M	BX	100	
CDR31BX222B_ _ _	222	2200	K, M	BX	100	
CDR31BX272B_ _ _	272	2700	K, M	BX	100	
CDR31BX332B_ _ _	332	3300	K, M	BX	100	
CDR31BX392B_ _ _	392	3900	K, M	BX	100	
CDR31BX472B_ _ _	472	4700	K, M	BX	100	
CDR31BX562A_ _ _	562	5600	K, M	BX	50	
CDR31BX682A_ _ _	682	6800	K, M	BX	50	
CDR31BX822A_ _ _	822	8200	K, M	BX	50	
CDR31BX103A_ _ _	103	10 000	K, M	BX	50	
CDR31BX123A_ _ _	123	12 000	K, M	BX	50	
CDR31BX153A_ _ _	153	15 000	K, M	BX	50	
CDR31BX183A_ _ _	183	18 000	K, M	BX	50	
CDR32BP						
CDR32BP1R0B_ _ _	1R0	1.0	C	BP	100	
CDR32BP1R1B_ _ _	1R1	1.1	C	BP	100	
CDR32BP1R2B_ _ _	1R2	1.2	C	BP	100	
CDR32BP1R3B_ _ _	1R3	1.3	C	BP	100	
CDR32BP1R5B_ _ _	1R5	1.5	C	BP	100	
CDR32BP1R6B_ _ _	1R6	1.6	C	BP	100	
CDR32BP1R8B_ _ _	1R8	1.8	C	BP	100	
CDR32BP2R0B_ _ _	2R0	2.0	C	BP	100	
CDR32BP2R2B_ _ _	2R2	2.2	C	BP	100	
CDR32BP2R4B_ _ _	2R4	2.4	C	BP	100	
CDR32BP2R7B_ _ _	2R7	2.7	C, D	BP	100	
CDR32BP3R0B_ _ _	3R0	3.0	C, D	BP	100	
CDR32BP3R3B_ _ _	3R3	3.3	C, D	BP	100	
CDR32BP3R6B_ _ _	3R6	3.6	C, D	BP	100	
CDR32BP3R9B_ _ _	3R9	3.9	C, D	BP	100	
CDR32BP4R3B_ _ _	4R3	4.3	C, D	BP	100	
CDR32BP4R7B_ _ _	4R7	4.7	C, D	BP	100	
CDR32BP5R1B_ _ _	5R1	5.1	C, D	BP	100	
CDR32BP5R6B_ _ _	5R6	5.6	C, D	BP	100	
CDR32BP6R2B_ _ _	6R2	6.2	C, D	BP	100	
CDR32BP6R8B_ _ _	6R8	6.8	C, D	BP	100	
CDR32BP7R5B_ _ _	7R5	7.5	C, D	BP	100	
CDR32BP8R2B_ _ _	8R2	8.2	C, D	BP	100	
CDR32BP9R1B_ _ _	9R1	9.1	C, D	BP	100	
CDR32BP100B_ _ _	100	10	F, J, K	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR32BP						
CDR32BP110B_ _ _	110	11	F, J, K	BP	100	
CDR32BP120B_ _ _	120	12	F, J, K	BP	100	
CDR32BP130B_ _ _	130	13	F, J, K	BP	100	
CDR32BP150B_ _ _	150	15	F, J, K	BP	100	
CDR32BP160B_ _ _	160	16	F, J, K	BP	100	
CDR32BP180B_ _ _	180	18	F, J, K	BP	100	
CDR32BP200B_ _ _	200	20	F, J, K	BP	100	
CDR32BP220B_ _ _	220	22	F, J, K	BP	100	
CDR32BP240B_ _ _	240	24	F, J, K	BP	100	
CDR32BP270B_ _ _	270	27	F, J, K	BP	100	
CDR32BP300B_ _ _	300	30	F, J, K	BP	100	
CDR32BP330B_ _ _	330	33	F, J, K	BP	100	
CDR32BP360B_ _ _	360	36	F, J, K	BP	100	
CDR32BP390B_ _ _	390	39	F, J, K	BP	100	
CDR32BP430B_ _ _	430	43	F, J, K	BP	100	
CDR32BP470B_ _ _	470	47	F, J, K	BP	100	
CDR32BP510B_ _ _	510	51	F, J, K	BP	100	
CDR32BP560B_ _ _	560	56	F, J, K	BP	100	
CDR32BP620B_ _ _	620	62	F, J, K	BP	100	
CDR32BP680B_ _ _	680	68	F, J, K	BP	100	
CDR32BP750B_ _ _	750	75	F, J, K	BP	100	
CDR32BP820B_ _ _	820	82	F, J, K	BP	100	
CDR32BP910B_ _ _	910	91	F, J, K	BP	100	
CDR32BP101B_ _ _	101	100	F, J, K	BP	100	
CDR32BP111B_ _ _	111	110	F, J, K	BP	100	
CDR32BP121B_ _ _	121	120	F, J, K	BP	100	
CDR32BP131B_ _ _	131	130	F, J, K	BP	100	
CDR32BP151B_ _ _	151	150	F, J, K	BP	100	
CDR32BP161B_ _ _	161	160	F, J, K	BP	100	
CDR32BP181B_ _ _	181	180	F, J, K	BP	100	
CDR32BP201B_ _ _	201	200	F, J, K	BP	100	
CDR32BP221B_ _ _	221	220	F, J, K	BP	100	
CDR32BP241B_ _ _	241	240	F, J, K	BP	100	
CDR32BP271B_ _ _	271	270	F, J, K	BP	100	
CDR32BP301B_ _ _	301	300	F, J, K	BP	100	
CDR32BP331B_ _ _	331	330	F, J, K	BP	100	
CDR32BP361B_ _ _	361	360	F, J, K	BP	100	
CDR32BP391B_ _ _	391	390	F, J, K	BP	100	
CDR32BP431B_ _ _	431	430	F, J, K	BP	100	
CDR32BP471B_ _ _	471	470	F, J, K	BP	100	
CDR32BP511B_ _ _	511	510	F, J, K	BP	100	
CDR32BP561B_ _ _	561	560	F, J, K	BP	100	
CDR32BP621B_ _ _	621	620	F, J, K	BP	100	
CDR32BP681B_ _ _	681	680	F, J, K	BP	100	
CDR32BP751B_ _ _	751	750	F, J, K	BP	100	
CDR32BP821B_ _ _	821	820	F, J, K	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR32BP						
CDR32BP911B_ _ _	911	910	F, J, K	BP	100	
CDR32BP102B_ _ _	102	1000	F, J, K	BP	100	
CDR32BP112A_ _ _	112	1100	F, J, K	BP	50	
CDR32BP122A_ _ _	122	1200	F, J, K	BP	50	
CDR32BP132A_ _ _	132	1300	F, J, K	BP	50	
CDR32BP152A_ _ _	152	1500	F, J, K	BP	50	
CDR32BP162A_ _ _	162	1600	F, J, K	BP	50	
CDR32BP182A_ _ _	182	1800	F, J, K	BP	50	
CDR32BP202A_ _ _	202	2000	F, J, K	BP	50	
CDR32BP222A_ _ _	222	2200	F, J, K	BP	50	
CDR32BX						
CDR32BX472B_ _ _	472	4700	K, M	BX	100	
CDR32BX562B_ _ _	562	5600	K, M	BX	100	
CDR32BX682B_ _ _	682	6800	K, M	BX	100	
CDR32BX822B_ _ _	822	8200	K, M	BX	100	
CDR32BX103B_ _ _	103	10 000	K, M	BX	100	
CDR32BX123B_ _ _	123	12 000	K, M	BX	100	
CDR32BX153B_ _ _	153	15 000	K, M	BX	100	
CDR32BX183A_ _ _	183	18 000	K, M	BX	50	
CDR32BX223A_ _ _	223	22 000	K, M	BX	50	
CDR32BX273A_ _ _	273	27 000	K, M	BX	50	
CDR32BX333A_ _ _	333	33 000	K, M	BX	50	
CDR32BX393A_ _ _	393	39 000	K, M	BX	50	
CDR33BP						
CDR33BP102B_ _ _	102	1000	F, J, K	BP	100	
CDR33BP112B_ _ _	112	1100	F, J, K	BP	100	
CDR33BP122B_ _ _	122	1200	F, J, K	BP	100	
CDR33BP132B_ _ _	132	1300	F, J, K	BP	100	
CDR33BP152B_ _ _	152	1500	F, J, K	BP	100	
CDR33BP162B_ _ _	162	1600	F, J, K	BP	100	
CDR33BP182B_ _ _	182	1800	F, J, K	BP	100	
CDR33BP202B_ _ _	202	2000	F, J, K	BP	100	
CDR33BP222B_ _ _	222	2200	F, J, K	BP	100	
CDR33BP242A_ _ _	242	2400	F, J, K	BP	50	
CDR33BP272A_ _ _	272	2700	F, J, K	BP	50	
CDR33BP302A_ _ _	302	3000	F, J, K	BP	50	
CDR33BP332A_ _ _	332	3300	F, J, K	BP	50	
CDR33BX						
CDR33BX153B_ _ _	153	15 000	K, M	BX	100	
CDR33BX183B_ _ _	183	18 000	K, M	BX	100	
CDR33BX223B_ _ _	223	22 000	K, M	BX	100	
CDR33BX273B_ _ _	273	27 000	K, M	BX	100	
CDR33BX393A_ _ _	393	39 000	K, M	BX	50	
CDR33BX473A_ _ _	473	47 000	K, M	BX	50	
CDR33BX563A_ _ _	563	56 000	K, M	BX	50	
CDR33BX683A_ _ _	683	68 000	K, M	BX	50	
CDR33BX823A_ _ _	823	82 000	K, M	BX	50	
CDR33BX104A_ _ _	104	100 000	K, M	BX	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR34BP						
CDR34BP222B_ _ _	222	2200	F, J, K	BP	100	
CDR34BP242B_ _ _	242	2400	F, J, K	BP	100	
CDR34BP272B_ _ _	272	2700	F, J, K	BP	100	
CDR34BP302B_ _ _	302	3000	F, J, K	BP	100	
CDR34BP332B_ _ _	332	3300	F, J, K	BP	100	
CDR34BP362B_ _ _	362	3600	F, J, K	BP	100	
CDR34BP392B_ _ _	392	3900	F, J, K	BP	100	
CDR34BP432B_ _ _	432	4300	F, J, K	BP	100	
CDR34BP472B_ _ _	472	4700	F, J, K	BP	100	
CDR34BP512A_ _ _	512	5100	F, J, K	BP	50	
CDR34BP562A_ _ _	562	5600	F, J, K	BP	50	
CDR34BP622A_ _ _	622	6200	F, J, K	BP	50	
CDR34BP682A_ _ _	682	6800	F, J, K	BP	50	
CDR34BP752A_ _ _	752	7500	F, J, K	BP	50	
CDR34BP822A_ _ _	822	8200	F, J, K	BP	50	
CDR34BP912A_ _ _	912	9100	F, J, K	BP	50	
CDR34BP103A_ _ _	103	10 000	F, J, K	BP	50	
CDR34BX						
CDR34BX273B_ _ _	273	27 000	K, M	BX	100	
CDR34BX333B_ _ _	333	33 000	K, M	BX	100	
CDR34BX393B_ _ _	393	39 000	K, M	BX	100	
CDR34BX473B_ _ _	473	47 000	K, M	BX	100	
CDR34BX563B_ _ _	563	56 000	K, M	BX	100	
CDR34BX104A_ _ _	104	100 000	K, M	BX	50	
CDR34BX124A_ _ _	124	120 000	K, M	BX	50	
CDR34BX154A_ _ _	154	150 000	K, M	BX	50	
CDR34BX184A_ _ _	184	180 000	K, M	BX	50	
CDR35BP						
CDR35BP472B_ _ _	472	4700	F, J, K	BP	100	
CDR35BP512B_ _ _	512	5100	F, J, K	BP	100	
CDR35BP562B_ _ _	562	5600	F, J, K	BP	100	
CDR35BP622B_ _ _	622	6200	F, J, K	BP	100	
CDR35BP682B_ _ _	682	6800	F, J, K	BP	100	
CDR35BP752B_ _ _	752	7500	F, J, K	BP	100	
CDR35BP822B_ _ _	822	8200	F, J, K	BP	100	
CDR35BP912B_ _ _	912	9100	F, J, K	BP	100	
CDR35BP103B_ _ _	103	10 000	F, J, K	BP	100	
CDR35BP113A_ _ _	113	11 000	F, J, K	BP	50	
CDR35BP123A_ _ _	123	12 000	F, J, K	BP	50	
CDR35BP133A_ _ _	133	13 000	F, J, K	BP	50	
CDR35BP153A_ _ _	153	15 000	F, J, K	BP	50	
CDR35BP163A_ _ _	163	16 000	F, J, K	BP	50	
CDR35BP183A_ _ _	183	18 000	F, J, K	BP	50	
CDR35BP203A_ _ _	203	20 000	F, J, K	BP	50	
CDR35BP223A_ _ _	223	22 000	F, J, K	BP	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR35BX						
CDR35BX563B_ _ _	563	56 000	K, M	BX	100	
CDR35BX683B_ _ _	683	68 000	K, M	BX	100	
CDR35BX823B_ _ _	823	82 000	K, M	BX	100	
CDR35BX104B_ _ _	104	100 000	K, M	BX	100	
CDR35BX124B_ _ _	124	120 000	K, M	BX	100	
CDR35BX154B_ _ _	154	150 000	K, M	BX	100	
CDR35BX184A_ _ _	184	180 000	K, M	BX	50	
CDR35BX224A_ _ _	224	220 000	K, M	BX	50	
CDR35BX274A_ _ _	274	270 000	K, M	BX	50	
CDR35BX334A_ _ _	334	330 000	K, M	BX	50	
CDR35BX394A_ _ _	394	390 000	K, M	BX	50	
CDR35BX474A_ _ _	474	470 000	K, M	BX	50	
CDR37BP						
CDR37BP1R0X_ _ _	1R0	1.0	C, D	BP	10	
CDR37BP1R2X_ _ _	1R2	1.2	C, D	BP	10	
CDR37BP1R5X_ _ _	1R5	1.5	C, D	BP	10	
CDR37BP1R8X_ _ _	1R8	1.8	C, D	BP	10	
CDR37BP2R2X_ _ _	2R2	2.2	C, D	BP	10	
CDR37BP2R4X_ _ _	2R4	2.4	C, D	BP	10	
CDR37BP2R7X_ _ _	2R7	2.7	C, D	BP	10	
CDR37BP3R0X_ _ _	3R0	3.0	C, D	BP	10	
CDR37BP3R3X_ _ _	3R3	3.3	C, D	BP	10	
CDR37BP3R6X_ _ _	3R6	3.6	C, D	BP	10	
CDR37BP3R9X_ _ _	3R9	3.9	C, D	BP	10	
CDR37BP4R7X_ _ _	4R7	4.7	C, D	BP	10	
CDR37BP5R1X_ _ _	5R1	5.1	C, D	BP	10	
CDR37BP5R6X_ _ _	5R6	5.6	C, D	BP	10	
CDR37BP6R2X_ _ _	6R2	6.2	C, D	BP	10	
CDR37BP6R8X_ _ _	6R8	6.8	C, D	BP	10	
CDR37BP7R5X_ _ _	7R5	7.5	C, D	BP	10	
CDR37BP8R2X_ _ _	8R2	8.2	C, D	BP	10	
CDR37BP9R1X_ _ _	9R1	9.1	C, D	BP	10	
CDR37BP100X_ _ _	100	10	F, G, J	BP	10	
CDR37BP110X_ _ _	110	11	F, G, J	BP	10	
CDR37BP120X_ _ _	120	12	F, G, J	BP	10	
CDR37BP130X_ _ _	130	13	F, G, J	BP	10	
CDR37BP150X_ _ _	150	15	F, G, J	BP	10	
CDR37BP160X_ _ _	160	16	F, G, J	BP	10	
CDR37BP180X_ _ _	180	18	F, G, J	BP	10	
CDR37BP200X_ _ _	200	20	F, G, J	BP	10	
CDR37BP220X_ _ _	220	22	F, G, J	BP	10	
CDR37BP240X_ _ _	240	24	F, G, J	BP	10	
CDR37BP270X_ _ _	270	27	F, G, J	BP	10	
CDR37BP300X_ _ _	300	30	F, G, J	BP	10	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BP						
CDR37BP330X_	330	33	F, G, J	BP	10	
CDR37BP360X_	360	36	F, G, J	BP	10	
CDR37BP390X_	390	39	F, G, J	BP	10	
CDR37BP430X_	430	43	F, G, J	BP	10	
CDR37BP470X_	470	47	F, G, J	BP	10	
CDR37BP510X_	510	51	F, G, J	BP	10	
CDR37BP560X_	560	56	F, G, J	BP	10	
CDR37BP620X_	620	62	F, G, J	BP	10	
CDR37BP680X_	680	68	F, G, J	BP	10	
CDR37BP750X_	750	75	F, G, J	BP	10	
CDR37BP820X_	820	82	F, G, J	BP	10	
CDR37BP910X_	910	91	F, G, J	BP	10	
CDR37BP101X_	101	100	F, G, J	BP	10	
CDR37BP121X_	121	120	F, G, J	BP	10	
CDR37BP151X_	151	150	F, G, J	BP	10	
CDR37BP1R0Y_	1R0	1.0	C, D	BP	16	
CDR37BP1R2Y_	1R2	1.2	C, D	BP	16	
CDR37BP1R5Y_	1R5	1.5	C, D	BP	16	
CDR37BP1R8Y_	1R8	1.8	C, D	BP	16	
CDR37BP2R2Y_	2R2	2.2	C, D	BP	16	
CDR37BP2R4Y_	2R4	2.4	C, D	BP	16	
CDR37BP2R7Y_	2R7	2.7	C, D	BP	16	
CDR37BP3R0Y_	3R0	3.0	C, D	BP	16	
CDR37BP3R3Y_	3R3	3.3	C, D	BP	16	
CDR37BP3R6Y_	3R6	3.6	C, D	BP	16	
CDR37BP3R9Y_	3R9	3.9	C, D	BP	16	
CDR37BP4R7Y_	4R7	4.7	C, D	BP	16	
CDR37BP5R1Y_	5R1	5.1	C, D	BP	16	
CDR37BP5R6Y_	5R6	5.6	C, D	BP	16	
CDR37BP6R2Y_	6R2	6.2	C, D	BP	16	
CDR37BP6R8Y_	6R8	6.8	C, D	BP	16	
CDR37BP7R5Y_	7R5	7.5	C, D	BP	16	
CDR37BP8R2Y_	8R2	8.2	C, D	BP	16	
CDR37BP9R1Y_	9R1	9.1	C, D	BP	16	
CDR37BP100Y_	100	10	F, G, J	BP	16	
CDR37BP110Y_	110	11	F, G, J	BP	16	
CDR37BP120Y_	120	12	F, G, J	BP	16	
CDR37BP130Y_	130	13	F, G, J	BP	16	
CDR37BP150Y_	150	15	F, G, J	BP	16	
CDR37BP160Y_	160	16	F, G, J	BP	16	
CDR37BP180Y_	180	18	F, G, J	BP	16	
CDR37BP200Y_	200	20	F, G, J	BP	16	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BP						
CDR37BP220Y_	220	22	F, G, J	BP	16	
CDR37BP240Y_	240	24	F, G, J	BP	16	
CDR37BP270Y_	270	27	F, G, J	BP	16	
CDR37BP300Y_	300	30	F, G, J	BP	16	
CDR37BP330Y_	330	33	F, G, J	BP	16	
CDR37BP360Y_	360	36	F, G, J	BP	16	
CDR37BP390Y_	390	39	F, G, J	BP	16	
CDR37BP430Y_	430	43	F, G, J	BP	16	
CDR37BP470Y_	470	47	F, G, J	BP	16	
CDR37BP510Y_	510	51	F, G, J	BP	16	
CDR37BP560Y_	560	56	F, G, J	BP	16	
CDR37BP620Y_	620	62	F, G, J	BP	16	
CDR37BP680Y_	680	68	F, G, J	BP	16	
CDR37BP750Y_	750	75	F, G, J	BP	16	
CDR37BP820Y_	820	82	F, G, J	BP	16	
CDR37BP910Y_	910	91	F, G, J	BP	16	
CDR37BP101Y_	101	100	F, G, J	BP	16	
CDR37BP121Y_	121	120	F, G, J	BP	16	
CDR37BP151Y_	151	150	F, G, J	BP	16	
CDR37BP1R0Z_	1R0	1.0	C, D	BP	25	
CDR37BP1R2Z_	1R2	1.2	C, D	BP	25	
CDR37BP1R5Z_	1R5	1.5	C, D	BP	25	
CDR37BP1R8Z_	1R8	1.8	C, D	BP	25	
CDR37BP2R2Z_	2R2	2.2	C, D	BP	25	
CDR37BP2R4Z_	2R4	2.4	C, D	BP	25	
CDR37BP2R7Z_	2R7	2.7	C, D	BP	25	
CDR37BP3R0Z_	3R0	3.0	C, D	BP	25	
CDR37BP3R3Z_	3R3	3.3	C, D	BP	25	
CDR37BP3R6Z_	3R6	3.6	C, D	BP	25	
CDR37BP3R9Z_	3R9	3.9	C, D	BP	25	
CDR37BP4R7Z_	4R7	4.7	C, D	BP	25	
CDR37BP5R1Z_	5R1	5.1	C, D	BP	25	
CDR37BP5R6Z_	5R6	5.6	C, D	BP	25	
CDR37BP6R2Z_	6R2	6.2	C, D	BP	25	
CDR37BP6R8Z_	6R8	6.8	C, D	BP	25	
CDR37BP7R5Z_	7R5	7.5	C, D	BP	25	
CDR37BP8R2Z_	8R2	8.2	C, D	BP	25	
CDR37BP9R1Z_	9R1	9.1	C, D	BP	25	
CDR37BP100Z_	100	10	F, G, J	BP	25	
CDR37BP110Z_	110	11	F, G, J	BP	25	
CDR37BP120Z_	120	12	F, G, J	BP	25	
CDR37BP130Z_	130	13	F, G, J	BP	25	
CDR37BP150Z_	150	15	F, G, J	BP	25	
CDR37BP160Z_	160	16	F, G, J	BP	25	
CDR37BP180Z_	180	18	F, G, J	BP	25	
CDR37BP200Z_	200	20	F, G, J	BP	25	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BP						
CDR37BP220Z_ _ _	220	22	F, G, J	BP	25	
CDR37BP240Z_ _ _	240	24	F, G, J	BP	25	
CDR37BP270Z_ _ _	270	27	F, G, J	BP	25	
CDR37BP300Z_ _ _	300	30	F, G, J	BP	25	
CDR37BP330Z_ _ _	330	33	F, G, J	BP	25	
CDR37BP360Z_ _ _	360	36	F, G, J	BP	25	
CDR37BP390Z_ _ _	390	39	F, G, J	BP	25	
CDR37BP430Z_ _ _	430	43	F, G, J	BP	25	
CDR37BP470Z_ _ _	470	47	F, G, J	BP	25	
CDR37BP510Z_ _ _	510	51	F, G, J	BP	25	
CDR37BP560Z_ _ _	560	56	F, G, J	BP	25	
CDR37BP620Z_ _ _	620	62	F, G, J	BP	25	
CDR37BP680Z_ _ _	680	68	F, G, J	BP	25	
CDR37BP750Z_ _ _	750	75	F, G, J	BP	25	
CDR37BP820Z_ _ _	820	82	F, G, J	BP	25	
CDR37BP910Z_ _ _	910	91	F, G, J	BP	25	
CDR37BP101Z_ _ _	101	100	F, G, J	BP	25	
CDR37BP121Z_ _ _	121	120	F, G, J	BP	25	
CDR37BP151Z_ _ _	151	150	F, G, J	BP	25	
CDR37BP1R0A_ _ _	1R0	1.0	C, D	BP	50	
CDR37BP1R2A_ _ _	1R2	1.2	C, D	BP	50	
CDR37BP1R5A_ _ _	1R5	1.5	C, D	BP	50	
CDR37BP1R8A_ _ _	1R8	1.8	C, D	BP	50	
CDR37BP2R2A_ _ _	2R2	2.2	C, D	BP	50	
CDR37BP2R4A_ _ _	2R4	2.4	C, D	BP	50	
CDR37BP2R7A_ _ _	2R7	2.7	C, D	BP	50	
CDR37BP3R0A_ _ _	3R0	3.0	C, D	BP	50	
CDR37BP3R3A_ _ _	3R3	3.3	C, D	BP	50	
CDR37BP3R6A_ _ _	3R6	3.6	C, D	BP	50	
CDR37BP3R9A_ _ _	3R9	3.9	C, D	BP	50	
CDR37BP4R7A_ _ _	4R7	4.7	C, D	BP	50	
CDR37BP5R1A_ _ _	5R1	5.1	C, D	BP	50	
CDR37BP5R6A_ _ _	5R6	5.6	C, D	BP	50	
CDR37BP6R2A_ _ _	6R2	6.2	C, D	BP	50	
CDR37BP6R8A_ _ _	6R8	6.8	C, D	BP	50	
CDR37BP7R5A_ _ _	7R5	7.5	C, D	BP	50	
CDR37BP8R2A_ _ _	8R2	8.2	C, D	BP	50	
CDR37BP9R1A_ _ _	9R1	9.1	C, D	BP	50	
CDR37BP100A_ _ _	100	10	F, G, J	BP	50	
CDR37BP110A_ _ _	110	11	F, G, J	BP	50	
CDR37BP120A_ _ _	120	12	F, G, J	BP	50	
CDR37BP130A_ _ _	130	13	F, G, J	BP	50	
CDR37BP150A_ _ _	150	15	F, G, J	BP	50	
CDR37BP160A_ _ _	160	16	F, G, J	BP	50	
CDR37BP180A_ _ _	180	18	F, G, J	BP	50	
CDR37BP200A_ _ _	200	20	F, G, J	BP	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BP						
CDR37BP220A_ _ _	220	22	F, G, J	BP	50	
CDR37BP240A_ _ _	240	24	F, G, J	BP	50	
CDR37BP270A_ _ _	270	27	F, G, J	BP	50	
CDR37BP300A_ _ _	300	30	F, G, J	BP	50	
CDR37BP330A_ _ _	330	33	F, G, J	BP	50	
CDR37BP360A_ _ _	360	36	F, G, J	BP	50	
CDR37BP390A_ _ _	390	39	F, G, J	BP	50	
CDR37BP430A_ _ _	430	43	F, G, J	BP	50	
CDR37BP470A_ _ _	470	47	F, G, J	BP	50	
CDR37BP510A_ _ _	510	51	F, G, J	BP	50	
CDR37BP560A_ _ _	560	56	F, G, J	BP	50	
CDR37BP620A_ _ _	620	62	F, G, J	BP	50	
CDR37BP680A_ _ _	680	68	F, G, J	BP	50	
CDR37BP750A_ _ _	750	75	F, G, J	BP	50	
CDR37BP820A_ _ _	820	82	F, G, J	BP	50	
CDR37BP910A_ _ _	910	91	F, G, J	BP	50	
CDR37BP101A_ _ _	101	100	F, G, J	BP	50	
CDR37BP121A_ _ _	121	120	F, G, J	BP	50	
CDR37BP151A_ _ _	151	150	F, G, J	BP	50	
CDR37BP1R0B_ _ _	1R0	1.0	C, D	BP	100	
CDR37BP1R2B_ _ _	1R2	1.2	C, D	BP	100	
CDR37BP1R5B_ _ _	1R5	1.5	C, D	BP	100	
CDR37BP1R8B_ _ _	1R8	1.8	C, D	BP	100	
CDR37BP2R2B_ _ _	2R2	2.2	C, D	BP	100	
CDR37BP2R4B_ _ _	2R4	2.4	C, D	BP	100	
CDR37BP2R7B_ _ _	2R7	2.7	C, D	BP	100	
CDR37BP3R0B_ _ _	3R0	3.0	C, D	BP	100	
CDR37BP3R3B_ _ _	3R3	3.3	C, D	BP	100	
CDR37BP3R6B_ _ _	3R6	3.6	C, D	BP	100	
CDR37BP3R9B_ _ _	3R9	3.9	C, D	BP	100	
CDR37BP4R7B_ _ _	4R7	4.7	C, D	BP	100	
CDR37BP5R1B_ _ _	5R1	5.1	C, D	BP	100	
CDR37BP5R6B_ _ _	5R6	5.6	C, D	BP	100	
CDR37BP6R2B_ _ _	6R2	6.2	C, D	BP	100	
CDR37BP6R8B_ _ _	6R8	6.8	C, D	BP	100	
CDR37BP7R5B_ _ _	7R5	7.5	C, D	BP	100	
CDR37BP8R2B_ _ _	8R2	8.2	C, D	BP	100	
CDR37BP9R1B_ _ _	9R1	9.1	C, D	BP	100	
CDR37BP100B_ _ _	100	10	F, G, J	BP	100	
CDR37BP110B_ _ _	110	11	F, G, J	BP	100	
CDR37BP120B_ _ _	120	12	F, G, J	BP	100	
CDR37BP130B_ _ _	130	13	F, G, J	BP	100	
CDR37BP150B_ _ _	150	15	F, G, J	BP	100	
CDR37BP160B_ _ _	160	16	F, G, J	BP	100	
CDR37BP180B_ _ _	180	18	F, G, J	BP	100	
CDR37BP200B_ _ _	200	20	F, G, J	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BP						
CDR37BP220B_	220	22	F, G, J	BP	100	
CDR37BP240B_	240	24	F, G, J	BP	100	
CDR37BP270B_	270	27	F, G, J	BP	100	
CDR37BP300B_	300	30	F, G, J	BP	100	
CDR37BP330B_	330	33	F, G, J	BP	100	
CDR37BP360B_	360	36	F, G, J	BP	100	
CDR37BP390B_	390	39	F, G, J	BP	100	
CDR37BP430B_	430	43	F, G, J	BP	100	
CDR37BP470B_	470	47	F, G, J	BP	100	
CDR37BP510B_	510	51	F, G, J	BP	100	
CDR37BP560B_	560	56	F, G, J	BP	100	
CDR37BP620B_	620	62	F, G, J	BP	100	
CDR37BP680B_	680	68	F, G, J	BP	100	
CDR37BP750B_	750	75	F, G, J	BP	100	
CDR37BP820B_	820	82	F, G, J	BP	100	
CDR37BP910B_	910	91	F, G, J	BP	100	
CDR37BP101B_	101	100	F, G, J	BP	100	
CDR37BP121B_	121	120	F, G, J	BP	100	
CDR37BP151B_	151	150	F, G, J	BP	100	
CD37BX						
CDR37BX101W_	101	100	J, K, M	BX	6.3	
CDR37BX121W_	121	120	J, K, M	BX	6.3	
CDR37BX151W_	151	150	J, K, M	BX	6.3	
CDR37BX181W_	181	180	J, K, M	BX	6.3	
CDR37BX221W_	221	220	J, K, M	BX	6.3	
CDR37BX271W_	271	270	J, K, M	BX	6.3	
CDR37BX331W_	331	330	J, K, M	BX	6.3	
CDR37BX391W_	391	390	J, K, M	BX	6.3	
CDR37BX471W_	471	470	J, K, M	BX	6.3	
CDR37BX561W_	561	560	J, K, M	BX	6.3	
CDR37BX681W_	681	680	J, K, M	BX	6.3	
CDR37BX821W_	821	820	J, K, M	BX	6.3	
CDR37BX102W_	102	1000	J, K, M	BX	6.3	
CDR37BX122W_	122	1200	J, K, M	BX	6.3	
CDR37BX152W_	152	1500	J, K, M	BX	6.3	
CDR37BX182W_	182	1800	J, K, M	BX	6.3	
CDR37BX222W_	222	2200	J, K, M	BX	6.3	
CDR37BX272W_	272	2700	J, K, M	BX	6.3	
CDR37BX332W_	332	3300	J, K, M	BX	6.3	
CDR37BX392W_	392	3900	J, K, M	BX	6.3	
CDR37BX472W_	472	4700	J, K, M	BX	6.3	
CDR37BX562W_	562	5600	J, K, M	BX	6.3	
CDR37BX682W_	682	6800	J, K, M	BX	6.3	
CDR37BX822W_	822	8200	J, K, M	BX	6.3	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CD37BX						
CDR37BX101X_ _ _	101	100	J, K, M	BX	10	
CDR37BX121X_ _ _	121	120	J, K, M	BX	10	
CDR37BX151X_ _ _	151	150	J, K, M	BX	10	
CDR37BX181X_ _ _	181	180	J, K, M	BX	10	
CDR37BX221X_ _ _	221	220	J, K, M	BX	10	
CDR37BX271X_ _ _	271	270	J, K, M	BX	10	
CDR37BX331X_ _ _	331	330	J, K, M	BX	10	
CDR37BX391X_ _ _	391	390	J, K, M	BX	10	
CDR37BX471X_ _ _	471	470	J, K, M	BX	10	
CDR37BX561X_ _ _	561	560	J, K, M	BX	10	
CDR37BX681X_ _ _	681	680	J, K, M	BX	10	
CDR37BX821X_ _ _	821	820	J, K, M	BX	10	
CDR37BX102X_ _ _	102	1000	J, K, M	BX	10	
CDR37BX122X_ _ _	122	1200	J, K, M	BX	10	
CDR37BX152X_ _ _	152	1500	J, K, M	BX	10	
CDR37BX182X_ _ _	182	1800	J, K, M	BX	10	
CDR37BX222X_ _ _	222	2200	J, K, M	BX	10	
CDR37BX272X_ _ _	272	2700	J, K, M	BX	10	
CDR37BX332X_ _ _	332	3300	J, K, M	BX	10	
CDR37BX392X_ _ _	392	3900	J, K, M	BX	10	
CDR37BX472X_ _ _	472	4700	J, K, M	BX	10	
CDR37BX562X_ _ _	562	5600	J, K, M	BX	10	
CDR37BX682X_ _ _	682	6800	J, K, M	BX	10	
CDR37BX822X_ _ _	822	8200	J, K, M	BX	10	
CDR37BX101Y_ _ _	101	100	J, K, M	BX	16	
CDR37BX121Y_ _ _	121	120	J, K, M	BX	16	
CDR37BX151Y_ _ _	151	150	J, K, M	BX	16	
CDR37BX181Y_ _ _	181	180	J, K, M	BX	16	
CDR37BX221Y_ _ _	221	220	J, K, M	BX	16	
CDR37BX271Y_ _ _	271	270	J, K, M	BX	16	
CDR37BX331Y_ _ _	331	330	J, K, M	BX	16	
CDR37BX391Y_ _ _	391	390	J, K, M	BX	16	
CDR37BX471Y_ _ _	471	470	J, K, M	BX	16	
CDR37BX561Y_ _ _	561	560	J, K, M	BX	16	
CDR37BX681Y_ _ _	681	680	J, K, M	BX	16	
CDR37BX821Y_ _ _	821	820	J, K, M	BX	16	
CDR37BX102Y_ _ _	102	1000	J, K, M	BX	16	
CDR37BX122Y_ _ _	122	1200	J, K, M	BX	16	
CDR37BX152Y_ _ _	152	1500	J, K, M	BX	16	
CDR37BX182Y_ _ _	182	1800	J, K, M	BX	16	
CDR37BX222Y_ _ _	222	2200	J, K, M	BX	16	
CDR37BX272Y_ _ _	272	2700	J, K, M	BX	16	
CDR37BX332Y_ _ _	332	3300	J, K, M	BX	16	
CDR37BX392Y_ _ _	392	3900	J, K, M	BX	16	
CDR37BX472Y_ _ _	472	4700	J, K, M	BX	16	
CDR37BX562Y_ _ _	562	5600	J, K, M	BX	16	
CDR37BX682Y_ _ _	682	6800	J, K, M	BX	16	
CDR37BX822Y_ _ _	822	8200	J, K, M	BX	16	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BX						
CDR37BX101Z_ _ _	101	100	J, K, M	BX	25	
CDR37BX121Z_ _ _	121	120	J, K, M	BX	25	
CDR37BX151Z_ _ _	151	150	J, K, M	BX	25	
CDR37BX181Z_ _ _	181	180	J, K, M	BX	25	
CDR37BX221Z_ _ _	221	220	J, K, M	BX	25	
CDR37BX271Z_ _ _	271	270	J, K, M	BX	25	
CDR37BX331Z_ _ _	331	330	J, K, M	BX	25	
CDR37BX391Z_ _ _	391	390	J, K, M	BX	25	
CDR37BX471Z_ _ _	471	470	J, K, M	BX	25	
CDR37BX561Z_ _ _	561	560	J, K, M	BX	25	
CDR37BX681Z_ _ _	681	680	J, K, M	BX	25	
CDR37BX821Z_ _ _	821	820	J, K, M	BX	25	
CDR37BX102Z_ _ _	102	1000	J, K, M	BX	25	
CDR37BX122Z_ _ _	122	1200	J, K, M	BX	25	
CDR37BX152Z_ _ _	152	1500	J, K, M	BX	25	
CDR37BX182Z_ _ _	182	1800	J, K, M	BX	25	
CDR37BX222Z_ _ _	222	2200	J, K, M	BX	25	
CDR37BX272Z_ _ _	272	2700	J, K, M	BX	25	
CDR37BX332Z_ _ _	332	3300	J, K, M	BX	25	
CDR37BX392Z_ _ _	392	3900	J, K, M	BX	25	
CDR37BX101A_ _ _	101	100	J, K, M	BX	50	
CDR37BX121A_ _ _	121	120	J, K, M	BX	50	
CDR37BX151A_ _ _	151	150	J, K, M	BX	50	
CDR37BX181A_ _ _	181	180	J, K, M	BX	50	
CDR37BX221A_ _ _	221	220	J, K, M	BX	50	
CDR37BX271A_ _ _	271	270	J, K, M	BX	50	
CDR37BX331A_ _ _	331	330	J, K, M	BX	50	
CDR37BX391A_ _ _	391	390	J, K, M	BX	50	
CDR37BX471A_ _ _	471	470	J, K, M	BX	50	
CDR37BX561A_ _ _	561	560	J, K, M	BX	50	
CDR37BX681A_ _ _	681	680	J, K, M	BX	50	
CDR37BX821A_ _ _	821	820	J, K, M	BX	50	
CDR37BX102A_ _ _	102	1000	J, K, M	BX	50	
CDR37BX122A_ _ _	122	1200	J, K, M	BX	50	
CDR37BX152A_ _ _	152	1500	J, K, M	BX	50	
CDR37BR						
CDR37BR101W_ _ _	101	100	J, K, M	BR	6.3	
CDR37BR121W_ _ _	121	120	J, K, M	BR	6.3	
CDR37BR151W_ _ _	151	150	J, K, M	BR	6.3	
CDR37BR181W_ _ _	181	180	J, K, M	BR	6.3	
CDR37BR221W_ _ _	221	220	J, K, M	BR	6.3	
CDR37BR271W_ _ _	271	270	J, K, M	BR	6.3	
CDR37BR331W_ _ _	331	330	J, K, M	BR	6.3	
CDR37BR391W_ _ _	391	390	J, K, M	BR	6.3	
CDR37BR471W_ _ _	471	470	J, K, M	BR	6.3	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BR						
CDR37BR561W_ _ _	561	560	J, K, M	BR	6.3	
CDR37BR681W_ _ _	681	680	J, K, M	BR	6.3	
CDR37BR821W_ _ _	821	820	J, K, M	BR	6.3	
CDR37BR102W_ _ _	102	1000	J, K, M	BR	6.3	
CDR37BR122W_ _ _	122	1200	J, K, M	BR	6.3	
CDR37BR152W_ _ _	152	1500	J, K, M	BR	6.3	
CDR37BR182W_ _ _	182	1800	J, K, M	BR	6.3	
CDR37BR222W_ _ _	222	2200	J, K, M	BR	6.3	
CDR37BR272W_ _ _	272	2700	J, K, M	BR	6.3	
CDR37BR332W_ _ _	332	3300	J, K, M	BR	6.3	
CDR37BR392W_ _ _	392	3900	J, K, M	BR	6.3	
CDR37BR472W_ _ _	472	4700	J, K, M	BR	6.3	
CDR37BR562W_ _ _	562	5600	J, K, M	BR	6.3	
CDR37BR682W_ _ _	682	6800	J, K, M	BR	6.3	
CDR37BR822W_ _ _	822	8200	J, K, M	BR	6.3	
CDR37BR103W_ _ _	103	10 000	J, K, M	BR	6.3	
CDR37BR101X_ _ _	101	100	J, K, M	BR	10	
CDR37BR121X_ _ _	121	120	J, K, M	BR	10	
CDR37BR151X_ _ _	151	150	J, K, M	BR	10	
CDR37BR181X_ _ _	181	180	J, K, M	BR	10	
CDR37BR221X_ _ _	221	220	J, K, M	BR	10	
CDR37BR271X_ _ _	271	270	J, K, M	BR	10	
CDR37BR331X_ _ _	331	330	J, K, M	BR	10	
CDR37BR391X_ _ _	391	390	J, K, M	BR	10	
CDR37BR471X_ _ _	471	470	J, K, M	BR	10	
CDR37BR561X_ _ _	561	560	J, K, M	BR	10	
CDR37BR681X_ _ _	681	680	J, K, M	BR	10	
CDR37BR821X_ _ _	821	820	J, K, M	BR	10	
CDR37BR102X_ _ _	102	1000	J, K, M	BR	10	
CDR37BR122X_ _ _	122	1200	J, K, M	BR	10	
CDR37BR152X_ _ _	152	1500	J, K, M	BR	10	
CDR37BR182X_ _ _	182	1800	J, K, M	BR	10	
CDR37BR222X_ _ _	222	2200	J, K, M	BR	10	
CDR37BR272X_ _ _	272	2700	J, K, M	BR	10	
CDR37BR332X_ _ _	332	3300	J, K, M	BR	10	
CDR37BR392X_ _ _	392	3900	J, K, M	BR	10	
CDR37BR472X_ _ _	472	4700	J, K, M	BR	10	
CDR37BR562X_ _ _	562	5600	J, K, M	BR	10	
CDR37BR682X_ _ _	682	6800	J, K, M	BR	10	
CDR37BR822X_ _ _	822	8200	J, K, M	BR	10	
CDR37BR103X_ _ _	103	10 000	J, K, M	BR	10	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BR						
CDR37BR101Y_	101	100	J, K, M	BR	16	
CDR37BR121Y_	121	120	J, K, M	BR	16	
CDR37BR151Y_	151	150	J, K, M	BR	16	
CDR37BR181Y_	181	180	J, K, M	BR	16	
CDR37BR221Y_	221	220	J, K, M	BR	16	
CDR37BR271Y_	271	270	J, K, M	BR	16	
CDR37BR331Y_	331	330	J, K, M	BR	16	
CDR37BR391Y_	391	390	J, K, M	BR	16	
CDR37BR471Y_	471	470	J, K, M	BR	16	
CDR37BR561Y_	561	560	J, K, M	BR	16	
CDR37BR681Y_	681	680	J, K, M	BR	16	
CDR37BR821Y_	821	820	J, K, M	BR	16	
CDR37BR102Y_	102	1000	J, K, M	BR	16	
CDR37BR122Y_	122	1200	J, K, M	BR	16	
CDR37BR152Y_	152	1500	J, K, M	BR	16	
CDR37BR182Y_	182	1800	J, K, M	BR	16	
CDR37BR222Y_	222	2200	J, K, M	BR	16	
CDR37BR272Y_	272	2700	J, K, M	BR	16	
CDR37BR332Y_	332	3300	J, K, M	BR	16	
CDR37BR392Y_	392	3900	J, K, M	BR	16	
CDR37BR472Y_	472	4700	J, K, M	BR	16	
CDR37BR562Y_	562	5600	J, K, M	BR	16	
CDR37BR682Y_	682	6800	J, K, M	BR	16	
CDR37BR822Y_	822	8200	J, K, M	BR	16	
CDR37BR103Y_	103	10 000	J, K, M	BR	16	
CDR37BR101Z_	101	100	J, K, M	BR	25	
CDR37BR121Z_	121	120	J, K, M	BR	25	
CDR37BR151Z_	151	150	J, K, M	BR	25	
CDR37BR181Z_	181	180	J, K, M	BR	25	
CDR37BR221Z_	221	220	J, K, M	BR	25	
CDR37BR271Z_	271	270	J, K, M	BR	25	
CDR37BR331Z_	331	330	J, K, M	BR	25	
CDR37BR391Z_	391	390	J, K, M	BR	25	
CDR37BR471Z_	471	470	J, K, M	BR	25	
CDR37BR561Z_	561	560	J, K, M	BR	25	
CDR37BR681Z_	681	680	J, K, M	BR	25	
CDR37BR821Z_	821	820	J, K, M	BR	25	
CDR37BR102Z_	102	1000	J, K, M	BR	25	
CDR37BR122Z_	122	1200	J, K, M	BR	25	
CDR37BR152Z_	152	1500	J, K, M	BR	25	
CDR37BR182Z_	182	1800	J, K, M	BR	25	
CDR37BR222Z_	222	2200	J, K, M	BR	25	
CDR37BR272Z_	272	2700	J, K, M	BR	25	
CDR37BR332Z_	332	3300	J, K, M	BR	25	
CDR37BR392Z_	392	3900	J, K, M	BR	25	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR37BR						
CDR37BR101A_ _ _	101	100	J, K, M	BR	50	
CDR37BR121A_ _ _	121	120	J, K, M	BR	50	
CDR37BR151A_ _ _	151	150	J, K, M	BR	50	
CDR37BR181A_ _ _	181	180	J, K, M	BR	50	
CDR37BR221A_ _ _	221	220	J, K, M	BR	50	
CDR37BR271A_ _ _	271	270	J, K, M	BR	50	
CDR37BR331A_ _ _	331	330	J, K, M	BR	50	
CDR37BR391A_ _ _	391	390	J, K, M	BR	50	
CDR37BR471A_ _ _	471	470	J, K, M	BR	50	
CDR37BR561A_ _ _	561	560	J, K, M	BR	50	
CDR37BR681A_ _ _	681	680	J, K, M	BR	50	
CDR37BR821A_ _ _	821	820	J, K, M	BR	50	
CDR37BR102A_ _ _	102	1000	J, K, M	BR	50	
CDR37BR122A_ _ _	122	1200	J, K, M	BR	50	
CDR37BR152A_ _ _	152	1500	J, K, M	BR	50	
CDR37BR182A_ _ _	182	1800	J, K, M	BR	50	
CDR37BR222A_ _ _	222	2200	J, K, M	BR	50	
CDR37BR272A_ _ _	272	2700	J, K, M	BR	50	
CDR37BR332A_ _ _	332	3300	J, K, M	BR	50	
CDR37BR392A_ _ _	392	3900	J, K, M	BR	50	
CDR36BP						
CDR36BP1R0X_ _ _	1R0	1.0	C, D	BP	10	
CDR36BP1R2X_ _ _	1R2	1.2	C, D	BP	10	
CDR36BP1R5X_ _ _	1R5	1.5	C, D	BP	10	
CDR36BP1R8X_ _ _	1R8	1.8	C, D	BP	10	
CDR36BP2R2X_ _ _	2R2	2.2	C, D	BP	10	
CDR36BP2R4X_ _ _	2R4	2.4	C, D	BP	10	
CDR36BP2R7X_ _ _	2R7	2.7	C, D	BP	10	
CDR36BP3R0X_ _ _	3R0	3.0	C, D	BP	10	
CDR36BP3R3X_ _ _	3R3	3.3	C, D	BP	10	
CDR36BP3R6X_ _ _	3R6	3.6	C, D	BP	10	
CDR36BP3R9X_ _ _	3R9	3.9	C, D	BP	10	
CDR36BP4R7X_ _ _	4R7	4.7	C, D	BP	10	
CDR36BP5R1X_ _ _	5R1	5.1	C, D	BP	10	
CDR36BP5R6X_ _ _	5R6	5.6	C, D	BP	10	
CDR36BP6R2X_ _ _	6R2	6.2	C, D	BP	10	
CDR36BP6R8X_ _ _	6R8	6.8	C, D	BP	10	
CDR36BP7R5X_ _ _	7R5	7.5	C, D	BP	10	
CDR36BP8R2X_ _ _	8R2	8.2	C, D	BP	10	
CDR36BP9R1X_ _ _	9R1	9.1	C, D	BP	10	
CDR36BP100X_ _ _	100	10	F, G, J	BP	10	
CDR36BP110X_ _ _	110	11	F, G, J	BP	10	
CDR36BP120X_ _ _	120	12	F, G, J	BP	10	
CDR36BP130X_ _ _	130	13	F, G, J	BP	10	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP150X_	150	15	F, G, J	BP	10	
CDR36BP160X_	160	16	F, G, J	BP	10	
CDR36BP180X_	180	18	F, G, J	BP	10	
CDR36BP200X_	200	20	F, G, J	BP	10	
CDR36BP220X_	220	22	F, G, J	BP	10	
CDR36BP240X_	240	24	F, G, J	BP	10	
CDR36BP270X_	270	27	F, G, J	BP	10	
CDR36BP300X_	300	30	F, G, J	BP	10	
CDR36BP330X_	330	33	F, G, J	BP	10	
CDR36BP360X_	360	36	F, G, J	BP	10	
CDR36BP390X_	390	39	F, G, J	BP	10	
CDR36BP430X_	430	43	F, G, J	BP	10	
CDR36BP470X_	470	47	F, G, J	BP	10	
CDR36BP510X_	510	51	F, G, J	BP	10	
CDR36BP560X_	560	56	F, G, J	BP	10	
CDR36BP620X_	620	62	F, G, J	BP	10	
CDR36BP680X_	680	68	F, G, J	BP	10	
CDR36BP750X_	750	75	F, G, J	BP	10	
CDR36BP820X_	820	82	F, G, J	BP	10	
CDR36BP910X_	910	91	F, G, J	BP	10	
CDR36BP101X_	101	100	F, G, J	BP	10	
CDR36BP121X_	121	120	F, G, J	BP	10	
CDR36BP151X_	151	150	F, G, J	BP	10	
CDR36BP181X_	181	180	F, G, J	BP	10	
CDR36BP221X_	221	220	F, G, J	BP	10	
CDR36BP271X_	271	270	F, G, J	BP	10	
CDR36BP331X_	331	330	F, G, J	BP	10	
CDR36BP391X_	391	390	F, G, J	BP	10	
CDR36BP471X_	471	470	F, G, J	BP	10	
CDR36BP561X_	561	560	F, G, J	BP	10	
CDR36BP681X_	681	680	F, G, J	BP	10	
CDR36BP821X_	821	820	F, G, J	BP	10	
CDR36BP102X_	102	1000	F, G, J	BP	10	
CDR36BP1R0Y_	1R0	1.0	C, D	BP	16	
CDR36BP1R2Y_	1R2	1.2	C, D	BP	16	
CDR36BP1R5Y_	1R5	1.5	C, D	BP	16	
CDR36BP1R8Y_	1R8	1.8	C, D	BP	16	
CDR36BP2R2Y_	2R2	2.2	C, D	BP	16	
CDR36BP2R4Y_	2R4	2.4	C, D	BP	16	
CDR36BP2R7Y_	2R7	2.7	C, D	BP	16	
CDR36BP3R0Y_	3R0	3.0	C, D	BP	16	
CDR36BP3R3Y_	3R3	3.3	C, D	BP	16	
CDR36BP3R6Y_	3R6	3.6	C, D	BP	16	
CDR36BP3R9Y_	3R9	3.9	C, D	BP	16	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP4R7Y_	4R7	4.7	C, D	BP	16	
CDR36BP5R1Y_	5R1	5.1	C, D	BP	16	
CDR36BP5R6Y_	5R6	5.6	C, D	BP	16	
CDR36BP6R2Y_	6R2	6.2	C, D	BP	16	
CDR36BP6R8Y_	6R8	6.8	C, D	BP	16	
CDR36BP7R5Y_	7R5	7.5	C, D	BP	16	
CDR36BP8R2Y_	8R2	8.2	C, D	BP	16	
CDR36BP9R1Y_	9R1	9.1	C, D	BP	16	
CDR36BP100Y_	100	10	F, G, J	BP	16	
CDR36BP110Y_	110	11	F, G, J	BP	16	
CDR36BP120Y_	120	12	F, G, J	BP	16	
CDR36BP130Y_	130	13	F, G, J	BP	16	
CDR36BP150Y_	150	15	F, G, J	BP	16	
CDR36BP160Y_	160	16	F, G, J	BP	16	
CDR36BP180Y_	180	18	F, G, J	BP	16	
CDR36BP200Y_	200	20	F, G, J	BP	16	
CDR36BP220Y_	220	22	F, G, J	BP	16	
CDR36BP240Y_	240	24	F, G, J	BP	16	
CDR36BP270Y_	270	27	F, G, J	BP	16	
CDR36BP300Y_	300	30	F, G, J	BP	16	
CDR36BP330Y_	330	33	F, G, J	BP	16	
CDR36BP360Y_	360	36	F, G, J	BP	16	
CDR36BP390Y_	390	39	F, G, J	BP	16	
CDR36BP430Y_	430	43	F, G, J	BP	16	
CDR36BP470Y_	470	47	F, G, J	BP	16	
CDR36BP510Y_	510	51	F, G, J	BP	16	
CDR36BP560Y_	560	56	F, G, J	BP	16	
CDR36BP620Y_	620	62	F, G, J	BP	16	
CDR36BP680Y_	680	68	F, G, J	BP	16	
CDR36BP750Y_	750	75	F, G, J	BP	16	
CDR36BP820Y_	820	82	F, G, J	BP	16	
CDR36BP910Y_	910	91	F, G, J	BP	16	
CDR36BP101Y_	101	100	F, G, J	BP	16	
CDR36BP121Y_	121	120	F, G, J	BP	16	
CDR36BP151Y_	151	150	F, G, J	BP	16	
CDR36BP181Y_	181	180	F, G, J	BP	16	
CDR36BP221Y_	221	220	F, G, J	BP	16	
CDR36BP271Y_	271	270	F, G, J	BP	16	
CDR36BP331Y_	331	330	F, G, J	BP	16	
CDR36BP391Y_	391	390	F, G, J	BP	16	
CDR36BP471Y_	471	470	F, G, J	BP	16	
CDR36BP561Y_	561	560	F, G, J	BP	16	
CDR36BP681Y_	681	680	F, G, J	BP	16	
CDR36BP821Y_	821	820	F, G, J	BP	16	
CDR36BP102Y_	102	1000	F, G, J	BP	16	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP1R0Z_	1R0	1.0	C, D	BP	25	
CDR36BP1R2Z_	1R2	1.2	C, D	BP	25	
CDR36BP1R5Z_	1R5	1.5	C, D	BP	25	
CDR36BP1R8Z_	1R8	1.8	C, D	BP	25	
CDR36BP2R2Z_	2R2	2.2	C, D	BP	25	
CDR36BP2R4Z_	2R4	2.4	C, D	BP	25	
CDR36BP2R7Z_	2R7	2.7	C, D	BP	25	
CDR36BP3R0Z_	3R0	3.0	C, D	BP	25	
CDR36BP3R3Z_	3R3	3.3	C, D	BP	25	
CDR36BP3R6Z_	3R6	3.6	C, D	BP	25	
CDR36BP3R9Z_	3R9	3.9	C, D	BP	25	
CDR36BP4R7Z_	4R7	4.7	C, D	BP	25	
CDR36BP5R1Z_	5R1	5.1	C, D	BP	25	
CDR36BP5R6Z_	5R6	5.6	C, D	BP	25	
CDR36BP6R2Z_	6R2	6.2	C, D	BP	25	
CDR36BP6R8Z_	6R8	6.8	C, D	BP	25	
CDR36BP7R5Z_	7R5	7.5	C, D	BP	25	
CDR36BP8R2Z_	8R2	8.2	C, D	BP	25	
CDR36BP9R1Z_	9R1	9.1	C, D	BP	25	
CDR36BP100Z_	100	10	F, G, J	BP	25	
CDR36BP110Z_	110	11	F, G, J	BP	25	
CDR36BP120Z_	120	12	F, G, J	BP	25	
CDR36BP130Z_	130	13	F, G, J	BP	25	
CDR36BP150Z_	150	15	F, G, J	BP	25	
CDR36BP160Z_	160	16	F, G, J	BP	25	
CDR36BP180Z_	180	18	F, G, J	BP	25	
CDR36BP200Z_	200	20	F, G, J	BP	25	
CDR36BP220Z_	220	22	F, G, J	BP	25	
CDR36BP240Z_	240	24	F, G, J	BP	25	
CDR36BP270Z_	270	27	F, G, J	BP	25	
CDR36BP300Z_	300	30	F, G, J	BP	25	
CDR36BP330Z_	330	33	F, G, J	BP	25	
CDR36BP360Z_	360	36	F, G, J	BP	25	
CDR36BP390Z_	390	39	F, G, J	BP	25	
CDR36BP430Z_	430	43	F, G, J	BP	25	
CDR36BP470Z_	470	47	F, G, J	BP	25	
CDR36BP510Z_	510	51	F, G, J	BP	25	
CDR36BP560Z_	560	56	F, G, J	BP	25	
CDR36BP620Z_	620	62	F, G, J	BP	25	
CDR36BP680Z_	680	68	F, G, J	BP	25	
CDR36BP750Z_	750	75	F, G, J	BP	25	
CDR36BP820Z_	820	82	F, G, J	BP	25	
CDR36BP910Z_	910	91	F, G, J	BP	25	
CDR36BP101Z_	101	100	F, G, J	BP	25	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP121Z_ _ _	121	120	F, G, J	BP	25	
CDR36BP151Z_ _ _	151	150	F, G, J	BP	25	
CDR36BP181Z_ _ _	181	180	F, G, J	BP	25	
CDR36BP221Z_ _ _	221	220	F, G, J	BP	25	
CDR36BP271Z_ _ _	271	270	F, G, J	BP	25	
CDR36BP331Z_ _ _	331	330	F, G, J	BP	25	
CDR36BP391Z_ _ _	391	390	F, G, J	BP	25	
CDR36BP471Z_ _ _	471	470	F, G, J	BP	25	
CDR36BP561Z_ _ _	561	560	F, G, J	BP	25	
CDR36BP681Z_ _ _	681	680	F, G, J	BP	25	
CDR36BP821Z_ _ _	821	820	F, G, J	BP	25	
CDR36BP102Z_ _ _	102	1000	F, G, J	BP	25	
CDR36BP1R0A_ _ _	1R0	1.0	C, D	BP	50	
CDR36BP1R2A_ _ _	1R2	1.2	C, D	BP	50	
CDR36BP1R5A_ _ _	1R5	1.5	C, D	BP	50	
CDR36BP1R8A_ _ _	1R8	1.8	C, D	BP	50	
CDR36BP2R2A_ _ _	2R2	2.2	C, D	BP	50	
CDR36BP2R4A_ _ _	2R4	2.4	C, D	BP	50	
CDR36BP2R7A_ _ _	2R7	2.7	C, D	BP	50	
CDR36BP3R0A_ _ _	3R0	3.0	C, D	BP	50	
CDR36BP3R3A_ _ _	3R3	3.3	C, D	BP	50	
CDR36BP3R6A_ _ _	3R6	3.6	C, D	BP	50	
CDR36BP3R9A_ _ _	3R9	3.9	C, D	BP	50	
CDR36BP4R7A_ _ _	4R7	4.7	C, D	BP	50	
CDR36BP5R1A_ _ _	5R1	5.1	C, D	BP	50	
CDR36BP5R6A_ _ _	5R6	5.6	C, D	BP	50	
CDR36BP6R2A_ _ _	6R2	6.2	C, D	BP	50	
CDR36BP6R8A_ _ _	6R8	6.8	C, D	BP	50	
CDR36BP7R5A_ _ _	7R5	7.5	C, D	BP	50	
CDR36BP8R2A_ _ _	8R2	8.2	C, D	BP	50	
CDR36BP9R1A_ _ _	9R1	9.1	C, D	BP	50	
CDR36BP100A_ _ _	100	10	F, G, J	BP	50	
CDR36BP110A_ _ _	110	11	F, G, J	BP	50	
CDR36BP120A_ _ _	120	12	F, G, J	BP	50	
CDR36BP130A_ _ _	130	13	F, G, J	BP	50	
CDR36BP150A_ _ _	150	15	F, G, J	BP	50	
CDR36BP160A_ _ _	160	16	F, G, J	BP	50	
CDR36BP180A_ _ _	180	18	F, G, J	BP	50	
CDR36BP200A_ _ _	200	20	F, G, J	BP	50	
CDR36BP220A_ _ _	220	22	F, G, J	BP	50	
CDR36BP240A_ _ _	240	24	F, G, J	BP	50	
CDR36BP270A_ _ _	270	27	F, G, J	BP	50	
CDR36BP300A_ _ _	300	30	F, G, J	BP	50	
CDR36BP330A_ _ _	330	33	F, G, J	BP	50	
CDR36BP360A_ _ _	360	36	F, G, J	BP	50	
CDR36BP390A_ _ _	390	39	F, G, J	BP	50	
CDR36BP430A_ _ _	430	43	F, G, J	BP	50	
CDR36BP470A_ _ _	470	47	F, G, J	BP	50	

Notes

RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"

Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP510A_ _ _	510	51	F, G, J	BP	50	
CDR36BP560A_ _ _	560	56	F, G, J	BP	50	
CDR36BP620A_ _ _	620	62	F, G, J	BP	50	
CDR36BP680A_ _ _	680	68	F, G, J	BP	50	
CDR36BP750A_ _ _	750	75	F, G, J	BP	50	
CDR36BP820A_ _ _	820	82	F, G, J	BP	50	
CDR36BP910A_ _ _	910	91	F, G, J	BP	50	
CDR36BP101A_ _ _	101	100	F, G, J	BP	50	
CDR36BP121A_ _ _	121	120	F, G, J	BP	50	
CDR36BP151A_ _ _	151	150	F, G, J	BP	50	
CDR36BP181A_ _ _	181	180	F, G, J	BP	50	
CDR36BP221A_ _ _	221	220	F, G, J	BP	50	
CDR36BP271A_ _ _	271	270	F, G, J	BP	50	
CDR36BP331A_ _ _	331	330	F, G, J	BP	50	
CDR36BP391A_ _ _	391	390	F, G, J	BP	50	
CDR36BP471A_ _ _	471	470	F, G, J	BP	50	
CDR36BP561A_ _ _	561	560	F, G, J	BP	50	
CDR36BP681A_ _ _	681	680	F, G, J	BP	50	
CDR36BP1R0B_ _ _	1R0	1.0	C, D	BP	100	
CDR36BP1R2B_ _ _	1R2	1.2	C, D	BP	100	
CDR36BP1R5B_ _ _	1R5	1.5	C, D	BP	100	
CDR36BP1R8B_ _ _	1R8	1.8	C, D	BP	100	
CDR36BP2R2B_ _ _	2R2	2.2	C, D	BP	100	
CDR36BP2R4B_ _ _	2R4	2.4	C, D	BP	100	
CDR36BP2R7B_ _ _	2R7	2.7	C, D	BP	100	
CDR36BP3R0B_ _ _	3R0	3.0	C, D	BP	100	
CDR36BP3R3B_ _ _	3R3	3.3	C, D	BP	100	
CDR36BP3R6B_ _ _	3R6	3.6	C, D	BP	100	
CDR36BP3R9B_ _ _	3R9	3.9	C, D	BP	100	
CDR36BP4R7B_ _ _	4R7	4.7	C, D	BP	100	
CDR36BP5R1B_ _ _	5R1	5.1	C, D	BP	100	
CDR36BP5R6B_ _ _	5R6	5.6	C, D	BP	100	
CDR36BP6R2B_ _ _	6R2	6.2	C, D	BP	100	
CDR36BP6R8B_ _ _	6R8	6.8	C, D	BP	100	
CDR36BP7R5B_ _ _	7R5	7.5	C, D	BP	100	
CDR36BP8R2B_ _ _	8R2	8.2	C, D	BP	100	
CDR36BP9R1B_ _ _	9R1	9.1	C, D	BP	100	
CDR36BP100B_ _ _	100	10	F, G, J	BP	100	
CDR36BP110B_ _ _	110	11	F, G, J	BP	100	
CDR36BP120B_ _ _	120	12	F, G, J	BP	100	
CDR36BP130B_ _ _	130	13	F, G, J	BP	100	
CDR36BP150B_ _ _	150	15	F, G, J	BP	100	
CDR36BP160B_ _ _	160	16	F, G, J	BP	100	
CDR36BP180B_ _ _	180	18	F, G, J	BP	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BP						
CDR36BP200B_	200	20	F, G, J	BP	100	
CDR36BP220B_	220	22	F, G, J	BP	100	
CDR36BP240B_	240	24	F, G, J	BP	100	
CDR36BP270B_	270	27	F, G, J	BP	100	
CDR36BP300B_	300	30	F, G, J	BP	100	
CDR36BP330B_	330	33	F, G, J	BP	100	
CDR36BP360B_	360	36	F, G, J	BP	100	
CDR36BP390B_	390	39	F, G, J	BP	100	
CDR36BP430B_	430	43	F, G, J	BP	100	
CDR36BP470B_	470	47	F, G, J	BP	100	
CDR36BP510B_	510	51	F, G, J	BP	100	
CDR36BP560B_	560	56	F, G, J	BP	100	
CDR36BP620B_	620	62	F, G, J	BP	100	
CDR36BP680B_	680	68	F, G, J	BP	100	
CDR36BP750B_	750	75	F, G, J	BP	100	
CDR36BP820B_	820	82	F, G, J	BP	100	
CDR36BP910B_	910	91	F, G, J	BP	100	
CDR36BP101B_	101	100	F, G, J	BP	100	
CDR36BP121B_	121	120	F, G, J	BP	100	
CDR36BP151B_	151	150	F, G, J	BP	100	
CDR36BP181B_	181	180	F, G, J	BP	100	
CDR36BP221B_	221	220	F, G, J	BP	100	
CDR36BP271B_	271	270	F, G, J	BP	100	
CDR36BP331B_	331	330	F, G, J	BP	100	
CDR36BX						
CDR36BX101W_	101	100	J, K, M	BX	6.3	
CDR36BX121W_	121	120	J, K, M	BX	6.3	
CDR36BX151W_	151	150	J, K, M	BX	6.3	
CDR36BX181W_	181	180	J, K, M	BX	6.3	
CDR36BX221W_	221	220	J, K, M	BX	6.3	
CDR36BX271W_	271	270	J, K, M	BX	6.3	
CDR36BX331W_	331	330	J, K, M	BX	6.3	
CDR36BX391W_	391	390	J, K, M	BX	6.3	
CDR36BX471W_	471	470	J, K, M	BX	6.3	
CDR36BX561W_	561	560	J, K, M	BX	6.3	
CDR36BX681W_	681	680	J, K, M	BX	6.3	
CDR36BX821W_	821	820	J, K, M	BX	6.3	
CDR36BX102W_	102	1000	J, K, M	BX	6.3	
CDR36BX122W_	122	1200	J, K, M	BX	6.3	
CDR36BX152W_	152	1500	J, K, M	BX	6.3	
CDR36BX182W_	182	1800	J, K, M	BX	6.3	
CDR36BX222W_	222	2200	J, K, M	BX	6.3	
CDR36BX272W_	272	2700	J, K, M	BX	6.3	
CDR36BX332W_	332	3300	J, K, M	BX	6.3	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BX						
CDR36BX392W_ _ _	392	3900	J, K, M	BX	6.3	
CDR36BX472W_ _ _	472	4700	J, K, M	BX	6.3	
CDR36BX562W_ _ _	562	5600	J, K, M	BX	6.3	
CDR36BX682W_ _ _	682	6800	J, K, M	BX	6.3	
CDR36BX822W_ _ _	822	8200	J, K, M	BX	6.3	
CDR36BX103W_ _ _	103	10 000	J, K, M	BX	6.3	
CDR36BX123W_ _ _	123	12 000	J, K, M	BX	6.3	
CDR36BX153W_ _ _	153	15 000	J, K, M	BX	6.3	
CDR36BX183W_ _ _	183	18 000	J, K, M	BX	6.3	
CDR36BX223W_ _ _	223	22 000	J, K, M	BX	6.3	
CDR36BX273W_ _ _	273	27 000	J, K, M	BX	6.3	
CDR36BX333W_ _ _	333	33 000	J, K, M	BX	6.3	
CDR36BX393W_ _ _	393	39 000	J, K, M	BX	6.3	
CDR36BX473W_ _ _	473	47 000	J, K, M	BX	6.3	
CDR36BX563W_ _ _	563	56 000	J, K, M	BX	6.3	
CDR36BX101X_ _ _	101	100	J, K, M	BX	10	
CDR36BX121X_ _ _	121	120	J, K, M	BX	10	
CDR36BX151X_ _ _	151	150	J, K, M	BX	10	
CDR36BX181X_ _ _	181	180	J, K, M	BX	10	
CDR36BX221X_ _ _	221	220	J, K, M	BX	10	
CDR36BX271X_ _ _	271	270	J, K, M	BX	10	
CDR36BX331X_ _ _	331	330	J, K, M	BX	10	
CDR36BX391X_ _ _	391	390	J, K, M	BX	10	
CDR36BX471X_ _ _	471	470	J, K, M	BX	10	
CDR36BX561X_ _ _	561	560	J, K, M	BX	10	
CDR36BX681X_ _ _	681	680	J, K, M	BX	10	
CDR36BX821X_ _ _	821	820	J, K, M	BX	10	
CDR36BX102X_ _ _	102	1000	J, K, M	BX	10	
CDR36BX122X_ _ _	122	1200	J, K, M	BX	10	
CDR36BX152X_ _ _	152	1500	J, K, M	BX	10	
CDR36BX182X_ _ _	182	1800	J, K, M	BX	10	
CDR36BX222X_ _ _	222	2200	J, K, M	BX	10	
CDR36BX272X_ _ _	272	2700	J, K, M	BX	10	
CDR36BX332X_ _ _	332	3300	J, K, M	BX	10	
CDR36BX392X_ _ _	392	3900	J, K, M	BX	10	
CDR36BX472X_ _ _	472	4700	J, K, M	BX	10	
CDR36BX562X_ _ _	562	5600	J, K, M	BX	10	
CDR36BX682X_ _ _	682	6800	J, K, M	BX	10	
CDR36BX822X_ _ _	822	8200	J, K, M	BX	10	
CDR36BX103X_ _ _	103	10 000	J, K, M	BX	10	
CDR36BX123X_ _ _	123	12 000	J, K, M	BX	10	
CDR36BX153X_ _ _	153	15 000	J, K, M	BX	10	
CDR36BX183X_ _ _	183	18 000	J, K, M	BX	10	
CDR36BX223X_ _ _	223	22 000	J, K, M	BX	10	
CDR36BX273X_ _ _	273	27 000	J, K, M	BX	10	
CDR36BX333X_ _ _	333	33 000	J, K, M	BX	10	
CDR36BX393X_ _ _	393	39 000	J, K, M	BX	10	
CDR36BX473X_ _ _	473	47 000	J, K, M	BX	10	
CDR36BX563X_ _ _	563	56 000	J, K, M	BX	10	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BX						
CDR36BX101Y_ _ _	101	100	J, K, M	BX	16	
CDR36BX121Y_ _ _	121	120	J, K, M	BX	16	
CDR36BX151Y_ _ _	151	150	J, K, M	BX	16	
CDR36BX181Y_ _ _	181	180	J, K, M	BX	16	
CDR36BX221Y_ _ _	221	220	J, K, M	BX	16	
CDR36BX271Y_ _ _	271	270	J, K, M	BX	16	
CDR36BX331Y_ _ _	331	330	J, K, M	BX	16	
CDR36BX391Y_ _ _	391	390	J, K, M	BX	16	
CDR36BX471Y_ _ _	471	470	J, K, M	BX	16	
CDR36BX561Y_ _ _	561	560	J, K, M	BX	16	
CDR36BX681Y_ _ _	681	680	J, K, M	BX	16	
CDR36BX821Y_ _ _	821	820	J, K, M	BX	16	
CDR36BX102Y_ _ _	102	1000	J, K, M	BX	16	
CDR36BX122Y_ _ _	122	1200	J, K, M	BX	16	
CDR36BX152Y_ _ _	152	1500	J, K, M	BX	16	
CDR36BX182Y_ _ _	182	1800	J, K, M	BX	16	
CDR36BX222Y_ _ _	222	2200	J, K, M	BX	16	
CDR36BX272Y_ _ _	272	2700	J, K, M	BX	16	
CDR36BX332Y_ _ _	332	3300	J, K, M	BX	16	
CDR36BX392Y_ _ _	392	3900	J, K, M	BX	16	
CDR36BX472Y_ _ _	472	4700	J, K, M	BX	16	
CDR36BX562Y_ _ _	562	5600	J, K, M	BX	16	
CDR36BX682Y_ _ _	682	6800	J, K, M	BX	16	
CDR36BX822Y_ _ _	822	8200	J, K, M	BX	16	
CDR36BX103Y_ _ _	103	10 000	J, K, M	BX	16	
CDR36BX123Y_ _ _	123	12 000	J, K, M	BX	16	
CDR36BX153Y_ _ _	153	15 000	J, K, M	BX	16	
CDR36BX183Y_ _ _	183	18 000	J, K, M	BX	16	
CDR36BX223Y_ _ _	223	22 000	J, K, M	BX	16	
CDR36BX273Y_ _ _	273	27 000	J, K, M	BX	16	
CDR36BX333Y_ _ _	333	33 000	J, K, M	BX	16	
CDR36BX393Y_ _ _	393	39 000	J, K, M	BX	16	
CDR36BX473Y_ _ _	473	47 000	J, K, M	BX	16	
CDR36BX563Y_ _ _	563	56 000	J, K, M	BX	16	
CDR36BX101Z_ _ _	101	100	J, K, M	BX	25	
CDR36BX121Z_ _ _	121	120	J, K, M	BX	25	
CDR36BX151Z_ _ _	151	150	J, K, M	BX	25	
CDR36BX181Z_ _ _	181	180	J, K, M	BX	25	
CDR36BX221Z_ _ _	221	220	J, K, M	BX	25	
CDR36BX271Z_ _ _	271	270	J, K, M	BX	25	
CDR36BX331Z_ _ _	331	330	J, K, M	BX	25	
CDR36BX391Z_ _ _	391	390	J, K, M	BX	25	
CDR36BX471Z_ _ _	471	470	J, K, M	BX	25	
CDR36BX561Z_ _ _	561	560	J, K, M	BX	25	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BX						
CDR36BX681Z_ _ _	681	680	J, K, M	BX	25	
CDR36BX821Z_ _ _	821	820	J, K, M	BX	25	
CDR36BX102Z_ _ _	102	1000	J, K, M	BX	25	
CDR36BX122Z_ _ _	122	1200	J, K, M	BX	25	
CDR36BX152Z_ _ _	152	1500	J, K, M	BX	25	
CDR36BX182Z_ _ _	182	1800	J, K, M	BX	25	
CDR36BX222Z_ _ _	222	2200	J, K, M	BX	25	
CDR36BX272Z_ _ _	272	2700	J, K, M	BX	25	
CDR36BX332Z_ _ _	332	3300	J, K, M	BX	25	
CDR36BX392Z_ _ _	392	3900	J, K, M	BX	25	
CDR36BX472Z_ _ _	472	4700	J, K, M	BX	25	
CDR36BX562Z_ _ _	562	5600	J, K, M	BX	25	
CDR36BX682Z_ _ _	682	6800	J, K, M	BX	25	
CDR36BX822Z_ _ _	822	8200	J, K, M	BX	25	
CDR36BX103Z_ _ _	103	10 000	J, K, M	BX	25	
CDR36BX123Z_ _ _	123	12 000	J, K, M	BX	25	
CDR36BX153Z_ _ _	153	15 000	J, K, M	BX	25	
CDR36BX183Z_ _ _	183	18 000	J, K, M	BX	25	
CDR36BX223Z_ _ _	223	22 000	J, K, M	BX	25	
CDR36BX273Z_ _ _	273	27 000	J, K, M	BX	25	
CDR36BX101A_ _ _	101	100	J, K, M	BX	50	
CDR36BX121A_ _ _	121	120	J, K, M	BX	50	
CDR36BX151A_ _ _	151	150	J, K, M	BX	50	
CDR36BX181A_ _ _	181	180	J, K, M	BX	50	
CDR36BX221A_ _ _	221	220	J, K, M	BX	50	
CDR36BX271A_ _ _	271	270	J, K, M	BX	50	
CDR36BX331A_ _ _	331	330	J, K, M	BX	50	
CDR36BX391A_ _ _	391	390	J, K, M	BX	50	
CDR36BX471A_ _ _	471	470	J, K, M	BX	50	
CDR36BX561A_ _ _	561	560	J, K, M	BX	50	
CDR36BX681A_ _ _	681	680	J, K, M	BX	50	
CDR36BX821A_ _ _	821	820	J, K, M	BX	50	
CDR36BX102A_ _ _	102	1000	J, K, M	BX	50	
CDR36BX122A_ _ _	122	1200	J, K, M	BX	50	
CDR36BX152A_ _ _	152	1500	J, K, M	BX	50	
CDR36BX182A_ _ _	182	1800	J, K, M	BX	50	
CDR36BX222A_ _ _	222	2200	J, K, M	BX	50	
CDR36BX272A_ _ _	272	2700	J, K, M	BX	50	
CDR36BX332A_ _ _	332	3300	J, K, M	BX	50	
CDR36BX392A_ _ _	392	3900	J, K, M	BX	50	
CDR36BX472A_ _ _	472	4700	J, K, M	BX	50	
CDR36BX562A_ _ _	562	5600	J, K, M	BX	50	
CDR36BX682A_ _ _	682	6800	J, K, M	BX	50	
CDR36BX822A_ _ _	822	8200	J, K, M	BX	50	
CDR36BX103A_ _ _	103	10 000	J, K, M	BX	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BX						
CDR36BX101B_	101	100	J, K, M	BX	100	
CDR36BX121B_	121	120	J, K, M	BX	100	
CDR36BX151B_	151	150	J, K, M	BX	100	
CDR36BX181B_	181	180	J, K, M	BX	100	
CDR36BX221B_	221	220	J, K, M	BX	100	
CDR36BX271B_	271	270	J, K, M	BX	100	
CDR36BX331B_	331	330	J, K, M	BX	100	
CDR36BX391B_	391	390	J, K, M	BX	100	
CDR36BX471B_	471	470	J, K, M	BX	100	
CDR36BX561B_	561	560	J, K, M	BX	100	
CDR36BX681B_	681	680	J, K, M	BX	100	
CDR36BX821B_	821	820	J, K, M	BX	100	
CDR36BX102B_	102	1000	J, K, M	BX	100	
CDR36BX122B_	122	1200	J, K, M	BX	100	
CDR36BX152B_	152	1500	J, K, M	BX	100	
CDR36BX182B_	182	1800	J, K, M	BX	100	
CDR36BX222B_	222	2200	J, K, M	BX	100	
CDR36BX272B_	272	2700	J, K, M	BX	100	
CDR36BR						
CDR36BR101W_	101	100	J, K, M	BR	6.3	
CDR36BR121W_	121	120	J, K, M	BR	6.3	
CDR36BR151W_	151	150	J, K, M	BR	6.3	
CDR36BR181W_	181	180	J, K, M	BR	6.3	
CDR36BR221W_	221	220	J, K, M	BR	6.3	
CDR36BR271W_	271	270	J, K, M	BR	6.3	
CDR36BR331W_	331	330	J, K, M	BR	6.3	
CDR36BR391W_	391	390	J, K, M	BR	6.3	
CDR36BR471W_	471	470	J, K, M	BR	6.3	
CDR36BR561W_	561	560	J, K, M	BR	6.3	
CDR36BR681W_	681	680	J, K, M	BR	6.3	
CDR36BR821W_	821	820	J, K, M	BR	6.3	
CDR36BR102W_	102	1000	J, K, M	BR	6.3	
CDR36BR122W_	122	1200	J, K, M	BR	6.3	
CDR36BR152W_	152	1500	J, K, M	BR	6.3	
CDR36BR182W_	182	1800	J, K, M	BR	6.3	
CDR36BR222W_	222	2200	J, K, M	BR	6.3	
CDR36BR272W_	272	2700	J, K, M	BR	6.3	
CDR36BR332W_	332	3300	J, K, M	BR	6.3	
CDR36BR392W_	392	3900	J, K, M	BR	6.3	
CDR36BR472W_	472	4700	J, K, M	BR	6.3	
CDR36BR562W_	562	5600	J, K, M	BR	6.3	
CDR36BR682W_	682	6800	J, K, M	BR	6.3	
CDR36BR822W_	822	8200	J, K, M	BR	6.3	
CDR36BR103W_	103	10 000	J, K, M	BR	6.3	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BR						
CDR36BR123W_ _ _	123	12 000	J, K, M	BR	6.3	
CDR36BR153W_ _ _	153	15 000	J, K, M	BR	6.3	
CDR36BR183W_ _ _	183	18 000	J, K, M	BR	6.3	
CDR36BR223W_ _ _	223	22 000	J, K, M	BR	6.3	
CDR36BR273W_ _ _	273	27 000	J, K, M	BR	6.3	
CDR36BR333W_ _ _	333	33 000	J, K, M	BR	6.3	
CDR36BR393W_ _ _	393	39 000	J, K, M	BR	6.3	
CDR36BR473W_ _ _	473	47 000	J, K, M	BR	6.3	
CDR36BR563W_ _ _	563	56 000	J, K, M	BR	6.3	
CDR36BR683W_ _ _	683	68 000	J, K, M	BR	6.3	
CDR36BR823W_ _ _	823	82 000	J, K, M	BR	6.3	
CDR36BR104W_ _ _	104	100 000	J, K, M	BR	6.3	
CDR36BR101X_ _ _	101	100	J, K, M	BR	10	
CDR36BR121X_ _ _	121	120	J, K, M	BR	10	
CDR36BR151X_ _ _	151	150	J, K, M	BR	10	
CDR36BR181X_ _ _	181	180	J, K, M	BR	10	
CDR36BR221X_ _ _	221	220	J, K, M	BR	10	
CDR36BR271X_ _ _	271	270	J, K, M	BR	10	
CDR36BR331X_ _ _	331	330	J, K, M	BR	10	
CDR36BR391X_ _ _	391	390	J, K, M	BR	10	
CDR36BR471X_ _ _	471	470	J, K, M	BR	10	
CDR36BR561X_ _ _	561	560	J, K, M	BR	10	
CDR36BR681X_ _ _	681	680	J, K, M	BR	10	
CDR36BR821X_ _ _	821	820	J, K, M	BR	10	
CDR36BR102X_ _ _	102	1000	J, K, M	BR	10	
CDR36BR122X_ _ _	122	1200	J, K, M	BR	10	
CDR36BR152X_ _ _	152	1500	J, K, M	BR	10	
CDR36BR182X_ _ _	182	1800	J, K, M	BR	10	
CDR36BR222X_ _ _	222	2200	J, K, M	BR	10	
CDR36BR272X_ _ _	272	2700	J, K, M	BR	10	
CDR36BR332X_ _ _	332	3300	J, K, M	BR	10	
CDR36BR392X_ _ _	392	3900	J, K, M	BR	10	
CDR36BR472X_ _ _	472	4700	J, K, M	BR	10	
CDR36BR562X_ _ _	562	5600	J, K, M	BR	10	
CDR36BR682X_ _ _	682	6800	J, K, M	BR	10	
CDR36BR822X_ _ _	822	8200	J, K, M	BR	10	
CDR36BR103X_ _ _	103	10 000	J, K, M	BR	10	
CDR36BR123X_ _ _	123	12 000	J, K, M	BR	10	
CDR36BR153X_ _ _	153	15 000	J, K, M	BR	10	
CDR36BR183X_ _ _	183	18 000	J, K, M	BR	10	
CDR36BR223X_ _ _	223	22 000	J, K, M	BR	10	
CDR36BR273X_ _ _	273	27 000	J, K, M	BR	10	
CDR36BR333X_ _ _	333	33 000	J, K, M	BR	10	
CDR36BR393X_ _ _	393	39 000	J, K, M	BR	10	
CDR36BR473X_ _ _	473	47 000	J, K, M	BR	10	
CDR36BR563X_ _ _	563	56 000	J, K, M	BR	10	
CDR36BR683X_ _ _	683	68 000	J, K, M	BR	10	
CDR36BR823X_ _ _	823	82 000	J, K, M	BR	10	
CDR36BR104X_ _ _	104	100 000	J, K, M	BR	10	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BR						
CDR36BR101Y_	101	100	J, K, M	BR	16	
CDR36BR121Y_	121	120	J, K, M	BR	16	
CDR36BR151Y_	151	150	J, K, M	BR	16	
CDR36BR181Y_	181	180	J, K, M	BR	16	
CDR36BR221Y_	221	220	J, K, M	BR	16	
CDR36BR271Y_	271	270	J, K, M	BR	16	
CDR36BR331Y_	331	330	J, K, M	BR	16	
CDR36BR391Y_	391	390	J, K, M	BR	16	
CDR36BR471Y_	471	470	J, K, M	BR	16	
CDR36BR561Y_	561	560	J, K, M	BR	16	
CDR36BR681Y_	681	680	J, K, M	BR	16	
CDR36BR821Y_	821	820	J, K, M	BR	16	
CDR36BR102Y_	102	1000	J, K, M	BR	16	
CDR36BR122Y_	122	1200	J, K, M	BR	16	
CDR36BR152Y_	152	1500	J, K, M	BR	16	
CDR36BR182Y_	182	1800	J, K, M	BR	16	
CDR36BR222Y_	222	2200	J, K, M	BR	16	
CDR36BR272Y_	272	2700	J, K, M	BR	16	
CDR36BR332Y_	332	3300	J, K, M	BR	16	
CDR36BR392Y_	392	3900	J, K, M	BR	16	
CDR36BR472Y_	472	4700	J, K, M	BR	16	
CDR36BR562Y_	562	5600	J, K, M	BR	16	
CDR36BR682Y_	682	6800	J, K, M	BR	16	
CDR36BR822Y_	822	8200	J, K, M	BR	16	
CDR36BR103Y_	103	10 000	J, K, M	BR	16	
CDR36BR123Y_	123	12 000	J, K, M	BR	16	
CDR36BR153Y_	153	15 000	J, K, M	BR	16	
CDR36BR183Y_	183	18 000	J, K, M	BR	16	
CDR36BR223Y_	223	22 000	J, K, M	BR	16	
CDR36BR273Y_	273	27 000	J, K, M	BR	16	
CDR36BR333Y_	333	33 000	J, K, M	BR	16	
CDR36BR393Y_	393	39 000	J, K, M	BR	16	
CDR36BR473Y_	473	47 000	J, K, M	BR	16	
CDR36BR563Y_	563	56 000	J, K, M	BR	16	
CDR36BR683Y_	683	68 000	J, K, M	BR	16	
CDR36BR823Y_	823	82 000	J, K, M	BR	16	
CDR36BR104Y_	104	100 000	J, K, M	BR	16	
CDR36BR101Z_	101	100	J, K, M	BR	25	
CDR36BR121Z_	121	120	J, K, M	BR	25	
CDR36BR151Z_	151	150	J, K, M	BR	25	
CDR36BR181Z_	181	180	J, K, M	BR	25	
CDR36BR221Z_	221	220	J, K, M	BR	25	
CDR36BR271Z_	271	270	J, K, M	BR	25	
CDR36BR331Z_	331	330	J, K, M	BR	25	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**MIL-C-55681 QUALIFIED, TYPE CDR**

MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BR						
CDR36BR391Z_ _ _	391	390	J, K, M	BR	25	
CDR36BR471Z_ _ _	471	470	J, K, M	BR	25	
CDR36BR561Z_ _ _	561	560	J, K, M	BR	25	
CDR36BR681Z_ _ _	681	680	J, K, M	BR	25	
CDR36BR821Z_ _ _	821	820	J, K, M	BR	25	
CDR36BR102Z_ _ _	102	1000	J, K, M	BR	25	
CDR36BR122Z_ _ _	122	1200	J, K, M	BR	25	
CDR36BR152Z_ _ _	152	1500	J, K, M	BR	25	
CDR36BR182Z_ _ _	182	1800	J, K, M	BR	25	
CDR36BR222Z_ _ _	222	2200	J, K, M	BR	25	
CDR36BR272Z_ _ _	272	2700	J, K, M	BR	25	
CDR36BR332Z_ _ _	332	3300	J, K, M	BR	25	
CDR36BR392Z_ _ _	392	3900	J, K, M	BR	25	
CDR36BR472Z_ _ _	472	4700	J, K, M	BR	25	
CDR36BR562Z_ _ _	562	5600	J, K, M	BR	25	
CDR36BR682Z_ _ _	682	6800	J, K, M	BR	25	
CDR36BR822Z_ _ _	822	8200	J, K, M	BR	25	
CDR36BR103Z_ _ _	103	10 000	J, K, M	BR	25	
CDR36BR123Z_ _ _	123	12 000	J, K, M	BR	25	
CDR36BR153Z_ _ _	153	15 000	J, K, M	BR	25	
CDR36BR183Z_ _ _	183	18 000	J, K, M	BR	25	
CDR36BR223Z_ _ _	223	22 000	J, K, M	BR	25	
CDR36BR273Z_ _ _	273	27 000	J, K, M	BR	25	
CDR36BR333Z_ _ _	333	33 000	J, K, M	BR	25	
CDR36BR393Z_ _ _	393	39 000	J, K, M	BR	25	
CDR36BR473Z_ _ _	473	47 000	J, K, M	BR	25	
CDR36BR563Z_ _ _	563	56 000	J, K, M	BR	25	
CDR36BR101A_ _ _	101	100	J, K, M	BR	50	
CDR36BR121A_ _ _	121	120	J, K, M	BR	50	
CDR36BR151A_ _ _	151	150	J, K, M	BR	50	
CDR36BR181A_ _ _	181	180	J, K, M	BR	50	
CDR36BR221A_ _ _	221	220	J, K, M	BR	50	
CDR36BR271A_ _ _	271	270	J, K, M	BR	50	
CDR36BR331A_ _ _	331	330	J, K, M	BR	50	
CDR36BR391A_ _ _	391	390	J, K, M	BR	50	
CDR36BR471A_ _ _	471	470	J, K, M	BR	50	
CDR36BR561A_ _ _	561	560	J, K, M	BR	50	
CDR36BR681A_ _ _	681	680	J, K, M	BR	50	
CDR36BR821A_ _ _	821	820	J, K, M	BR	50	
CDR36BR102A_ _ _	102	1000	J, K, M	BR	50	
CDR36BR122A_ _ _	122	1200	J, K, M	BR	50	
CDR36BR152A_ _ _	152	1500	J, K, M	BR	50	
CDR36BR182A_ _ _	182	1800	J, K, M	BR	50	
CDR36BR222A_ _ _	222	2200	J, K, M	BR	50	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
- Not RoHS-compliant



MIL-C-55681 QUALIFIED, TYPE CDR						
MILITARY TYPE DESIGNATION	CAPACITANCE CODE	CAPACITANCE (pF)	CAPACITANCE TOLERANCE	RATED TEMP. AND VOLTAGE TEMP. LIMITS	VOLTAGE (DC)	RoHS STATUS
CDR36BR						
CDR36BR272A_ _ _	272	2700	J, K, M	BR	50	
CDR36BR332A_ _ _	332	3300	J, K, M	BR	50	
CDR36BR392A_ _ _	392	3900	J, K, M	BR	50	
CDR36BR472A_ _ _	472	4700	J, K, M	BR	50	
CDR36BR562A_ _ _	562	5600	J, K, M	BR	50	
CDR36BR682A_ _ _	682	6800	J, K, M	BR	50	
CDR36BR822A_ _ _	822	8200	J, K, M	BR	50	
CDR36BR103A_ _ _	103	10 000	J, K, M	BR	50	
CDR36BR123A_ _ _	123	12 000	J, K, M	BR	50	
CDR36BR153A_ _ _	153	15 000	J, K, M	BR	50	
CDR36BR183A_ _ _	183	18 000	J, K, M	BR	50	
CDR36BR223A_ _ _	223	22 000	J, K, M	BR	50	
CDR36BR273A_ _ _	273	27 000	J, K, M	BR	50	
CDR36BR101B_ _ _	101	100	J, K, M	BR	100	
CDR36BR121B_ _ _	121	120	J, K, M	BR	100	
CDR36BR151B_ _ _	151	150	J, K, M	BR	100	
CDR36BR181B_ _ _	181	180	J, K, M	BR	100	
CDR36BR221B_ _ _	221	220	J, K, M	BR	100	
CDR36BR271B_ _ _	271	270	J, K, M	BR	100	
CDR36BR331B_ _ _	331	330	J, K, M	BR	100	
CDR36BR391B_ _ _	391	390	J, K, M	BR	100	
CDR36BR471B_ _ _	471	470	J, K, M	BR	100	
CDR36BR561B_ _ _	561	560	J, K, M	BR	100	
CDR36BR681B_ _ _	681	680	J, K, M	BR	100	
CDR36BR821B_ _ _	821	820	J, K, M	BR	100	
CDR36BR102B_ _ _	102	1000	J, K, M	BR	100	
CDR36BR122B_ _ _	122	1200	J, K, M	BR	100	
CDR36BR152B_ _ _	152	1500	J, K, M	BR	100	
CDR36BR182B_ _ _	182	1800	J, K, M	BR	100	
CDR36BR222B_ _ _	222	2200	J, K, M	BR	100	
CDR36BR272B_ _ _	272	2700	J, K, M	BR	100	
CDR36BR332B_ _ _	332	3300	J, K, M	BR	100	
CDR36BR392B_ _ _	392	3900	J, K, M	BR	100	
CDR36BR472B_ _ _	472	4700	J, K, M	BR	100	
CDR36BR562B_ _ _	562	5600	J, K, M	BR	100	
CDR36BR682B_ _ _	682	6800	J, K, M	BR	100	
CDR36BR822B_ _ _	822	8200	J, K, M	BR	100	

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing terminations, codes "W", "Z", and "U"
 Not RoHS-compliant

**TAPE AND REEL QUANTITIES (1)(2)(3)**

STYLES	BODY SIZE	TAPE SIZE	7" REEL QUANTITIES			11 1/4" AND 13" REEL QUANTITIES		BULK
			PACKAGING CODE			PACKAGING CODE		
			“C”	“T”	“J”	“P”	“R”	
CDR37	0402	8 mm	5000	n/a	1000	10 000	n/a	100
CDR36	0603	8 mm	4000	n/a	1000	10 000	n/a	100
CDR01, CDR31	0805	8 mm	3000	3000	1000	10 000	10 000	100
CDR32	1206	8 mm	n/a	3000	1000	n/a	10 000	100
CDR33	1210	8 mm	n/a	3000	1000	n/a	10 000	100
CDR02	1805	12 mm	n/a	2000	500	n/a	10 000	100
CDR03	1808	12 mm	n/a	2000	500	n/a	10 000	100
CDR04, CDR34	1812	12 mm	n/a	1000	500	n/a	4000	100
CDR35	1825	12 mm	n/a	1000	500	n/a	4000	100
CDR06	2225	12 mm	n/a	500	250	n/a	4000	100

Notes

- (1) Vishay Vitramon uses embossed plastic carrier tape and punched paper carrier tape
(2) Paper tape is not available for case sizes > 1206 or for component thickness > 0.035" (0.89 mm)
(3) DC voltage rating should not be exceeded in application

STORAGE AND HANDLING CONDITIONS

(1) Store the components at 5 °C to +40 °C ambient temperature and ≤ 70 % related humidity conditions

(2) The product is recommended to be used within a time-frame of 2 years after shipment.

Check solderability in case extended shelf life beyond the expiry date is needed

Precautions:

- Do not store products in an environment containing corrosive elements, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. This may cause corrosion or oxidization of the terminations, which can easily lead to poor soldering
- Store products on the shelf and avoid exposure to moisture or dust
- Do not expose products to excessive shock, vibration, direct sunlight and so on



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.