

## 156-00860



Article Number: 156-00860

Cable Tie and Edge Clip, 8.0" Length, EC4A, Outside Serrated, PA66HS, Black, 500/bag



[Download drawing](#)



[Download spec sheet](#)

### Base Data

Local Order Number 156-00860

Type T50ROSEC4A

Color Black (BK)

**Features and Benefits**

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
- Cable tie is outside serrated to reduce bundle chafing.

**Product Description** The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

**Fixation Method (FF)** EdgeClip, top, assembled, 2 piece

**Identification Plate Position** none

**Releasable Closure (Yes/No)** No

**Variant** Outside Serrated

**Short Description** Cable Tie and Edge Clip, 8.0" Length, EC4A, Outside Serrated, PA66HS, Black, 500/bag

### Product Dimensions

**Minimum Tensile Strength (imperial)** 50.0 lbs

**Minimum Tensile Strength (N)** 225 N

**Length L (imperial)** 8.0 "

**Length L (metric)** 200.0 mm

**Length L2 (imperial)** 0.55 "

**Length L2 (metric)** 14.0 mm

**Width W (imperial)** 0.18 "

**Width W (metric)** 4.6 mm

**Width W2 (imperial)** 0.45 "

**Width W2 (metric)** 11.5 mm

**Height H (imperial)** 0.05 "

**Height H (metric)** 1.3 mm

**Height H2 (imperial)** 0.43 "

**Height H2 (metric)** 10.8 mm

**Bundle Diameter min (imperial)** 0.16 "

**Bundle Diameter min (metric)** 4.0 mm

**Bundle Diameter max (imperial)** 1.8 "

**Bundle Diameter max (metric)** 45.0 mm

**Panel Thickness max. (imperial)** 0.12 "

**Panel Thickness max. (metric)** 3.0 mm

**Panel Thickness min. (imperial)** 0.04 "

**Panel Thickness min. (metric)** 1.0 mm

**Thickness T (imperial)** 0.05 "

**Thickness T (Metric)** 1.2 mm

## Logistics and Packaging

---

**Quantity per** bag

**Package Quantity** 500

**Weight (Metric)** 4.5 kg

## Material and Specifications

---

**Material** Polyamide 6.6 heat stabilized (PA66HS)

Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

**Material Shortcut** PA66HS

PA66HIRHS

**Material Cable Tie** Polyamide 6.6 heat stabilized (PA66HS)

**Material Edge Clip** Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

**Flammability** UL94 HB

**Operating Temperature** -40°F to +221°F (-40°C to +105°C)

**ROHS Conformity** Yes