


PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	EXPANDED WIRE RANGE***	BARREL		OVERALL LENGTH "A" ± .12	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS			
			I.D. ± .01	O.D. ± .01			CT-720	CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2920, CT-2940*	CT-2001	CT-2950**, CT-2980, CT-980, CT-980CH
SCS300-X	300 kcmil	#2/0-300 kcmil	.65	.81	2.25	1-1/16	CD-720-4 WHITE P66 2 CRIMPS	CD-920-300 WHITE P66 2 CRIMPS	CD-2001-300 WHITE P66 2 CRIMPS	STD 2 CRIMPS
SCS350-X	350 kcmil	#3/0-350 kcmil	.70	.87	2.37	1-1/8	CD-720-5 RED P71 2 CRIMPS	CD-920-350 RED P71 2 CRIMPS	CD-2001-350 RED P71 2 CRIMPS	STD 2 CRIMPS
SCS400-6	400 kcmil	#4/0-400 kcmil	.76	.95	2.50	1-3/16	CD-720-6 BLUE P76 2 CRIMPS	CD-920-400 BLUE P76 2 CRIMPS	CD-2001-400 BLUE P76 3 CRIMPS	STD 2 CRIMPS
SCS500-6	500 kcmil	#4/0-500 kcmil	.83	1.05	2.87	1-3/8	CD-720-7 BROWN P87 2 CRIMPS	CD-920-500 BROWN P87 2 CRIMPS	CD-2001-500 BROWN P87 3 CRIMPS	STD 2 CRIMPS
SCS600-6	600 kcmil	250-600 kcmil	.92	1.18	2.87	1-3/8	————	CD-920-600 GREEN P94 2 CRIMPS	————	STD 2 CRIMPS
SCS750-6	750 kcmil	500-750 kcmil	1.03	1.29	3.37	1-5/8	————	CD-920-750 CD-940-750*** BLACK P106 2 CRIMPS	————	STD 2 CRIMPS
SCS1000-3	1000 kcmil	————	1.17	1.50	3.87	1-7/8	————	CD-940-1000*** WHITE P125 2 CRIMPS	————	————



- NOTES:
1. MATERIAL – HIGH CONDUCTIVITY SEAMLESS COPPER TUBING.
 2. ELECTRO-TIN PLATED.
 3. BARREL COLOR CODED WITH DIE SET INDEX NUMBER.
 4. UL LISTED WITH CODE COPPER CONDUCTORS FOR APPLICATIONS UP TO 35KV, FILE E52164.
 5. CONSULT CABLE MANUFACTURER FOR VOLTAGE STRESS RELIEF INSTRUCTIONS WITH APPLICATIONS GREATER THAN 2000 VOLTS.
 6. CSA CERTIFIED FOR APPLICATIONS UP TO 600V, FILE LR31212.
 7. FOR USE WITH COPPER CABLES ONLY.

* CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER
** MAX SIZE 500 MCM
*** WITH CT-980, CT-980CH, CT-2950 & CT-2980



LISTED
587H
E52164



CERTIFIED
LR31212

04	10/02	SAC		REMOVED SCS800-6 FROM DRAWING				
03	6/02	SAB	JAC	ADDED SCS800-6, UPDATED SCS750-6 & SCS1000-3 TOOL INFO., & ALL kcmils WERE MCMS	10252	JAC	LM	
02	4/01	BDK	SKB	ADDED THE LETTER "P" TO THE DIE INDEX NUMBER, ADDED CT-2950, CT-2980, CT-980 & CT-980CH, DRAWING NUMBER WAS N41135CB_PCD_01, ADDED EXPANDED WIRE RANGE	09383	JAC	RM	
01	2-94	PWS	JCJ	FILESPEC WAS C41105 / DWG WAS C41105	02060	LA	RM	
00	3-93	PWS	GRM	RELEASED	01415		KRS	
REV	DATE	BY	CHK	DESCRIPTION	ECN	CUST	PM	

CAD FILENAME/LAYERS		C41135_04	
PANDUIT CORP TINLEY PARK, ILLINOIS			
SCS STANDARD BARREL #300 THRU 1000 COPPER SPLICES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY	PWS	MAT'L:	SEE NOTES ABOVE
DATE	3-10-93	SCALE	
CHK'D	GRM	DRAWING NO.	C41135
		DWG SIZE	B SIZE