

DATA SHEET

KHS01 PLUG MOUNTED SURFACE PROBE TYPE 'K'

PLUG MOUNTED SURFACE BAND PROBE - Type 'K'

Description

The probe is designed for the measurement of surface temperatures giving a fast response time.

Construction

Ribbon band sensor with thermocouple sensor attached and draught shield : Stainless Steel 316 (Food Grade)
4mm diameter stem 100mm long.

Sensor Features

- **TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.**

This probe is manufactured using a two stage moulding technique. Firstly the probes are encased in tough nylon, then a thermoplastic over moulding is applied. This gives an extremely robust and durable construction with the added benefit that the assembly is waterproof.

- **HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT**

Type 'K' Thermocouple : Class I ($\pm 0.5^\circ\text{C} \pm 0.25\%$)

- **WIDE AMBIENT TEMPERATURE SPECIFICATION** : -30 TO 50°C
- **TIME RESPONSE** (*96% of value on clean metal*) : **0.1 Secs**
- **MEASUREMENT RANGE** : -100 TO 750°C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY