




NOTES:

1. ALL DIMENSIONS ARE IN INCHES (MILLIMETERS).
2. SLEEVE MATERIAL: RYNITE FR530 (UL94V-1 MINIMUM, UL94V-0 PREFERRED)
3. BASE MATERIAL: SHELL (BODY) IS MADE FROM BRASS WITH NICKEL-PLATED (BARREL)
4. OPERATING TEMPERATURE: $\sim -30^{\circ}\text{C}$ to $\sim +50^{\circ}\text{C}$

RoHS
COMPLIANT
2002/95/EC

REVISION NOTIFICATION

- ☐ DLC
- ☐ UL/ETL
- ☐ MADE IN USA
- ☐ CUSTOMER _____
- ☐ OTHER _____

ELECTRICAL - OPTICAL CHARACTERISTICS ($T_a = 25^{\circ}\text{C}$)

B3127CG6-0014	B3127CG6-48V-BP	HI-EFF GREEN	48Vdc	0.018 A	0.86W	0.680cd	566	60°
B3127CR6-0007	B3127CR6-48V/20-BP	ULTRA RED	48Vdc	0.018 A	-	-	654	60°
B3127CW5-0012	B3127CW5-48V-BP	PALE WHITE (Rd-Gn)	48Vdc	0.018 A	-	-	642/565	60°
B3127CY6-0003	B3127CR6-48V/15-BP	SUPER YELLOW/YELLOW	48Vdc	0.018 A	-	-	595/585	45°
LEDTRONICS PART NO.	DESCRIPTION PART NO.	COLOR EMITTED	INPUT VOLTAGE, V	CURRENT (A)	POWER (W)	MAXIMUM CANDELA	λ_P nm	VIEWING ANGLE (FULL BEAM WIDTH @ 50% INTENSITY)

LED[®]
LEDTRONICS, INC.[™]
23105 KASHIWA COURT
TORRANCE, CA 90505

-PROPRIETARY-
This document contains Proprietary
information of LEDTRONICS, INC.
It may not be copied, used or disclosed
for any purpose without the prior express
written consent of LEDTRONICS, INC.

.XXX $\pm$.010 TOLERANCE PER ANSI-Y14.5
.XX $\pm$.025 (UNLESS OTHERWISE STATED)
ANGLES $\pm$ 0°,30'
FRACT. $\pm$ 1/32

TITLE

B3127CXX-00XX
(B3127CXX-48V-BP)

DWG NO

B3127-48V-BP

SCALE

1:1

SHEET

1 OF 1

DATE

02-03-16

CODE
IDENT NO.
8Z410

DWG BY
GP
02-03-16

CHK BY
PL
02-04-16

QA

MFG

R&D
LUV
02-03-16