

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15-38-8088](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: 2.54mm SL™ Single Row, Female, Version A Receptacle, 8 Circuits

Documents:
[3D Model](#) [Product Specification PS-70430 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19880
UL E29179

General

Product Family FFC/FPC Connectors
Series [70430](#)
Overview [C-Grid® Products](#)
Product Name SL™
UPC 800753773950

Physical

Circuits (Loaded) 8
Color - Resin Black
Contact Position N/A
Durability (mating cycles max) 25
Entry Angle Vertical
Flammability 94V-0
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester Alloy
Net Weight 1.119/g
Number of Rows 1
Orientation Vertical
PC Tail Length 3.30mm
PCB Retention None
PCB Thickness - Recommended 1.60mm, 2.40mm
Packaging Type Tube
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 3.810µm
Plating min - Termination 1.905µm
Polarized to PCB No
Stackable Yes
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style IDT or Pierce
Wire/Cable Type FFC/FPC

Electrical


Current - Maximum per Contact 1A, 2A
Voltage - Maximum 250V

Material Info

Old Part Number 70430-0007

Reference - Drawing Numbers

Product Specification PS-70430



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[70430Series](#)

Mates With

2.54mm Pitch, Single or Dual Row,
Breakaway Headers

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Tool Kit for Standard	0622007400
Manual Press FFC	
Standard Manual	0622007800
Press for FFC	
TM-42™ Termination	0622018700
Kit	
Manual Ribbon	0638170100
Cable Cutter Hand	
Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com