


Datasheet Crimp Housings

[[Home](#) > [Products](#) > [Crimp Housings](#) > Datasheet]

09-50-8043

3.96mm (.156") Pitch KK® Crimp Terminal Housing, Friction Ramp, 4 Circuits



[View all parts in series 41695](#)

[2D Dimensions](#)

[E-mail this page](#)

[Samples](#)

[Buy](#)

This part is
ELV and RoHS
COMPLIANT

ENVIRONMENT

[RoHS Compliant](#) Yes

Features and Benefits

- Locking ramp feature available
- Polarizing rib feature available for side-to-side polarization
- Offset pin entry holes provide 180° polarization
- Accepts entire line of .156" contacts
- Optional voids available

RELATED PRODUCTS

[Use With](#) 2478, 2578, 6438, 6838, 7258, 8818

[Polarized to Mating Part](#) Yes

[Lock to Mating Part](#) Friction Ramp

M E C H A N I C A L

Contact Insertion Force-max. (per circuit) **17.8N (4.00lb)**

P H Y S I C A L

[Housing Material](#) PBT Polyester

[Flammability](#) UL 94V-0

[Temperature Range](#) 0°C to +75°C

R E F E R E N C E

[Product Specification](#) PS-08-50

[Packaging](#) Bag

[UL File Number](#) E29179

[CSA File Number](#) LR19980

[MX01 Catalog Page](#) D-6

[990 Catalog Page](#) J-64

[Old Part Number](#) 41695-N-D04

[Molex Series](#) 41695

[Overview](#) Molex Products[-8390]

2D D R A W I N G - For reference only. See technical Drawing (PDF) for design-in purposes.

D I M E N S I O N S




[Designed In](#) Inches

[Dimension A \(Overall Length\)](#) 16.72mm (.658")

[Dimension B \(First-to-Last\)](#) 11.89mm (.468")

Circuit)

First
Contact to
End
2.41mm
(.095")



© Copyright 2005 Molex Incorporated
0.59 secs