

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V _{DSS}	-12	V
Gate-Source Voltage			V _{GSS}	±8	V
Continuous Drain Current V _{GS} = -4.5V (Note 10)	Steady State	T _C = +25°C T _C = +70°C	I _D	-20 -16	A
	t < 5s (Note 6)	T _A = +25°C	I _D	-12.6	A
Pulsed Drain Current (10μs Pulse, Duty Cycle = 1%)			I _{DM}	-55	A
Maximum Body Diode Continuous Current (Note 6)			I _S	-2.8	A
Avalanche Current (Note 7), L = 0.1mH			I _{AS}	-21	A
Avalanche Energy (Note 7), L = 0.1mH			E _{AS}	22	mJ

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	P _D	0.72	W
	T _A = +70°C		0.46	
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	R _{θJA}	172	°C/W
	t < 5s		130	
Total Power Dissipation (Note 6)	T _A = +25°C	P _D	2.11	W
	T _A = +70°C		1.36	
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	R _{θJA}	59	°C/W
	t < 5s		44	
Thermal Resistance, Junction to Case (Note 6)	Steady State	R _{θJC}	9.0	
Operating and Storage Temperature Range		T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	-12	—	—	V	V _{GS} = 0V, I _D = -250μA
Zero Gate Voltage Drain Current	I _{DSS}	—	—	-1	μA	V _{DS} = -10V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	—	—	±100	nA	V _{GS} = ±8V, V _{DS} = 0V
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	V _{GS(TH)}	-0.3	-0.5	-0.9	V	V _{DS} = V _{GS} , I _D = -250μA
Static Drain-Source On-Resistance	R _{DS(ON)}	—	11	15	mΩ	V _{GS} = -4.5V, I _D = -5A
			12	20		V _{GS} = -3.7V, I _D = -5A
			15	30		V _{GS} = -2.5V, I _D = -4A
			20	40		V _{GS} = -1.8V, I _D = -1A
Diode Forward Voltage	V _{SD}	—	-0.8	-1.2	V	V _{GS} = 0V, I _S = -10A
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C _{iss}	—	1344	—	pF	V _{DS} = -10V, V _{GS} = 0V, f = 1.0MHz
Output Capacitance	C _{oss}	—	342	—		
Reverse Transfer Capacitance	C _{rss}	—	297	—		
Gate Resistance	R _g	—	15	—	Ω	V _{DS} = 0V, V _{GS} = 0V, f = 1MHz
Total Gate Charge (V _{GS} = -4.5V)	Q _g	—	19.5	—	nC	V _{DS} = -6V, I _D = -10A
Total Gate Charge (V _{GS} = -8V)	Q _g	—	31	—		
Gate-Source Charge	Q _{gs}	—	2.1	—		
Gate-Drain Charge	Q _{gd}	—	7.9	—		
Turn-On Delay Time	t _{D(ON)}	—	6.0	—	ns	V _{DS} = -6V, V _{GS} = -4.5V, R _g = 1Ω, I _D = -8A
Turn-On Rise Time	t _R	—	32	—		
Turn-Off Delay Time	t _{D(OFF)}	—	71	—		
Turn-Off Fall Time	t _F	—	85	—		
Reverse Recovery Time	t _{RR}	—	46	—	ns	I _F = -12A, di/dt = 500A/μs
Reverse Recovery Charge	Q _{RR}	—	44	—	nC	

- Notes:
- Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
 - Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
 - I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep T_J = +25°C.
 - Short duration pulse test used to minimize self-heating effect.
 - Guaranteed by design. Not subject to product testing.
 - Package limited.




Figure 1. Typical Output Characteristic




Figure 2. Typical Transfer Characteristic




Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 4. Typical Transfer Characteristic




Figure 5. Typical On-Resistance vs. Drain Current and Temperature




Figure 6. On-Resistance Variation with Temperature




Figure 7. On-Resistance Variation with Temperature




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 10. Typical Junction Capacitance




Figure 11. Gate Charge




Figure 12. SOA, Safe Operation Area





Figure 13. Transient Thermal Resistance

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2020-6 (Type F)




U-DFN2020-6 (Type F)			
Dim	Min	Max	Typ
A	0.57	0.63	0.60
A1	0.00	0.05	0.03
A3	-	-	0.15
b	0.25	0.35	0.30
D	1.95	2.05	2.00
D2	0.85	1.05	0.95
D2a	0.33	0.43	0.38
E	1.95	2.05	2.00
E2	1.05	1.25	1.15
E2a	0.65	0.75	0.70
e	0.65 BSC		
e2	0.863 BSC		
e3	0.70 BSC		
e4	0.325 BSC		
k	0.37 BSC		
k1	0.15 BSC		
k2	0.36 BSC		
L	0.225	0.325	0.275
z	0.20 BSC		
z1	0.110 BSC		
z2	0.20 BSC		
All Dimensions in mm			

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

U-DFN2020-6 (Type F)



Dimensions	Value (in mm)
C	0.650
X	0.400
X1	0.480
X2	0.950
X3	1.700
Y	0.425
Y1	0.800
Y2	1.150
Y3	1.450
Y4	2.300

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com