

**Cable glands
VG 16-MS54-ZE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Cable gland with external concentric strain relief
(clamping jaws), IP 54

General ordering data

Type	VG 16-MS54-ZE
Order No.	1718840000
Version	cable glands, Brass, nickel-plated, External thread: PG 16
GTIN (EAN)	4008190352066
Qty.	50 pc(s).

Cable glands VG 16-MS54-ZE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	33 mm	Net weight	55.4 g
--------	-------	------------	--------

General information

AF size 1	24 mm	AF size 2	27 mm
Cable gland	PG	Clamping range, max.	15 mm
Clamping range, min.	6.5 mm	Clamping range, strain relief, max.	17 mm
Clamping range, strain relief, min.	9.5 mm	External thread	PG 16
Length of thread	6.5 mm	Material	Brass, nickel-plated
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Protection degree with GWDR	IP 65	Seal insert	NBR
Torque for cap nut, max.	5 Nm	Torque for cap nut, min.	5 Nm
Torque for connecting adapter, max.	7.5 Nm	Torque for connecting adapter, min.	7.5 Nm

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
Descriptive text technical data	Optional sealing ring Length "L" varies depending on the cable diameter used.
Descriptive text accessories	For cable gland tools see the chapter "Tools", p. N.81

Approvals

Approvals



ROHS	Conform
------	---------