



1305




1305-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole

1306




1306-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole.

7305




7305-0-15-XX-47-XX-10-0
Solder mount in .060 min. mounting hole
Also available on 24mm wide carrier
tape: 1,500 parts per 13" reel.
Order as: 7305-0-57-XX-47-XX-10-0

0400




0400-0-15-XX-47-XX-04-0
Press-fit in .067 mounting hole.

0335




0335-0-15-XX-47-XX-04-0
Hex press-fit in .064
plated thru hole

4614




4614-0-31-XX-47-XX-04-0
Compliant press-fit in .040±.003 plated
hole. For .060→.100 thick board.

4615




4615-0-31-XX-47-XX-04-0
Compliant press-fit in .040±.003 plated
hole. For .090→.130 thick board.

7614




7614-0-31-XX-47-XX-04-0
Compliant press-fit in .040±.003 plated
hole. For .060→.100 thick board.

8401




8401-0-15-XX-47-XX-04-0
Hex press-fit in .063
plated thru hole

2400




2400-0-15-XX-47-XX-04-0
Press-fit in .066 mounting hole.

6857



6857-0-15-XX-47-XX-10-0
Press-fit in .061 mounting hole.

9393



9393-0-15-XX-47-XX-10-0
Press-fit in .067 mounting hole.

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - 47 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
27 30μ" GOLD OVER NICKEL



CONTACT

#47 CONTACT (DATA ON PAGE 221)