

## I.D. PRO *Plus*®, Brady LS2000 and BradyMarker™ XC Plus Labels


### PRINTER MODEL

**PRO** = ID PRO/PRO Plus

**LS** = LS2000

**BMXC** = BradyMarker XC Plus

**ALL** = All ID PRO, LS2000, BMXC



For use on components in control panels, electronic components and circuit boards, faceplates and electronic receptacles.



### COMPONENT AND GENERAL IDENTIFICATION LABELS

| Part Number | Portable Printer Model | Labels Per Roll | Label Material        | Label Width Inch (mm)<br>A | Label Height Inch (mm)<br>B | Maximum Lines of Print<br>(PRO/LS) | Maximum Characters Across Large<br>(PRO/LS) | Maximum Characters Across Small<br>(PRO/LS) |
|-------------|------------------------|-----------------|-----------------------|----------------------------|-----------------------------|------------------------------------|---------------------------------------------|---------------------------------------------|
| CL-105-499  | ALL                    | 500             | Nylon Cloth           | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-502  | ALL                    | 500             | Vinyl Cloth           | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-607  | ALL                    | 500             | Tamper-Proof Vinyl    | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-619  | ALL                    | 500             | Polyester             | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-621  | ALL                    | 500             | Translucent Polyester | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-652  | ALL                    | 500             | Polyimide             | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-105-969  | ALL                    | 500             | Metallized Polyester  | 0.500 (12.70)              | 0.275 (7.00)                | 1/1                                | 3/3                                         | 4/7                                         |
| CL-0807-619 | LS                     | 500             | Polyester             | 0.500 (12.70)              | 0.500 (12.70)               | 4                                  | 3                                           | 7                                           |
| CL-0807-969 | LS                     | 500             | Metallized Polyester  | 0.500 (12.70)              | 0.500 (12.70)               | 4                                  | 3                                           | 7                                           |
| CL-0309-502 | LS                     | 500             | Vinyl Cloth           | 0.650 (16.51)              | 0.187 (4.75)                | 1                                  | 4                                           | 9                                           |
| CL-0309-619 | LS                     | 500             | Polyester             | 0.650 (16.51)              | 0.187 (4.75)                | 1                                  | 4                                           | 9                                           |
| CL-0311-619 | LS                     | 500             | Polyester             | 0.800 (20.32)              | 0.200 (5.08)                | 1                                  | 5                                           | 11                                          |
| CL-0311-652 | LS                     | 500             | Polyimide Film        | 0.800 (20.32)              | 0.200 (5.08)                | 1                                  | 5                                           | 11                                          |
| CL-0411-502 | LS                     | 500             | Vinyl Cloth           | 0.750 (19.05)              | 0.250 (6.35)                | 2                                  | 5                                           | 11                                          |
| CL-0411-619 | LS                     | 500             | Polyester             | 0.750 (19.05)              | 0.250 (6.35)                | 2                                  | 5                                           | 11                                          |
| CL-0411-652 | LS                     | 500             | Polyimide Film        | 0.750 (19.05)              | 0.250 (6.35)                | 2                                  | 5                                           | 11                                          |
| CL-0411-969 | LS                     | 500             | Metallized Polyester  | 0.750 (19.05)              | 0.250 (6.35)                | 2                                  | 5                                           | 11                                          |
| CL-0413-619 | LS                     | 500             | Polyester             | 0.900 (22.86)              | 0.250 (6.35)                | 2                                  | 6                                           | 13                                          |
| CL-0413-652 | LS                     | 500             | Polyimide             | 0.900 (22.86)              | 0.250 (6.35)                | 2                                  | 6                                           | 13                                          |
| CL-111-122  | ALL                    | 500             | Paper                 | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-499  | ALL                    | 500             | Nylon Cloth           | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-502  | ALL                    | 500             | Vinyl Cloth           | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-607  | ALL                    | 500             | Tamper-Proof Vinyl    | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-619  | ALL                    | 500             | Polyester             | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-621  | ALL                    | 500             | Translucent Polyester | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-637  | ALL                    | 500             | Tedlar®               | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-652  | ALL                    | 500             | Polyimide             | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-111-969  | ALL                    | 500             | Metallized Polyester  | 1.000 (25.40)              | 0.275 (7.00)                | 1/1                                | 7/7                                         | 10/15                                       |
| CL-0423-502 | LS                     | 500             | Vinyl Cloth           | 1.500 (38.10)              | 0.250 (6.35)                | 2                                  | 11                                          | 23                                          |
| CL-0423-619 | LS                     | 500             | Polyester             | 1.500 (38.10)              | 0.250 (6.35)                | 2                                  | 11                                          | 23                                          |
| CL-0423-652 | LS                     | 500             | Polyimide Film        | 1.500 (38.10)              | 0.250 (6.35)                | 2                                  | 11                                          | 23                                          |
| CL-117-499  | ALL                    | 500             | Nylon Cloth           | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-502  | ALL                    | 500             | Vinyl Cloth           | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-619  | ALL                    | 500             | Polyester             | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-621  | ALL                    | 500             | Translucent Polyester | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-637  | ALL                    | 500             | Tedlar                | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-652  | ALL                    | 500             | Polyimide             | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-117-969  | ALL                    | 500             | Metallized Polyester  | 1.500 (38.10)              | 0.275 (7.00)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-0431-502 | LS                     | 500             | Vinyl Cloth           | 2.000 (50.80)              | 0.250 (6.35)                | 1/1                                | 10/11                                       | 15/23                                       |
| CL-0431-619 | LS                     | 500             | Polyester             | 2.000 (50.80)              | 0.250 (6.35)                | 2                                  | 15                                          | 31                                          |
| CL-0431-652 | LS                     | 500             | Polyimide Film        | 2.000 (50.80)              | 0.250 (6.35)                | 2                                  | 15                                          | 31                                          |
| CL-0431-969 | LS                     | 500             | Metallized Polyester  | 2.000 (50.80)              | 0.250 (6.35)                | 2                                  | 15                                          | 31                                          |
| CL-211-499  | ALL                    | 500             | Nylon Cloth           | 1.000 (25.40)              | 0.400 (10.16)               | 2/2                                | 7/7                                         | 10/15                                       |
| CL-211-502  | ALL                    | 500             | Vinyl Cloth           | 1.000 (25.40)              | 0.400 (10.16)               | 2/2                                | 7/7                                         | 10/15                                       |
| CL-211-619  | ALL                    | 500             | Polyester             | 1.000 (25.40)              | 0.400 (10.16)               | 2/2                                | 7/7                                         | 10/15                                       |
| CL-211-621  | ALL                    | 500             | Translucent Polyester | 1.000 (25.40)              | 0.400 (10.16)               | 2/2                                | 7/7                                         | 10/15                                       |

Tedlar® is a registered trademark of DuPont.