


## Phase Control SCR TO-220AB FULL-PAK, 25 A



TO-220AB FULL-PAK



### DESCRIPTION/FEATURES

The 25TTS...FPPbF High Voltage Series of silicon controlled rectifiers are specifically designed for medium power switching and phase control applications. The glass passivation technology used has reliable operation up to 140 °C junction temperature.



**RoHS\***  
COMPLIANT

Typical applications are in input rectification (soft start) and these products are designed to be used with Vishay HPP input diodes, switches and output rectifiers which are available in identical package outlines. Fully isolated package ( $V_{INS} = 2500 V_{RMS}$ ); plastic material 94V<sub>Ro</sub>.

This product has been designed and qualified for industrial level and lead (Pb)-free ("PbF" suffix).

### PRODUCT SUMMARY

$V_T$ at 16 A	< 1.25 V
$I_{TSM}$	200 A
$V_{RRM}$	800/1200 V

### OUTPUT CURRENT IN TYPICAL APPLICATIONS

APPLICATIONS	SINGLE-PHASE BRIDGE	THREE-PHASE BRIDGE	UNITS
Capacitive input filter $T_A = 55\text{ °C}$ , $T_J = 125\text{ °C}$ , common heatsink of 1 °C/W	18	22	A

### MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{T(AV)}$	Sinusoidal waveform	16	A
$I_{RMS}$		25	
$V_{RRM}/V_{DRM}$		800/1200	V
$I_{TSM}$		300	A
$V_T$	16 A, $T_J = 25\text{ °C}$	1.25	V
$dV/dt$		500	V/ $\mu$ s
$dI/dt$		150	A/ $\mu$ s
$T_J$		- 40 to 125	°C

### VOLTAGE RATINGS

PART NUMBER	$V_{RRM}$ , MAXIMUM PEAK REVERSE VOLTAGE V	$V_{DRM}$ , MAXIMUM PEAK DIRECT VOLTAGE V	$I_{RRM}/I_{DRM}$ AT 125 °C mA
25TTS08FPPbF	800	800	10
25TTS12FPPbF	1200	1200	

\* Pb containing terminations are not RoHS compliant, exemptions may apply

# 25TTS...FPPbF High Voltage Series



Vishay High Power Products Phase Control SCR  
TO-220AB FULL-PAK, 25 A

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES		UNITS
			TYP.	MAX.	
Maximum average on-state current	$I_{T(AV)}$	$T_C = 85\text{ }^{\circ}\text{C}$ , 180° conduction half sine wave	16		A
Maximum RMS on-state current	$I_{RMS}$		25		
Maximum peak, one-cycle, non-repetitive surge current	$I_{TSM}$	10 ms sine pulse, rated $V_{RRM}$ applied	300		
		10 ms sine pulse, no voltage reapplied	350		
Maximum $I^2t$ for fusing	$I^2t$	10 ms sine pulse, rated $V_{RRM}$ applied	450		$A^2s$
		10 ms sine pulse, no voltage reapplied	630		
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	$t = 0.1$ to 10 ms, no voltage reapplied	6300		$A^2\sqrt{s}$
Maximum on-state voltage drop	$V_{TM}$	16 A, $T_J = 25\text{ }^{\circ}\text{C}$	1.25		V
On-state slope resistance	$r_t$	$T_J = 125\text{ }^{\circ}\text{C}$	12.0		$m\Omega$
Threshold voltage	$V_{T(TO)}$		1.0		V
Maximum reverse and direct leakage current	$I_{RM}/I_{DM}$	$T_J = 25\text{ }^{\circ}\text{C}$	$V_R = \text{Rated } V_{RRM}/V_{DRM}$		mA
		$T_J = 125\text{ }^{\circ}\text{C}$			
Holding current	$I_H$	Anode supply = 6 V, resistive load, initial $I_T = 1$ A	-	100	
Maximum latching current	$I_L$	Anode supply = 6 V, resistive load	200		
Maximum rate of rise of off-state voltage	$dV/dt$		500		$V/\mu s$
Maximum rate of rise of turned-on current	$dI/dt$		150		$A/\mu s$

TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum peak gate power	$P_{GM}$		8.0		W
Maximum average gate power	$P_{G(AV)}$		2.0		
Maximum peak positive gate current	$+I_{GM}$		1.5		A
Maximum peak negative gate voltage	$-V_{GM}$		10		V
Maximum required DC gate current to trigger	$I_{GT}$	Anode supply = 6 V, resistive load, $T_J = -10\text{ }^{\circ}\text{C}$	60		mA
		Anode supply = 6 V, resistive load, $T_J = 25\text{ }^{\circ}\text{C}$	45		
		Anode supply = 6 V, resistive load, $T_J = 125\text{ }^{\circ}\text{C}$	20		
Maximum required DC gate voltage to trigger	$V_{GT}$	Anode supply = 6 V, resistive load, $T_J = -10\text{ }^{\circ}\text{C}$	2.5		V
		Anode supply = 6 V, resistive load, $T_J = 25\text{ }^{\circ}\text{C}$	2.0		
		Anode supply = 6 V, resistive load, $T_J = 125\text{ }^{\circ}\text{C}$	1.0		
Maximum DC gate voltage not to trigger	$V_{GD}$	$T_J = 125\text{ }^{\circ}\text{C}$ , $V_{DRM} = \text{Rated value}$	0.25		mA
Maximum DC gate current not to trigger	$I_{GD}$		2.0		

SWITCHING					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Typical turn-on time	$t_{gt}$	$T_J = 25\text{ }^{\circ}\text{C}$	0.9		$\mu s$
Typical reverse recovery time	$t_{rr}$	$T_J = 125\text{ }^{\circ}\text{C}$	4		
Typical turn-off time	$t_q$		110		



## 25TTS...FPPbF High Voltage Series

Phase Control SCR  
TO-220AB FULL-PAK, 25 A

Vishay High Power Products

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>		- 40 to 125	°C
Maximum thermal resistance, junction to case	R <sub>thJC</sub>	DC operation	1.5	°C/W
Maximum thermal resistance, junction to ambient	R <sub>thJA</sub>		62	
Typical thermal resistance, case to heatsink	R <sub>thCS</sub>	Mounting surface, smooth and greased	1.5	
Approximate weight			2	g
			0.07	oz.
Mounting torque	minimum		6 (5)	kgf · cm (lbf · in)
	maximum		12 (10)	
Marking device		Case style TO-220AB FULL-PAK (94/V0)	25TTS08FP	
			25TTS12FP	

# 25TTS...FPPbF High Voltage Series

Vishay High Power Products

Phase Control SCR  
TO-220AB FULL-PAK, 25 A




Fig. 1 - Current Rating Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current



## 25TTS...FPPbF High Voltage Series

Phase Control SCR  
TO-220AB FULL-PAK, 25 A

Vishay High Power Products




Fig. 7 - On-State Voltage Drop Characteristics




Fig. 8 - Thermal Impedance  $Z_{thJC}$  Characteristics




Fig. 9 - Gate Characteristics

# 25TTS...FPPbF High Voltage Series



Vishay High Power Products      Phase Control SCR  
TO-220AB FULL-PAK, 25 A

## ORDERING INFORMATION TABLE

Device code	25	T	T	S	12	FP	PbF
	1	2	3	4	5	6	7
	1	-	Current rating (25 = 25 A)				
	2	-	Circuit configuration:				
			T = Single thyristor				
	3	-	Package:				
			T = TO-220AB				
	4	-	Type of silicon:				
			Standard recovery rectifier				
	5	-	Voltage code x 100 = $V_{RRM}$				
						08 = 800 V	
						12 = 1200 V	
	6	-	FULL-PAK				
	7		• None = Standard production				
			• PbF = Lead (Pb)-free				

LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95072">http://www.vishay.com/doc?95072</a>
Part marking information	<a href="http://www.vishay.com/doc?95069">http://www.vishay.com/doc?95069</a>



### Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.