


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | MAXIMUM BUNDLE<br>DIAMETER | PACKAGE<br>QUANTITY | LENGTH =<br>L ± .3 [ 7 ] |
|------------------------|----------------------------|---------------------|--------------------------|
| MLT2LH-LP316           | 2.0" [ 51 ]                | 50                  | 7.9" [ 201 ]             |
| MLT4LH-LP316           | 4.0" [ 102 ]               | 50                  | 14.3" [ 362 ]            |
| MLT6LH-LP316           | 6.0" [ 152 ]               | 50                  | 20.5" [ 521 ]            |
| MLT8LH-LP316           | 8.0" [ 203 ]               | 50                  | 26.8" [ 679 ]            |




NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS (1112 NEWTONS) WHEN TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
.XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
.X = ±.03 [ .8 ]    ANGLES = ±2°

FULLY ROUNDED  
EDGES ALONG  
STRAP BODY

SECTION A - A  
SCALE: 8x

|                                                                                       |      |     |                                      |            |  |
|---------------------------------------------------------------------------------------|------|-----|--------------------------------------|------------|--|
| TITLE                                                                                 |      |     |                                      |            |  |
| METAL LOCKING TIE LIGHT-HEAVY SERIES<br>316 STAINLESS STEEL                           |      |     |                                      |            |  |
| CUSTOMER DRAWING                                                                      |      |     |                                      |            |  |
| ITEM REVISION NAME                                                                    |      |     | <b>PANDUIT</b>                       |            |  |
| N41127BS/04                                                                           |      |     |                                      |            |  |
| DATASET FILE NAME                                                                     |      |     | MATERIAL:                            |            |  |
| N41127BS/04                                                                           |      |     |                                      |            |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]                  |      |     | 316 STAINLESS STEEL                  |            |  |
| .x ± .1 [ 2.54 ]<br>.xx ± .01 [ .25 ]                                                 |      |     | .xxx ± .005 [ .127 ]<br>ANGLES ± 5 ° |            |  |
|  |      |     | THIRD ANGLE<br>PROJECTION            |            |  |
| DRAWING NUMBER:                                                                       |      |     | N41127BS_DC                          |            |  |
| DRAWN BY                                                                              | DATE | CHK | SCALE                                | SIZE       |  |
| JAMB                                                                                  | 6/03 | DPN | 2:1                                  | SHT 1 OF 1 |  |
|                                                                                       |      |     |                                      | A          |  |