

BXC SERIES

Load Life : 105°C 8000~12000 hours.

◆FEATURES

- High Ripple Current.
- For Electronic Ballast.
- RoHS compliance.



◆SPECIFICATIONS

Items	Characteristics																																
Category Temperature Range	-25~+105℃																																
Rated Voltage Range	160~500V.DC																																
Capacitance Tolerance	±20%(20℃,120Hz)																																
Leakage Current(MAX)	<table><tr><th>CV≤1000</th><th colspan="7">CV>1000</th></tr><tr><td>I=0.1CV+40μA (1minute) I=0.03CV+15μA (5minutes)</td><td colspan="7">I=0.04CV+100μA (1minute) I=0.02CV+25μA (5minutes)</td></tr></table>								CV≤1000	CV>1000							I=0.1CV+40μA (1minute) I=0.03CV+15μA (5minutes)	I=0.04CV+100μA (1minute) I=0.02CV+25μA (5minutes)							I=Leakage Current(μA) C=Capacitance(μF) V=Rated Voltage(V)								
CV≤1000	CV>1000																																
I=0.1CV+40μA (1minute) I=0.03CV+15μA (5minutes)	I=0.04CV+100μA (1minute) I=0.02CV+25μA (5minutes)																																
Dissipation Factor(MAX) (tanδ)	<table><tr><th>Rated Voltage (V)</th><th>160</th><th>200</th><th>250</th><th>350</th><th>400</th><th>450</th><th>500</th><th colspan="3">(20℃,120Hz)</th></tr><tr><th>tanδ</th><td>0.15</td><td>0.15</td><td>0.15</td><td>0.20</td><td>0.20</td><td>0.20</td><td>0.24</td><td colspan="3"></td></tr></table>										Rated Voltage (V)	160	200	250	350	400	450	500	(20℃,120Hz)			tanδ	0.15	0.15	0.15	0.20	0.20	0.20	0.24				
Rated Voltage (V)	160	200	250	350	400	450	500	(20℃,120Hz)																									
tanδ	0.15	0.15	0.15	0.20	0.20	0.20	0.24																										
Endurance	After life test with rated ripple current at conditions stated in the table below at 105℃, the capacitors shall meet the following requirements.																																
	<table><tr><td>Capacitance Change</td><td colspan="4">Within ±20% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td colspan="4">Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td colspan="4">Not more than the specified value.</td></tr></table>				Capacitance Change	Within ±20% of the initial value.				Dissipation Factor	Not more than 200% of the specified value.				Leakage Current	Not more than the specified value.				<table><tr><th>Case Size</th><th>Life Time (hrs)</th></tr><tr><td>8×11.5, 10×12.5</td><td>8000</td></tr><tr><td>10×16, 10×20</td><td>10000</td></tr><tr><td>φD≥12.5</td><td>12000</td></tr></table>						Case Size	Life Time (hrs)	8×11.5, 10×12.5	8000	10×16, 10×20	10000	φD≥12.5	12000
Capacitance Change	Within ±20% of the initial value.																																
Dissipation Factor	Not more than 200% of the specified value.																																
Leakage Current	Not more than the specified value.																																
Case Size	Life Time (hrs)																																
8×11.5, 10×12.5	8000																																
10×16, 10×20	10000																																
φD≥12.5	12000																																
	※500WV:10000hrs																																
Low Temperature Stability Impedance Ratio(MAX)	<table><tr><th>Rated Voltage (V)</th><th>160</th><th>200</th><th>250</th><th>350</th><th>400</th><th>450</th><th>500</th><th colspan="3">(120Hz)</th></tr><tr><th>Z(-25℃)/Z(20℃)</th><td>3</td><td>3</td><td>3</td><td>6</td><td>6</td><td>6</td><td>6</td><td colspan="3"></td></tr></table>										Rated Voltage (V)	160	200	250	350	400	450	500	(120Hz)			Z(-25℃)/Z(20℃)	3	3	3	6	6	6	6				
Rated Voltage (V)	160	200	250	350	400	450	500	(120Hz)																									
Z(-25℃)/Z(20℃)	3	3	3	6	6	6	6																										

◆MULTIPLIER FOR RIPPLE CURRENT

Frequency(Hz)		120	1k	10k	100k≤
Coefficient	1~5.6μF	0.2	0.4	0.8	1.0
	6.8~15μF	0.3	0.6	0.9	1.0
	22~82μF	0.4	0.7	0.9	1.0
	100~220μF	0.45	0.75	0.9	1.0

◆OPTION


	Code
PET Sleeve	EFC

◆PART NUMBER

□□□ Rated Voltage BXC Series □□□□□ Capacitance M Capacitance Tolerance □□□ Option □□ Lead Forming D×L Case Size

◆ **DIMENSIONS**

(mm)



◆ **STANDARD SIZE**

Size $\phi D \times L$ (mm), Ripple Current (mA r.m.s./105°C, 100kHz)

V.DC Cap(μF)	160(2C)		200(2D)		250(2E)		350(2V)	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
4.7					8×11.5	160	10×12.5	150
5.6							10×12.5	180
6.8					10×12.5	250	10×16	280
10	10×16	320	10×16	320	10×16	320	10×20	350
22	10×20	500	10×20	500	10×16 10×20	470 500	12.5×20	650
33	10×20	650	10×20	650	12.5×16 12.5×20	760 800	16×20	900
47	10×20	750	12.5×20	980	12.5×20	980	16×20	1080
56					12.5×20 18×16	1080 960		
68	12.5×20	1180	12.5×25 16×20	1300	12.5×25 16×20	1300	18×25	1470
82			16×20	1380	12.5×30 16×20	1500 1440	18×25	1530
100	12.5×25 16×20	1420	16×20	1420	16×25 18×20	1530 1440		
120					18×20	1500		
150	16×25	1890	16×25	1890	18×25	1960		
220	18×25	2370						

V.DC Cap(μF)	400(2G)		450(2W)		500(2H)	
	Size	Ripple	Size	Ripple	Size	Ripple
1	8×11.5 10×12.5	60 70				
1.5	8×11.5 10×12.5	90 100				
1.8	8×11.5 10×12.5	95 120				
2.2	8×11.5 10×12.5	95 140				
3.3	10×12.5 10×16	150 180				
4.7	10×16	220	10×16 10×20	180 220		
5.6	10×16	250	10×16 10×20	200 250		
6.8	10×16	280	10×16 10×20	230 280		
8.2			10×20	280		
10	10×20	350	10×20 12.5×16 12.5×20	330 360 450	12.5×20	320
15	12.5×20	550	12.5×20 12.5×25 16×16	450 600 600	12.5×25 16×20	440
22	12.5×25 16×20	760	12.5×25 16×20	600 730	12.5×35 16×25 18×20	560
33	16×20	900	16×20 16×25 18×20	730 980 780	16×31.5 18×25	700
47	16×25 18×20	1180	18×25	1200	18×31.5	880
68	18×25	1470				