


COIL: @ +25 °C
 RESISTANCE 700 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.5 VDC
 MUST RELEASE 8.0 VDC MAX, 15 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX
RELEASE 4 MS MAX
CONTACT STABILIZATION TIME 2.5 MS MAX
ALL OTHER REQUIREMENTS TO M39016/6-109M

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 11/19/93 CK. 11/19/93



CUST. DPL
 CUST. NO. M39016/6-109M

TYPE "HFW" RELAY

HFW1201K45M