

Automotive Transient Voltage Suppressors

High Temperature Stability and High Reliability Conditions



FEATURES

- Patented PAR[®] construction
- Available in uni-directional polarity only
- 400 W peak pulse power capability with a 10/1000 μ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Solder dip 260 °C, 40 s
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



RoHS
COMPLIANT

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, automotive and telecommunication.

MECHANICAL DATA

Case: MPG06, molded epoxy over passivated junction
Molding compound meets UL 94 V-0 flammability rating

Base P/NHE3 - RoHS compliant, high reliability/automotive grade (AEC Q101 qualified)

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

HE3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

PRIMARY CHARACTERISTICS	
V_{BR}	6.8 V to 43 V
P_{PPM}	400 W
P_D	1.0 W
I_{FSM}	40 A
T_J max.	185 °C

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	LIMIT	UNIT
Peak power dissipation with a 10/1000 μ s waveform ⁽¹⁾ (Fig. 1)	P_{PPM}	400	W
Peak pulse current with a 10/1000 μ s waveform ⁽¹⁾⁽²⁾ (Fig. 3)	I_{PPM}	See next table	A
Power dissipation on infinite heatsink at $T_L = 75$ °C (Fig. 5)	P_D	1.0	W
Peak forward surge current 8.3 ms single half sine-wave ⁽²⁾	I_{FSM}	40	A
Maximum instantaneous forward voltage at 25 A ⁽²⁾	V_F	3.5	V
Operating junction and storage temperature range	T_J, T_{STG}	- 65 to + 185	°C

Notes:

(1) Non-repetitive current pulse, per Fig. 3 and derated above $T_A = 25$ °C per Fig. 2

(2) Measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum

ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DEVICE TYPE	MAXIMUM BREAKDOWN VOLTAGE $V_{BR}^{(1)}$ AT I_T (V)		TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA)	REVERSE LEAKAGE AT V_{WM} $T_J = 150\text{ }^{\circ}\text{C}$ I_D (μA)	PEAK PULSE CURRENT $I_{PPM}^{(2)}$ (A)	MAXIMUM CLAMPING VOLTAGE AT I_{PPM} V_C (V)	MAXIMUM TEMP. COEFFICIENT OF V_{BR} ($\%/^{\circ}\text{C}$)
	MIN.	MAX.							
TMPG06-6.8	6.12	7.48	10.0	5.50	300	1000	27.8	10.8	0.057
TMPG06-6.8A	6.45	7.14	10.0	5.80	300	1000	28.6	10.5	0.057
TMPG06-7.5	6.75	8.25	10.0	6.05	150	500	25.6	11.7	0.060
TMPG06-7.5A	7.13	7.88	10.0	6.40	150	500	26.5	11.3	0.061
TMPG06-8.2	7.38	9.02	10.0	6.63	50.0	200	24.0	12.5	0.065
TMPG06-8.2A	7.79	8.61	10.0	7.02	50.0	200	24.8	12.1	0.065
TMPG06-9.1	8.19	10.0	1.0	7.37	10.0	50.0	21.7	13.8	0.068
TMPG06-9.1A	8.65	9.55	1.0	7.78	10.0	50.0	22.4	13.4	0.068
TMPG06-10	9.00	11.0	1.0	8.10	5.0	20.0	26.7	15.0	0.073
TMPG06-10A	9.50	10.5	1.0	8.55	5.0	20.0	27.6	14.5	0.073
TMPG06-11	9.90	12.1	1.0	8.92	2.0	10.0	24.7	16.2	0.075
TMPG06-11A	10.5	11.6	1.0	9.40	2.0	10.0	25.6	15.6	0.075
TMPG06-12	10.8	13.2	1.0	9.72	1.0	5.0	23.1	17.3	0.076
TMPG06-12A	11.4	12.6	1.0	10.2	1.0	5.0	24.0	16.7	0.078
TMPG06-13	11.7	14.3	1.0	10.5	1.0	5.0	21.1	19.0	0.081
TMPG06-13A	12.4	13.7	1.0	11.1	1.0	5.0	22.0	18.2	0.081
TMPG06-15	13.5	16.3	1.0	12.1	1.0	5.0	18.2	22.0	0.084
TMPG06-15A	14.3	15.8	1.0	12.8	1.0	5.0	18.9	21.2	0.084
TMPG06-16	14.4	17.6	1.0	12.9	1.0	5.0	17.0	23.5	0.086
TMPG06-16A	15.2	16.8	1.0	13.6	1.0	5.0	17.8	22.5	0.086
TMPG06-18	16.2	19.8	1.0	14.5	1.0	5.0	15.1	26.5	0.088
TMPG06-18A	17.1	18.9	1.0	15.3	1.0	5.0	15.9	25.5	0.088
TMPG06-20	18.0	22.0	1.0	16.2	1.0	5.0	13.7	29.1	0.090
TMPG06-20A	19.0	21.0	1.0	17.0	1.0	5.0	14.4	27.7	0.090
TMPG06-22	19.8	24.2	1.0	17.8	1.0	5.0	12.5	31.9	0.092
TMPG06-22A	20.9	23.1	1.0	18.8	1.0	5.0	13.1	30.6	0.092
TMPG06-24	21.6	26.4	1.0	19.4	1.0	5.0	11.5	34.2	0.094
TMPG06-24A	22.8	25.2	1.0	20.5	1.0	5.0	12.0	33.2	0.094
TMPG06-27	24.3	29.7	1.0	21.8	1.0	5.0	10.2	39.1	0.096
TMPG06-27A	25.7	28.4	1.0	23.1	1.0	5.0	10.7	37.5	0.096
TMPG06-30	27.0	33.0	1.0	24.3	1.0	5.0	9.2	43.5	0.097
TMPG06-30A	28.5	31.5	1.0	25.6	1.0	5.0	9.7	41.4	0.097
TMPG06-33	29.7	36.3	1.0	26.8	1.0	5.0	8.4	47.7	0.098
TMPG06-33A	31.4	34.7	1.0	28.2	1.0	5.0	8.8	45.7	0.098
TMPG06-36	32.4	39.6	1.0	29.1	1.0	5.0	7.7	52.0	0.099
TMPG06-36A	34.2	37.8	1.0	30.8	1.0	5.0	8.0	49.9	0.099
TMPG06-39	35.1	42.9	1.0	31.6	1.0	5.0	7.1	56.4	0.100
TMPG06-39A	37.1	41.0	1.0	33.3	1.0	5.0	7.4	53.9	0.100
TMPG06-43	38.7	47.3	1.0	34.8	1.0	5.0	6.5	61.9	0.101
TMPG06-43A	40.9	45.2	1.0	36.8	1.0	5.0	6.7	59.3	0.101

Notes:

- (1) Pulse test: $t_p \leq 50\text{ ms}$
- (2) Surge current waveform per Fig. 3 and derated per Fig. 2
- (3) All terms and symbols are consistent with ANSI/IEEE C62.35



ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
TMPG06-6.8AHE3/54 ⁽¹⁾	0.218	54	5500	13" diameter paper tape and reel

Note:

(1) Automotive grade AEC Q101 qualified

RATINGS AND CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. Peak Pulse Power Rating Curve




Figure 3. Pulse Waveform




Figure 2. Pulse Power or Current vs. Initial Junction Temperature




Figure 4. Typical Junction Capacitance




Figure 5. Power Derating Curve





Figure 6. Maximum Non-Repetitive Forward Surge Current

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.