



FCIconnect.com


Copyright FCI

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 -0.10	E±0.07	G
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 -0.10
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 -0.10
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 -0.20
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 -0.20

TIN LEAD PART NUMBER	TIN LEAD PART NUMBER	LEAD FREE PART NUMBER	LEAD FREE PART NUMBER
D09P81C4GX00	D09P81C6GX00	D09P81C4GX00LF	D09P81C6GX00LF
D15P81C4GX00	D15P81C6GX00	D15P81C4GX00LF	D15P81C6GX00LF
D25P81C4GX00	D25P81C6GX00	D25P81C4GX00LF	D25P81C6GX00LF
D37P81C4GX00	D37P81C6GX00	D37P81C4GX00LF	D37P81C6GX00LF
Gold flash	0.76 µ gold	Gold flash	0.76 µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB										
ltr	ecn no	dr	date	tolerances unless otherwise specified							title MALE CONNECTOR DELTA-D EUROPE RIGHT ANGLED PRESS FIT									
J	ELX-I-18050	MP	2014/06/23	angles	linear	.0±.0.1														
						.00±.0.1														
				0°±2°		.000±.0.1				scale 2:1	dwg no C01-8646-0513									
				dr	PESSON		1996/11/06			sheet 1 of 1						size				
				engr	MITHUN PAUL		2014/06/23			A3										
				chr	ALIAS BABU		2014/06/23													
				appd	BIJU K PAUL		2014/06/23													
sheet index		revision sheet		J	1															