


Capacitor, film, 0.33 uF, +/-5% Tol, -40/+85C, Power, 750VAC



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	42	NOM
H	45	NOM
S	25	+/-0.2

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Power
Style:	Radial Box
Features:	IGBT Snubber
Termination:	Flat tab

Specifications	
Capacitance:	0.33 uF
Rated Temperature:	70C
Temperature Range:	-40/+85C
Voltage:	3000V
Voltage AC:	750VAC
Tolerance:	+/-5%
Maximum dVdT:	2068 v/us
Current/Ripple Current:	24 A (Rms)
Current/Ripple Current:	683 A (pks)
Resistance/ESR:	5.4 mOhms (@ 100 kHz)
Miscellaneous Electrical:	Kemet style A Tabs
RoHS:	Yes

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.