


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



mat'l. code NOTES 1 & 4				tolerances unless otherwise specified		CUSTOMER COPY	Electronics FCI www.fciconnect.com		
ltr	ecm no	dr	date				title	product family	code
A	V82096	EPK	11/24/98	linear	.XX ±.01/.XX±.3	projection	VERT. 2-ROW GUIDE PIN (SLOTTED)	HEADERS	—
B	V82147	EPK	12/7/98		.XXX ±.005/.XX±.13		HDR.—SOLDER TAILS POL. SPECIAL		—
C	C90014	EPK	3/18/99	angles	.XXXX ±.0020/.XXX±.051				—
D	V94423	DAI	12/8/99	dr	0° ±2°	INCH/MM			—
				enr	H.SUNDY 11/24/98	scale			—
				chr	H.SUNDY 11/24/98	1:1			—
				appd	H.SUNDY 11/24/98				—
sheet index	revision sheet	D	D						
		1	2						

ACAD

PDM: Rev:D

STATUS: Released

Printed: Apr 09, 2002

cage code
22526

Tous droits strictement reserves. Reproduction ou communication a des tiers
interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

1		2				3		4	
PRODUCT NUMBER	SIZE	TAIL LENGTH DIM H	DIM D	DIM G	DIM E	OVERALL LENGTH DIM L	PLATING	PIN OMITTED	FIRST MATE POSITION
84883-001	2 x 9	.122/3.10	NOTE 3	.37/.94+DIM D	.40/10.2+DIM D	.48/12.2+DIM D	30μ" GXT OVER 50μ"/1.27μ Ni	A1, B9	A5

NOTES :

- ① MOLDING MATERIAL : HI-TEMP RESIN
PER UL 94 V-0 COLOR : BLACK
- ② PIN RETENTION TO BE 3 LBS/1.36 KG
MIN PER PIN IN EITHER DIRECTION.
- ③ DIM D =
(NO. OF COLUMNS-1) TIMES .100(ENGLISH)
(NO. OF COLUMNS-1) TIMES 2.54(METRIC)
- ④ TERMINAL MATERIAL : 3/4/HARD PHOS BRONZE ALLOY
UNS C51000
- ⑤ FLATNESS IS MEASURED FROM THE BOTTOM
OF THE END STANDOFFS.
6. 1 THRU 4 POSITIONS ARE NOT AVAILABLE
5 THRU 100 POSITIONS ARE AVAILABLE

mat'l. code NOTES 1 & 4				tolerances unless otherwise specified		CUSTOMER COPY	FCI Electronics www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3	projection	title		
D					.XXX ±.005/.XX±.13		VERT. 2-ROW GUIDE PIN (SLOTTED)		
				angles	.XXX ±.0020/.XXX±.051		HDR.-SOLDER TAILS POL. SPECIAL		
				dr	E.KROPIEWICKI 11/24/98	INCH/MM	product family	code	
				enr	H.SUNDY 11/24/98	scale 1:1	size	dwg no	
				chr	H.SUNDY 11/24/98		A	84883	sheet
				appd	H.SUNDY 11/24/98				2 of
sheet index	revision sheet								

ACAD

PDM: Rev:D

STATUS:Released

Printed: Apr 09, 2002

cage code
22526