




(1,27 mm) .050"



CLP SERIES

LOW PROFILE DUAL WIPE SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLP

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over

50µ" (1,27 µm) Ni

Current Rating (CLP/FTSH):

3.3 A per pin

(1 pin powered per row)

Voltage Rating:

240 VAC/340 VDC

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

10 mΩ

Insertion Depth:

Top Entry = (1,40 mm) .055"

minimum, Bottom Entry =

(2,41 mm) .095" minimum

plus board thickness

DH Entry = (2,31 mm) .091"

to (2,67 mm) .105"

Insertion Force:

(Single contact only)

3.8 oz (1,05 N) average

Normal Force:

60 grams (0,59 N) average

Withdrawal Force:

(Single contact only)

2 oz (0,56 N) average

Max Cycles:

100 with 10µ" (0,25 µm) Au

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:


(0,10 mm) .004" max (02-35)

(0,15 mm) .006" max (36-50)

Mates with:
FTSH, FTS, FW



High reliability
Tiger Claw™
contacts



Suitable for pass-through
applications



CLP	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 50				-F = Gold flash on contact, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail -G = 10µ" (0,25 µm) Gold (-D only)	-D = Double Row -DH = Double Horizontal (Requires FTSH -01 lead style)	-BE = Bottom Entry (Required for bottom entry applications) -A = Alignment Pin (Not available with -PA option) (05, 06, 07, 08, 10, 12, 15, 20, 25, 30, 40 positions only) (-DH option and other sizes. Contact Samtec.) -K = (4,00 mm) .157" DIA Polyimide film Pick & Place Pad (5 positions min.) -P = Pick & Place Pad (5 positions min. -D only) (Not always necessary for auto placement. See Flex Processing.) -PA = Pick & Place Pad with Alignment Pin (-D only) (Not Available with -A option) -TR = Tape & Reel

PIN/ROW **A**

04-15	(3,56) .140
16-50	(7,11) .280

If odd pins/row, alignment pins are on middle position on centerline of the part.
If even pins/row, then alignment pins are between middle two positions.

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Single row
 - Other platings
- Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.