



NOTES

1. ALL DIMENSIONS ARE IN INCHES
[MILLIMETERS]
2. DIMENSIONS APPEARING IN TABLE
ARE AS FOLLOWS:
a - AS SUPPLIED
b - AFTER UNRESTRICTED RECOVERY
3. COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS
APPEARING IN TABLE ARE FOR UNCOATED PARTS
WHEN COATING IS ADDED, ENTRY DIAMETERS WILL
BE REDUCED BY 0.06 MAX.
4. RECOMENDED MAXIMUM PANEL THICKNESS IS 10mm



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

ORDERING INFORMATION

207W2XX -X 01 /XX -0

BASE PART NUMBER

MATERIAL DASH NUMBER

- 3 POLYOLEFIN, SEMI RIGID (RT-301)
- 4 POLYOLEFIN, FLEXIBLE (RT-1304)
- 25 ELASTOMER, FLUID RESISTANT (RT-1325)
- 100 POLYOLEFIN, SEMI FLEXIBLE, ZEROHAL (RT-1323)

MODIFICATION NUMBER

ADHESIVE SLASH NUMBER

SEE COMPATIBILITY CHART BELOW

COLOR DESIGNATOR

TABLE OF DIMENSIONS

PART NUMBER	H	J	JO	K	M	P	R	U	T	JW	Hole DIA	Torque Nm
	Ref b	Min a	Max b	Max b	Ref b	THREAD b	±10% b	±10% b	Ref b	±20% b	±0.02	
207W213-01	.47 [12.0]	.39 [10.0]	.15 [4.0]	.60 [15.3]	.90 [23.0]	.78 [20.0]	2.44 [49.0]	1.93 [10.0]	.39 [10.0]	1.25 [32.0]	.04 [1.0]	.94 [24.0]
207W223-01	.78 [20.0]	.71 [18.0]	.27 [7.0]	.76 [19.5]	1.30 [33.0]	1.18 [30.0]	2.83 [72.0]	2.32 [59.0]	.39 [10.0]	1.65 [42.0]	.07 [1.8]	1.33 [34.0]
207W234-01	1.22 [31.0]	1.10 [28.0]	.47 [12.0]	1.06 [27.0]	1.81 [46.0]	1.65 [42.0]	3.42 [87.0]	2.91 [74.0]	.39 [10.0]	2.28 [58.0]	.10 [2.5]	1.85 [47.0]
207W245-01	1.77 [45.0]	1.65 [42.0]	.71 [18.0]	1.26 [32.2]	2.34 [59.5]	2.20 [56.0]	4.01 [102.0]	3.50 [89.0]	.39 [10.0]	2.79 [71.0]	.12 [3.0]	2.38 [60.5]
207W258-01	2.67 [68.0]	2.52 [64.0]	1.18 [30.0]	1.53 [39.0]	3.30 [84.0]	3.15 [80.0]	4.80 [122.0]	4.29 [109.0]	.39 [10.0]	3.82 [97.0]	.12 [3.0]	3.34 [85.0]
207W264-01	1.57 [40.0]	1.49 [38.0]	.59 [15.0]	1.11 [28.3]	2.12 [54.0]	1.97 [50.0]	3.74 [95.0]	3.22 [82.0]	.39 [10.0]	2.62 [86.5]	.10 [2.5]	2.16 [55.0]

Raychem Molded Parts

CUSTOMER DRAWING

COMPATIBILITY CHART

MATERIAL DASH NO.	ADHESIVE (COATING) SLASH NUMBER	ADHESIVE (COATING) S NUMBER
-3	/42; /86;	S-1017 / S-1048
-4	/42; /86;	S-1017 / S-1048
-25	/86; /225	S-1048 / S-1206
-100	/86; /180	S-1048 / S-1206

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO ELECTRONICS CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO ELECTRONICS CORPORATION IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE METRIC AND
INCHES ARE IN BRACKETS.

DECIMAL TOLERANCES

XXX ± 0.13 (.005)

XX ± 0.25 (.01)

X ± 0.50 (.10)

ANGLE TOLERANCE

.X ± 1 DEG.

DRAWN
M. Mazariegos
5/28/12APPROVED
D. Hurrell
5/30/12

TE

TE Connectivity

RPN

TITLE

CAD FILE:

207W213THRU264-01

TYCO ELECTRONICS RESERVES THE RIGHT TO
AMEND THIS DRAWING AT ANY TIME. USERS
SHOULD EVALUATE THE SUITABILITY OF THE
PRODUCT FOR THEIR APPLICATION.THIRD ANGLE
PROJECTION

SIZE

CODE IDENT. NO.

DWG. NO.

B

06090

207W213THRU264-01

DO NOT SCALE THIS DRAWING

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[207W213-3-01-0](#) [207W223-3-01-0](#) [207W234-3-01/42-0](#) [207W234-3-01-0](#)