




CORE DIMENSIONS:

A	20.50 [.807]	+	0.30 [.012]
B	9.85 [.388]	+	0.15 [.006]
C	37.50 [1.476]	+	0.55 [.022]
D	9.55 [.376]	+	0.15 [.006]




CASE DIMENSIONS:

A	24.82 [.977]	+	Ref.
B	10.00 [.394]	+	Ref.
C	55.91 [2.201]	+	Ref.
D	-	+	-
E	6.50 [.256]	+	Ref.

IMPEDANCE (Z)

Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	160 Ω	348 Ω	514 Ω
Minimum	- Ω	278 Ω	- Ω

Z vs. FREQUENCY (REF. ONLY)



AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture. TEST REF. 5452

UNCONTROLLED DOCUMENT

NOTES:

1. ASSEMBLED PART #: 28A0807-0A2
2. CASE COLOR: BLACK-0A2.
3. CASE FLAMMABILITY RATING: UL94 V-2.
4. CASE MATERIAL: Halogen Free Nylon

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
REV	DESCRIPTION	DATE	INT				
E	UPDATED NOTE 3	09/15/10	JUN	PROJECT/PART NUMBER: 28A0807-0A2			
D	UPDATE COMPANY LOGO ADD NOTES 3 AND 4	01/26/09	JRK				
C	UPDATE 100MHz MINIMUM VALUE	07/16/07	TMB	DATE: 11/01/06 CAD # 28A0807-0A2-E			
B	UPDATE COMPANY LOGO	04/18/07	TMB				
A	ORIGINAL DRAFT	11/01/06	TMB	SCALE: 1:1 TOOL # -			
REV	DESCRIPTION	DATE	INT				
				REV	E	PART TYPE: FERRITE SNAP-ON	DRAWN BY: TMB
				MATERIAL: NiZn Ferrite			

Laird
TECHNOLOGIES