


Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7924A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG Bonded-Pairs stranded (7x32) tinned copper conductors, polyolefin insulation, industrial grade sunlight- and oil-resistant PVC jacket. Sequential marking at two foot intervals.

Usage (Overall)

Suitable Applications:

Industrial Ethernet Cable, Harsh Environments, 350MHz Enhanced Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, CMX - Outdoor, RJ-45 Compatible, Flexible Applications

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
4	24	7x32	TC - Tinned Copper	0.5588

Total Number of Conductors:

8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PO - Polyolefin	0.203	1.067

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
Industrial Grade PVC - Polyvinyl Chloride	0.762

Overall Cable

Overall Nominal Diameter: 6.147 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Orange Stripe & Orange
2	White/Blue Stripe & Blue
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -25°C To +75°C

Installation Temperature Range: -25°C To +75°C

Operating Temperature Range: -40°C To +75°C

Bulk Cable Weight: 38.693 Kg/Km

Max. Recommended Pulling Tension: 177.928 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR, CMX-Outdoor, UL444

CEC/C(UL) Specification: CMR

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7924A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5, ICEA 661, Category 5e Patch, UL verified to TIA/EI-568-B.2, Category 5e

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
510

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.4	65.3	65.3	62.9	20.0
4	4.8	56.3	56.3	51.5	23.0
8	6.8	51.8	51.8	45.0	24.5
10	7.7	50.3	50.3	42.6	25.0
16	9.7	47.3	47.3	37.5	25.0
20	11.0	45.8	45.8	34.8	25.0
25	12.4	44.3	44.3	31.9	24.3
31.25	13.9	42.9	42.9	29.0	23.6
62.5	20.2	38.4	38.4	18.3	21.5

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7924A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

100	26.0	35.3	35.3	9.2	20.1
155	33.2	32.5	32.5	0	19.0
200	38.4	30.8	30.8		19.0
250	43.7	29.3	29.3		18.0
300	48.6	28.2	28.2		18.0
310	49.5	27.9	27.9		18.0
350	53.2	27.2	27.2		17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.7
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.8
100	100 ± 18	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: EtherNet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7924A 0021000	1,000 FT	30.000 LB	RED	C	4 PR #24 PP PVC
7924A 0061000	1,000 FT	30.000 LB	BLUE, LIGHT	C	4 PR #24 PP PVC
7924A 0081000	1,000 FT	30.000 LB	GRAY	C	4 PR #24 PP PVC
7924A 0101000	1,000 FT	30.000 LB	BLACK	C	4 PR #24 PP PVC
7924A 0102000	2,000 FT	58.000 LB	BLACK	C	4 PR #24 PP PVC
7924A 1NH1000	1,000 FT	30.000 LB	TEAL 1NH	C	4 PR #24 PP PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 7 Revision Date: 05-30-2014

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.