









PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-.01 [0.756]
1.25-2.0 [0.049-.079]	19.4-.01 [0.764]
2.0-3.0 [0.079-.118]	19.8-.01 [0.780]



PANEL CUTOUT
NOT TO SCALE

SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
DN	NONE	DN	
1a-1	DPEN	1-1b	



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles

E-SWITCH®

			TITLE			
			R1966C BLK BLK FF			
B	11663	REVISED PART DESCRIPTION	9/18/01	CJB		
REV.	ECN NO.	DESCRIPTION	DATE	CHKD		
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED						
			SCALE	DATE	DR	DWG
			1.5:1	5/20/96	MM	M302204
						REV
						B