



|                          |               |
|--------------------------|---------------|
| $V_{DS}$                 | <b>300V</b>   |
| $R_{DS(on)}$ <b>typ.</b> | <b>25.5mΩ</b> |
| <b>max.</b>              | <b>32mΩ</b>   |
| $I_D$                    | <b>70A</b>    |

#### Applications

- High Efficiency Synchronous Rectification in SMPS
- Uninterruptible Power Supply
- High Speed Power Switching
- Hard Switched and High Frequency Circuits

#### Benefits

- Improved Gate, Avalanche and Dynamic dV/dt Ruggedness
- Fully Characterized Capacitance and Avalanche SOA
- Enhanced body diode dV/dt and dI/dt Capability
- Lead-Free



|          |          |          |
|----------|----------|----------|
| <b>G</b> | <b>D</b> | <b>S</b> |
| Gate     | Drain    | Source   |

| Base Part Number | Package Type | Standard Pack |          | Orderable Part Number |
|------------------|--------------|---------------|----------|-----------------------|
|                  |              | Form          | Quantity |                       |
| IRFP4868PbF      | TO-247AC     | Tube          | 25       | IRFP4868PbF           |

#### Absolute Maximum Ratings

| Symbol                          | Parameter                                               | Max.              | Units |
|---------------------------------|---------------------------------------------------------|-------------------|-------|
| $I_D @ T_C = 25^\circ\text{C}$  | Continuous Drain Current, $V_{GS} @ 10\text{V}$         | 70                | A     |
| $I_D @ T_C = 100^\circ\text{C}$ | Continuous Drain Current, $V_{GS} @ 10\text{V}$         | 49                |       |
| $I_{DM}$                        | Pulsed Drain Current ①                                  | 280               |       |
| $P_D @ T_C = 25^\circ\text{C}$  | Maximum Power Dissipation                               | 517               | W     |
|                                 | Linear Derating Factor                                  | 3.4               | W/°C  |
| $V_{GS}$                        | Gate-to-Source Voltage                                  | $\pm 20$          | V     |
| $T_J$                           | Operating Junction and                                  | -55 to + 175      | °C    |
| $T_{STG}$                       | Storage Temperature Range                               |                   |       |
|                                 | Soldering Temperature, for 10 seconds (1.6mm from case) | 300               |       |
|                                 | Mounting torque, 6-32 or M3 screw                       | 10lbf.in (1.1N-m) |       |

#### Avalanche Characteristics

|                              |                                 |                           |    |
|------------------------------|---------------------------------|---------------------------|----|
| $E_{AS}$ (Thermally limited) | Single Pulse Avalanche Energy ② | 1093                      | mJ |
| $I_{AR}$                     | Avalanche Current ①             | See Fig. 14, 15, 22a, 22b | A  |
| $E_{AR}$                     | Repetitive Avalanche Energy ①   |                           | mJ |

#### Thermal Resistance

| Symbol          | Parameter                          | Typ. | Max. | Units |
|-----------------|------------------------------------|------|------|-------|
| $R_{\theta JC}$ | Junction-to-Case ⑦⑧                | —    | 0.29 |       |
| $R_{\theta CS}$ | Case-to-Sink, Flat Greased Surface | 0.24 | —    | °C/W  |
| $R_{\theta JA}$ | Junction-to-Ambient                | —    | 40   |       |


**Static @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

| Symbol                          | Parameter                            | Min. | Typ. | Max. | Units               | Conditions                                            |
|---------------------------------|--------------------------------------|------|------|------|---------------------|-------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 300  | —    | —    | V                   | $V_{GS} = 0V, I_D = 250\mu A$                         |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.29 | —    | V/ $^\circ\text{C}$ | Reference to $25^\circ\text{C}$ , $I_D = 5mA$ ①       |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | 25.5 | 32   | m $\Omega$          | $V_{GS} = 10V, I_D = 42A$ ④                           |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 3.0  | —    | 5.0  | V                   | $V_{DS} = V_{GS}, I_D = 250\mu A$                     |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 20   | $\mu A$             | $V_{DS} = 300V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —    | 250  |                     | $V_{DS} = 300V, V_{GS} = 0V, T_J = 125^\circ\text{C}$ |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA                  | $V_{GS} = 20V$                                        |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -100 |                     | $V_{GS} = -20V$                                       |
| $R_G$                           | Internal Gate Resistance             | —    | 1.1  | —    | $\Omega$            |                                                       |

**Dynamic @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

| Symbol                     | Parameter                                       | Min. | Typ.  | Max. | Units | Conditions                                          |
|----------------------------|-------------------------------------------------|------|-------|------|-------|-----------------------------------------------------|
| gfs                        | Forward Transconductance                        | 80   | —     | —    | S     | $V_{DS} = 50V, I_D = 42A$                           |
| $Q_g$                      | Total Gate Charge                               | —    | 180   | 270  | nC    | $I_D = 42A$                                         |
| $Q_{gs}$                   | Gate-to-Source Charge                           | —    | 60    | —    |       | $V_{DS} = 150V$                                     |
| $Q_{gd}$                   | Gate-to-Drain ("Miller") Charge                 | —    | 57    | —    |       | $V_{GS} = 10V$ ④                                    |
| $Q_{sync}$                 | Total Gate Charge Sync. ( $Q_g - Q_{gd}$ )      | —    | 123   | —    |       | $I_D = 42A, V_{DS} = 0V, V_{GS} = 10V$              |
| $t_{d(on)}$                | Turn-On Delay Time                              | —    | 24    | —    | ns    | $V_{DD} = 195V$                                     |
| $t_r$                      | Rise Time                                       | —    | 16    | —    |       | $I_D = 42A$                                         |
| $t_{d(off)}$               | Turn-Off Delay Time                             | —    | 62    | —    |       | $R_G = 1.0\Omega$                                   |
| $t_f$                      | Fall Time                                       | —    | 45    | —    |       | $V_{GS} = 10V$ ④                                    |
| $C_{iss}$                  | Input Capacitance                               | —    | 10774 | —    | pF    | $V_{GS} = 0V$                                       |
| $C_{oss}$                  | Output Capacitance                              | —    | 612   | —    |       | $V_{DS} = 50V$                                      |
| $C_{rss}$                  | Reverse Transfer Capacitance                    | —    | 193   | —    |       | $f = 1.0\text{ MHz}$ , See Fig. 5                   |
| $C_{oss\text{ eff. (ER)}}$ | Effective Output Capacitance (Energy Related) ⑥ | —    | 406   | —    |       | $V_{GS} = 0V, V_{DS} = 0V$ to $240V$ ⑥, See Fig. 11 |
| $C_{oss\text{ eff. (TR)}}$ | Effective Output Capacitance (Time Related) ⑤   | —    | 710   | —    |       | $V_{GS} = 0V, V_{DS} = 0V$ to $240V$ ⑤              |







**Diode Characteristics**


| Symbol    | Parameter                              | Min.                                                                    | Typ. | Max. | Units | Conditions                                                                                                                                           |
|-----------|----------------------------------------|-------------------------------------------------------------------------|------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$     | Continuous Source Current (Body Diode) | —                                                                       | —    | 70   | A     | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$  | Pulsed Source Current (Body Diode) ①   | —                                                                       | —    | 280  | A     |                                                                                                                                                      |
| $V_{SD}$  | Diode Forward Voltage                  | —                                                                       | —    | 1.3  | V     | $T_J = 25^\circ\text{C}, I_S = 42A, V_{GS} = 0V$ ④                                                                                                   |
| $dv/dt$   | Peak Diode Recovery ③                  | —                                                                       | 7.3  | —    | V/ns  | $T_J = 25^\circ\text{C}, I_S = 42A, V_{DS} = 300V$                                                                                                   |
| $t_{rr}$  | Reverse Recovery Time                  | —                                                                       | 351  | —    | ns    | $T_J = 25^\circ\text{C}$                                                                                                                             |
|           |                                        | —                                                                       | 454  | —    |       | $T_J = 125^\circ\text{C}$                                                                                                                            |
| $Q_{rr}$  | Reverse Recovery Charge                | —                                                                       | 2520 | —    | nC    | $T_J = 25^\circ\text{C}$                                                                                                                             |
|           |                                        | —                                                                       | 3686 | —    |       | $T_J = 125^\circ\text{C}$                                                                                                                            |
| $I_{RRM}$ | Reverse Recovery Current               | —                                                                       | 16   | —    | A     | $T_J = 25^\circ\text{C}$                                                                                                                             |
| $t_{on}$  | Forward Turn-On Time                   | Intrinsic turn-on time is negligible (turn-on is dominated by $LS+LD$ ) |      |      |       |                                                                                                                                                      |

**Notes:**


- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Limited by  $T_{Jmax}$ , starting  $T_J = 25^\circ\text{C}$ ,  $L = 1.2mH$ ,  $R_G = 50\Omega$ ,  $I_{AS} = 42A$ ,  $V_{GS} = 10V$ . Part not recommended for use above this value.
- ③  $ISD \leq 42A$ ,  $di/dt \leq 1706A/\mu s$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  $T_J \leq 175^\circ\text{C}$ .
- ④ Pulse width  $\leq 400\mu s$ ; duty cycle  $\leq 2\%$ .

- ⑤  $C_{oss\text{ eff. (TR)}}$  is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to  $80\% V_{DSS}$ .
- ⑥  $C_{oss\text{ eff. (ER)}}$  is a fixed capacitance that gives the same energy as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to  $80\% V_{DSS}$ .
- ⑦  $R_\theta$  is measured at  $T_J$  approximately  $90^\circ\text{C}$ .
- ⑧  $R_{\theta JC}$  value shown is at time zero.



**Fig 1. Typical Output Characteristics**

**Fig 2. Typical Output Characteristics**

**Fig 3. Typical Transfer Characteristics**

**Fig 4. Normalized On-Resistance vs. Temperature**

**Fig 5. Typical Capacitance vs. Drain-to-Source Voltage**

**Fig 6. Typical Gate Charge vs. Gate-to-Source Voltage**




**Fig 7.** Typical Source-to-Drain Diode Forward Voltage




**Fig 8.** Maximum Safe Operating Area




**Fig 9.** Maximum Drain Current vs. Case Temperature




**Fig 10.** Drain-to-Source Breakdown Voltage




**Fig 11.** Typical Coss Stored Energy




**Fig 12.** Maximum Avalanche Energy vs. Drain Current



**Fig 13.** Maximum Effective Transient Thermal Impedance, Junction-to-Case



**Fig 14.** Typical Avalanche Current vs. Pulsewidth



**Fig 15.** Maximum Avalanche Energy vs. Temperature






**Notes on Repetitive Avalanche Curves , Figures 14, 15:**  
(For further info, see AN-1005 at [www.irf.com](http://www.irf.com))



1. Avalanche failures assumption:  
Purely a thermal phenomenon and failure occurs at a temperature far in excess of  $T_{jmax}$ . This is validated for every part type.
2. Safe operation in Avalanche is allowed as long as  $T_{jmax}$  is not exceeded.
3. Equation below based on circuit and waveforms shown in Figures 16a, 16b.
4.  $P_{D(ave)}$  = Average power dissipation per single avalanche pulse.
5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6.  $I_{av}$  = Allowable avalanche current.
7.  $\Delta T$  = Allowable rise in junction temperature, not to exceed  $T_{jmax}$  (assumed as 25°C in Figure 14, 15).  
 $t_{av}$  = Average time in avalanche.  
 $D$  = Duty cycle in avalanche =  $tav \cdot f$   
 $Z_{thJC}(D, t_{av})$  = Transient thermal resistance, see Figures 13)

$$P_{D(ave)} = 1/2 (1.3 \cdot BV \cdot I_{av}) = \Delta T / Z_{thJC}$$



$$I_{av} = 2\Delta T / [1.3 \cdot BV \cdot Z_{thJC}]$$

$$E_{AS(AR)} = P_{D(ave)} \cdot t_{av}$$


**Fig. 16** Threshold Voltage vs. Temperature

**Fig. 17** Typical Recovery Current vs.  $di_F/dt$ 

**Fig 18.** Typical Recovery Current vs.  $di_F/dt$ 

**Fig 19.** Typical Stored Charge vs.  $di_F/dt$ 

**Fig 20.** Typical Stored Charge vs.  $di_F/dt$





**Fig 21.** Peak Diode Recovery  $dv/dt$  Test Circuit for N-Channel HEXFET® Power MOSFETs





**Fig 22a.** Unclamped Inductive Test Circuit

**Fig 22b.** Unclamped Inductive Waveforms



**Fig 23a.** Switching Time Test Circuit

**Fig 23b.** Switching Time Waveforms




**Fig 24a.** Gate Charge Test Circuit

**Fig 24b.** Gate Charge Waveform

## TO-247AC Package Outline

Dimensions are shown in millimeters (inches)



| SYMBOL | D I M E N S I O N S |      |              |       | NOTES |
|--------|---------------------|------|--------------|-------|-------|
|        | INCHES              |      | MILLIMETERS  |       |       |
|        | MIN.                | MAX. | MIN.         | MAX.  |       |
| A      | .190                | .204 | 4.83         | 5.20  |       |
| A1     | .090                | .100 | 2.29         | 2.54  |       |
| A2     | .075                | .085 | 1.91         | 2.16  |       |
| b      | .042                | .052 | 1.07         | 1.33  |       |
| b2     | .075                | .094 | 1.91         | 2.41  |       |
| b4     | .113                | .133 | 2.87         | 3.38  |       |
| c      | .022                | .026 | 0.55         | 0.68  |       |
| D      | .819                | .830 | 20.80        | 21.10 | 4     |
| D1     | .640                | .694 | 16.25        | 17.65 | 5     |
| E      | .620                | .635 | 15.75        | 16.13 | 4     |
| E1     | .512                | .570 | 13.00        | 14.50 |       |
| E2     | .145                | .196 | 3.68         | 5.00  |       |
| e      | .215 Typical        |      | 5.45 Typical |       |       |
| L      | .780                | .800 | 19.80        | 20.32 |       |
| L1     | .161                | .173 | 4.10         | 4.40  |       |
| ø P    | .138                | .143 | 3.51         | 3.65  |       |
| Q      | .216                | .236 | 5.49         | 6.00  |       |
| S      | .238                | .248 | 6.04         | 6.30  |       |

### LEAD ASSIGNMENTS

#### HEXFET

- 1.- GATE
- 2.- DRAIN
- 3.- SOURCE
- 4.- DRAIN

#### IGBTs, CoPACK

- 1.- GATE
- 2.- COLLECTOR
- 3.- EMITTER
- 4.- COLLECTOR

#### DIODES

- 1.- ANODE/OPEN
- 2.- CATHODE
- 3.- ANODE

### NOTES:


- 1 DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M 1994.
- 2 DIMENSIONS ARE SHOWN IN INCHES AND MILLIMETERS.
- 3 CONTOUR OF SLOT OPTIONAL.
- 4 DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5 THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS D1 & E1.
- 6 LEAD FINISH UNCONTROLLED IN L1.
- 7 ø P TO HAVE A MAXIMUM DRAFT ANGLE OF 1.5 ° TO THE TOP OF THE PART WITH A MAXIMUM HOLE DIAMETER OF .154 INCH.

## TO-247AC Part Marking Information

Notes: This part marking information applies to devices produced after 02/26/2001

EXAMPLE: THIS IS AN IRFPE30  
WITH ASSEMBLY  
LOT CODE 5657  
ASSEMBLED ON WW 35, 2001  
IN THE ASSEMBLY LINE "H"

Note: "P" in assembly line position  
indicates "Lead-Free"



TO-247 package is not recommended for Surface Mount Application.

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>

# Qualification information<sup>†</sup>

|                            |                                                                            |     |
|----------------------------|----------------------------------------------------------------------------|-----|
| Qualification level        | Industrial <sup>††</sup><br>(per JEDEC JESD47F <sup>†††</sup> guidelines ) |     |
| Moisture Sensitivity Level | TO-247AC                                                                   | N/A |
| RoHS compliant             | Yes                                                                        |     |

† Qualification standards can be found at International Rectifier's web site

<http://www.irf.com/product-info/reliability>

†† Higher qualification ratings may be available should the user have such requirements.

Please contact your International Rectifier sales representative for further information:

<http://www.irf.com/whoto-call/salesrep/>

††† Applicable version of JEDEC standard at the time of product release.

Data and specifications subject to change without notice.

International  
 Rectifier

**IR WORLD HEADQUARTERS:** 101N Sepulveda., El Segundo, California 90245, USA Tel: (310) 252-7105

TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.