



DST2080S



Pin out



Description

Littelfuse DST series Ultra Low V_F Schottky Barrier Rectifier is designed to meet the general requirements of commercial and industry applications by providing high temperature, low leakage and lower V_F products.

It is suitable for high frequency switching mode power supply, free-wheeling diodes and polarity protection diodes.

Features

- Ultra low forward voltage drop
- High frequency operation
- High junction temperature capability
- Guard ring for enhanced ruggedness and long term reliability
- Single die in TO-277B Package

Applications

- Switching mode power supply
- DC/DC converters
- Free-Wheeling diodes
- Polarity Protection Diodes

Maximum Ratings

| Parameters | Symbol | Test Conditions | Max | Unit |
|---|-------------|---|-----|------|
| Peak Inverse Voltage | V_{RWM} | - | 80 | V |
| Average Forward Current (per device) * | $I_{F(AV)}$ | 50% duty cycle @ $T_A=85^\circ\text{C}$ rectangular wave form | 20 | A |
| Peak One Cycle Non-Repetitive Surge Current (per leg) | I_{FSM} | 8.3 ms, half Sine pulse | 150 | A |

* Mounted on 30 mm x 30 mm pad areas aluminum PCB

Electrical Characteristics

| Parameters | Symbol | Test Conditions | Typ | Max | Unit |
|----------------------------------|----------|--|------|------|---------------|
| Forward Voltage Drop (per leg) * | V_{F1} | @10A, Pulse, $T_J = 25^\circ\text{C}$ | 0.52 | - | V |
| | | @20A, Pulse, $T_J = 25^\circ\text{C}$ | 0.64 | 0.70 | |
| | V_{F2} | @10A, Pulse, $T_J = 125^\circ\text{C}$ | 0.46 | - | |
| | | @20A, Pulse, $T_J = 125^\circ\text{C}$ | 0.60 | 0.65 | |
| Reverse Current (per leg) * | I_{R1} | @ $V_R = \text{rated } V_R, T_J = 25^\circ\text{C}$ | 22 | 300 | μA |
| | I_{R2} | @ $V_R = \text{rated } V_R, T_J = 125^\circ\text{C}$ | 11 | 75 | mA |

* Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

| Parameters | Symbol | Test Conditions | Max | Unit |
|---|-------------|-----------------|-------------|------|
| Junction Temperature | T_J | | -55 to +150 | °C |
| Storage Temperature | T_{stg} | | -55 to +150 | °C |
| Typical Thermal Resistance Junction to Ambient | $R_{th,JA}$ | DC operation | 70 | °C/W |
| Approximate Weight | wt | | 0.08 | g |
| Case Style | | TO-277B | | |

Figure 1: Typical Forward Characteristics




Figure 2: Typical Reverse Characteristics






Figure 3: Typical Junction Capacitance



Dimensions-TO-277B



| Symbol | Millimeters | | |
|----------|-------------|------|------|
| | Min | Typ | Max |
| A | 6.30 | 6.50 | 6.70 |
| B | 3.88 | 3.98 | 4.08 |
| C | 0.95 | 1.10 | 1.25 |
| D | 0.20 | 0.25 | 0.30 |
| E | 5.28 | 5.38 | 5.48 |
| F | 3.40 | 3.55 | 3.70 |
| G | 2.90 | 3.05 | 3.20 |
| H | 1.74 | 1.84 | 1.94 |
| I | 1.10 | 1.25 | 1.40 |
| J | - | 0.85 | - |
| K | 1.70 | 1.80 | 1.90 |
| L | 0.85 | 0.90 | 0.95 |
| M | - | 0.56 | - |

Part Numbering and Marking System


Packing Options

| Part Number | Marking | Packing Mode | M.O.Q |
|-------------|----------|----------------|-------|
| DST2080S | DST2080S | 5000pcs / Reel | 5000 |



DST = Device Type
 20 = Forward Current (20A)
 80 = Reverse Voltage (80V)
 S = Package Type
 LF = Littelfuse
 YY = Year
 WW = Week
 L = Lot Number

Carrier Tape & Reel Specification



| Symbol | Millimeters | |
|-----------|-------------|-------|
| | Min | Max |
| A | 4.28 | 4.48 |
| B | 6.80 | 7.00 |
| d | 1.40 | 1.60 |
| d1 | - | 1.50 |
| E | 1.65 | 1.85 |
| F | 7.40 | 7.60 |
| P | 7.90 | 8.10 |
| P0 | 3.90 | 4.10 |
| W | 15.70 | 16.30 |