

## Safety label with special adhesive - EMLS (76X51)R SR - 0800350

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Safety label with special adhesive, Roll, silver, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 76 x 51 mm

The figure shows a version of the article

### Product Features

- ✓ Labeling service: Phoenix Contact can custom-label all EMLS ... markers according to your requirements
- ✓ The safety function is ensured up to 80°C
- ✓ The EMLS ... materials are UL-listed
- ✓ Tamper-proof label, can be used as a rating plate or seal, for example
- ✓ When peeled off, part of the metallic layer comes away, leaving behind a triangular pattern on both the label and the surface

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 1             |
| GTIN             | 4046356580397 |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 76 mm |
| Width (a)  | 51 mm |

#### Ambient conditions

|                                 |                                                                                       |
|---------------------------------|---------------------------------------------------------------------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1)                                                           |
| Ambient temperature (operation) | -40 °C ... 150 °C                                                                     |
| Ambient temperature (assembly)  | > 5 °C                                                                                |
| Recommended storage conditions  | 10-25 °C / 35-65 % relative humidity. Storage in a cool and dry place is recommended. |

#### General

|                                     |                                |
|-------------------------------------|--------------------------------|
| Color                               | silver                         |
| Components                          | free from silicone and halogen |
| Material                            | Polyester                      |
| Number of individual labels         | 250                            |
| Number of individual labels per row | 1                              |
| RoHS compliant                      | Yes                            |
| Adhesive                            | Acrylic                        |
| File number                         | UL-MH48542 / PC-014            |

## Safety label with special adhesive - EMLS (76X51)R SR - 0800350

### Technical data

#### General

|                                                                            |                                     |
|----------------------------------------------------------------------------|-------------------------------------|
| <b>Printability</b>                                                        | Thermal transfer                    |
| <b>Test for substances that would hinder coating with paint or varnish</b> | VW PV 3.10.7:2005-02                |
| <b>Result</b>                                                              | Test passed                         |
| <b>Test specification weathering-resistance</b>                            | Following ISO 4892-2:2013-03        |
| <b>Test duration</b>                                                       | 96 h                                |
| <b>Wipe resistance test result</b>                                         | Test passed                         |
| <b>Salt spray test specification</b>                                       | DIN EN 60068-2-11:2000-02           |
| <b>Test duration</b>                                                       | 96 h                                |
| <b>Salt spray testing result</b>                                           | Test passed                         |
| <b>Alternating condensation climate with SO2 test specification</b>        | Following DIN 50018:2013-05         |
| <b>Climate level</b>                                                       | AHT 1.0 S                           |
| <b>Cycles</b>                                                              | 2                                   |
| <b>Condensation test result</b>                                            | Test passed                         |
| <b>Wipe resistance of test specification inscriptions</b>                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| <b>Result</b>                                                              | Test passed                         |
| <b>Foil strength</b>                                                       | 53 µm                               |
| <b>Adhesive strength</b>                                                   | 20 µm                               |

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 24190219 |
| <b>eCl@ss 4.1</b> | 24190219 |
| <b>eCl@ss 5.0</b> | 27149103 |
| <b>eCl@ss 5.1</b> | 27141137 |
| <b>eCl@ss 6.0</b> | 27141137 |
| <b>eCl@ss 7.0</b> | 27141137 |
| <b>eCl@ss 8.0</b> | 27141137 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

## Safety label with special adhesive - EMLS (76X51)R SR - 0800350

### approvals

---

UL Recognized /

---

#### Approval details

UL Recognized 

### accessories

#### Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>