




ELECTRICAL CHARACTERISTICS @ 25°C


1.0	URNS RATIO:	(P2-P3-P1) : (J6-J3)	: 1CT : 1CT ± 3%
		(P6-P4-P5) : (J2-J1)	: 1CT : 1CT ± 3%
2.0	INDUCTANCE:	(P6-P5)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC Bias
		(J6-J3)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC Bias
3.0	LEAKAGE INDUCTANCE:	P6-P5 (WITH J2 AND J1 SHORT)	: 0.3uH MAX. @ 1MHz
		P2-P1 (WITH J6 AND J3 SHORT)	: 0.3uH MAX. @ 1MHz
4.0	INTERWINDING CAPACITANCE:	(P2,P3,P1) TO (J6,J3)	: 25pF MAX @ 1MHz
		(P6,P4,P5) TO (J2,J1)	: 25pF MAX. @ 1MHz
5.0	DC RESISTANCE:	(P2-P1)	: 1.2 ohms Max.
		(J2-J1)	: 1.2 ohms Max.
6.0	RETURN LOSS:	(P6-P4)=100 OHMS AND (P1-P3)=100 OHM REF.	
		1MHz TO 30MHz	: -18dB MIN.
		60MHz TO 80MHz	: -12dB MIN.
NOTE: 100 OHMS CONNECTED TO (J2-J1) OR (J6-J3).			
7.0	DIELECTRIC WITHSTAND:	(J1, J2) TO (P6, P5)	: 1500 Vrms
		(J3, J6) TO (P2, P1)	: 1500 Vrms
8.0	INSERTION LOSS:	RS=RL=100 ohms	
		100KHz TO 100MHz	: -1.1 dB TYP
9.0	RISE TIME:	RS=100 OHMS AND RL = 100 OHMS	
		OUTPUT VOLTAGE = 1 V peak	: 3.0 nS MAX
		PULSE WIDTH= 112nS	: 3.0 nS MAX
10.0	CROSS TALK:	1MHz TO 100MHz	: -35 dB TYP
11.0	COMMON TO COMMON MODE ATTENUATION:	1MHz TO 100MHz	: -45 dB TYP



ORIGINATED BY	DATE	TITLE MagJack® 10/100BT TAB DOWN, SHIELDED PATENTED	PART NO. / DRAWING NO.		STANDARD DIM.		[] METRIC DIM. AS REFERENCE		bel COMPONENTS FOR A CONNECTED PLANET	
Bain Liu	08-31-09		SI-60076-F		TOL. IN INCH		UNIT : INCH [mm]			REV. : A0
DRAWN BY	DATE		FILE NAME		.X		SCALE : N/A			SIZE : A4
Bain Liu	08-31-09		SI-60076-F.DWG		.XX					PAGE : 2
				.XXX	±0.005					


THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS
2002/95/EC



LED SPECIFICATION			
STANDARD LED	WAVELENGTH	Forward V (MAX)	* (TYP)
GREEN	565 nm	2.5 V	2.2 V

*WITH A FORWARD CURRENT OF 20 mA (TYP)





P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE


ALL CENTERLINE DIMENSIONS ARE BASIC.

NOTES:

- CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACT/SHIELD: COPPER ALLOY
SHIELD PLATING: NICKEL OR TIN
CONTACT PLATING: SELECTIVE GOLD,
50 MICRO-INCHES MIN. IN CONTACT AREA.
- PIN NOT ELECTRICALLY CONNECTED MAYBE OMITTED.
SEE ELECTRICAL DRAWING FOR OMITTED PINS.
- TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS.
- ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE $\pm .005 [0.13]$
- WAVE SOLDER COMPATIBLE - PREHEAT 125°C/90SECS.




ORIGINATED BY Bain Liu	DATE 08-31-09	TITLE MagJack® 10/100BT TAB DOWN, SHIELDED PATENTED	PART NO. / DRAWING NO. SI-60076-F	STANDARD DIM. TOL. IN INCH .X .XX .XXX ±0.005	[] METRIC DIM. AS REFERENCE		bel COMPONENTS FOR A CONNECTED PLANET
					UNIT : INCH [mm]	REV. : A0	
DRAWN BY Bain Liu	DATE 08-31-09		FILE NAME SI-60076-F.DWG		SCALE : N/A	SIZE : A4	
						PAGE : 3	



SUGGESTED PANEL OPENING

.000 (TOP OF PCB TO BOTTOM OF OPENING)

.010 [0.25] MAX. RADIUS(4)



1. THE SUGGESTED PANEL OPENING IS INTENDED TO GIVE THE USER THE ABILITY TO HAVE REASONABLE JACK / PANEL CLEARANCES YET MAINTAIN RELIABLE GROUNDING CAPABILITY.
2. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ± 0.005 [0.13]

ORIGINATED BY	DATE	TITLE MagJack® 10/100BT TAB DOWN, SHIELDED PATENTED	PART NO. / DRAWING NO.		STANDARD DIM.		[] METRIC DIM. AS REFERENCE		bel COMPONENTS FOR A CONNECTED PLANET	
Bain Liu	08-31-09		SI-60076-F		TOL. IN INCH		UNIT : INCH [mm]			REV. : A0
DRAWN BY	DATE		FILE NAME		.X		SCALE : N/A			SIZE : A4
Bain Liu	08-31-09		SI-60076-F.DWG		.XX					PAGE : 4
				.XXX	±0.005					