


4

3

2

1

LOC 00	DIST 00	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005150	21MAR11	RK	HMR



6. FOR TERMINATION, USE FOLLOWING EQUIPMENT:
SHOWN FOR REFERENCE ONLY (USER SUPPLIED)
CRIMP TOOL: M22520/1-01
TURRET HEAD/LOCATOR: M22520/1-02

5 FINISH: GOLD PLATED, .000030 MIN THICK
OVER NICKEL PLATED, .000050 MIN THICK

4 FINISH: GOLD PLATED, .000010 MIN THICK
OVER NICKEL PLATED, .000050 MIN THICK


3. MATERIAL: COPPER ALLOY.

2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED
ON THE CONTAINER WITH THE FOLLOWING INFORMATION:
PART NUMBER & DATE CODE OF MANUFACTURE.

1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING ITEM
INTERCHANGEABILITY REQUIRE PRIOR TE CONNECTIVITY APPROVAL AND
AUTHORIZATION BY REVISION TO THIS DRAWING.

NOTES: UNLESS OTHERWISE SPECIFIED

1650155-2	5
1650155-1	4
PART NUMBER	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. PATTERSON 11JULY07	 TE Connectivity			
		CHK D. ORRIS 11JULY07				
DIMENSIONS: INCHES		APVD D. ORRIS	NAME		CONTACT, PIN, SIZE #20 CRIMP, STANDARD, .33 PIN EXT	
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL SEE NOTE 1, SHEET 1		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1650155	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 8=1	SHEET 1 OF 1	REV B1