




DESCRIPTION: VERTICAL - HIGH PROFILE - STAMPED

DIMENSIONS (mm)

NUMBER OF CONTACTS	A	B	C	D
15	30.80	24.99	16.34	19.20
26	39.20	33.32	24.70	27.70

SPECIFICATIONS:

ELECTRICAL:	
INSULATOR RESISTANCE:	1000 MΩ MIN.
WORKING VOLTAGE:	250V
OPERATING TEMPERATURE:	-50°C TO +100°C
CONTACT RESISTANCE:	15 mΩ MAX.
CONTACT AMPERAGE:	3 AMPS
MATERIALS:	
CONTACTS:	BRASS
	GOLD FLASH IN MATING AREA
	TIN PLATING ON TAIL ENDS
SHELL	STEEL, NICKEL PLATED
INSULATOR	PBT, UL94-V0
	(PROCESS TEMP 230°C)



198-YYY-213L YY1

SERIES	198
POSITIONS	YYY
015	
026	
GENDER	2 = FEMALE
TERMINATION	1 = VERTICAL SOLDER
SHELL PLATING	3 = NICKEL
HARDWARE OPTIONS	00 = NO HARDWARE
03 = .197" 4-40 HEX STANDOFF	
55 = .161" 4-40 CLINCH NUT (BOARD SIDE)	
PLATING OPTIONS	1 = GOLD FLASH

RoHS COMPLIANT

DRAWN: P. JENKINS
DATE: 09/15/2005

UNITS = mm



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

SCALE: NTS	SHEET 1 OF 3	REV 3
DWG NO.	198-YYY-213L YY1	



HOLE PATTERN SHOWN
ARE FOR FEMALE

* TYP.
SUGGESTED SIZE
MAY NOT BE SUITABLE FOR ALL APPLICATIONS

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
09/15/2005

UNITS = inches


DO NOT SCALE FROM DRAWING




SCALE: NTS	SHEET 2 OF 3	REV 3
DWG NO. 198-YYY-213LYY1		

HARDWARE OPTIONS:

55 = #4-40 CLINCH NUT (BOARD SIDE)



03 = #4-40 HEX STANDOFF



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
09/15/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET 3 OF 3

REV 3

DWG NO. 198-YYY-213LYY1