


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECO-16-004800	08SEP2016	NK	MZ



- 1 STAINLESS STEEL.
- 2 BRASS.
- 3 1.27µm [0.000050] MIN TIN-LEAD OVER 1.27µm [0.000050] MIN NICKEL.
- 4 WIRE RANGE: 14-18 AWG. INSULATION RANGE: 2.79-3.81 [0.110-0.150] DIA.
- 5 0.76µm [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, OVER 1.27µm [0.000050] MIN NICKEL.
- 6 1.27µm [0.000050] MIN TIN OVER 1.27µm [0.000050] MIN NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	LOOSE PIECE	6	213603-6
	STRIP	6	213603-5
7	OBSOLETE LOOSE PIECE	5	213603-4
	STRIP	5	213603-3
OBSOLETE	LOOSE PIECE	3	213603-2
	STRIP	3	213603-1
DESCRIPTION		PIN FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SPRING:
PIN:

SEE TABLE

DWN L.SIPE 05/07/90
CHK R STONE 5-17-90
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV F3

TE Connectivity

PIN ASSEMBLY, 5015 SERIES,
14-18 AWG, SPECIAL TYPE III+

SIZE A3
CAGE CODE 00779
DRAWING NO C-213603

RESTRICTED TO -