

Date: 10/23/2008

VARISTOR SPECIFICATION SHEET

MAIDA STYLE NUMBER D6321ZOV131RA70

MAIDA ITEM NUMBER 01-0048

Electrical Specifications


Continuous AC Voltage	130 VAC
Continuous DC Voltage	175 VDC
Maximum DC Leakage @ 175 VDC	200 uA
Low Varistor Voltage Limit	184 VDC
High Varistor Voltage Limit	224 VDC
Nominal Varistor Voltage	204 VDC
Current for Varistor Voltage	1 mA
Maximum Clamp Voltage	340 V
Maximum Clamp Voltage Test Current	100 A
Peak Current Rating (1 Pulse)	9000 A
Peak Current Rating (2 Pulse)	7000 A
Energy Rating (8X20us)	130 J
Energy Rating (10X1000us)	130 J
Typical Capacitance	2140 pF
Impulse Response Time	< 50 ns
Minimum Hipot of Coating	2500 VDC
Minimum I.R. of Coating	1000 MΩ

Thermal Specifications

Minimum Operating Temperature	-40 °C
Maximum Operating Temperature	85 °C
Varistor Voltage Temperature Coeff	-0.05 %/°C
Minimum Storage Temperature	-50 °C
Maximum Storage Temperature	125 °C
Current/Energy Derating Above 85°C	-2.5 %/°C

Notes**Physical Specifications**

Lead Style	110B1
X Nominal	0.3 in.
X Tolerance	0.04 in.
Lead Length Nominal	1.00 in.
Lead Length Tolerance	min. in.
Y Nominal	0.068 in.
Y Tolerance	0.03 in.
d Nominal	0.032 in.
Wire Gauge	20 AWG
Minimum Marking	Z131-70UL
Nominal Disk Size	18 mm
D Maximum	0.787 in.
T Maximum	0.204 in.
H Maximum	0.912 in.



* Contact Maida for a more detailed configuration drawing.

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	
SEV File Number	

**DEVELOPMENT COMPANY**

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194