


# Crimphousing 2,54 mm

Series

430



|                       |                                        |
|-----------------------|----------------------------------------|
| Rated current         | 3,0 A                                  |
| Rated voltage         | 250 V <sub>RMS</sub> / V <sub>DC</sub> |
| Withstand voltage     | 600 V <sub>RMS</sub> for 1 minute      |
| Material contact      | Copper alloy                           |
| Material insulator    | Thermoplast UL94V-0                    |
| Operating temperature | -25°C to +105°C                        |

pitch  
2,54

mating pin  
size  
□ 0,64

max.  
pincount  
024

All dimensions in mm.



## Variation

## Contact





Series

607

AWG 22 - 26





1



2

Plating:  
T = Sn

Packaging:  
L = Bulk  
R = Reel




3

607-1-TX-X?

## Crimp Tool

454



454-1-04

\* No. of contacts:

Variation 1 = 002 - 012

Variation 2 = 004 - 024

Variation 3 = 004 - 024

Variation (1,2,3)

No. of contacts \*  
(002,... - 024)



www.mpe-connector.de

Order code:

430-?-?-?-X-KS0

Mating series  
see page

087 090 088 334 368 093  
3-37 3-39 3-41 3-42 3-43 3-47