





PRODUCT NUMBER
SEE SHEET 2

NOTES :

1. MINI PUSH-OUT FORCE TERMINAL IN BOTH DIRECTIONS 22N.
2. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 1 = 19.32$ mm



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
P	F07-0220	JCO	07.06.14	angles	.X ±0.3	mm	SHR. HEADER
R	F08-0147	YOV	08.04.14	linear	.XX ±0.15	mm	STR DR TMT
S	B-19286	AMA	14.11.03		.XXX ±0.05	scale 5:1	dwg no
L	F06-0106	LMU	06.01.12	dr	G CORBOZ	01.01.12	sheet 1 of 2
M	F06-0228	LMU	06.07.11	enrg	P NIZZI	01.01.12	size
N	F07-0147	LMU	07.03.01	chr	D LEGRAND	01.01.12	A3
sheet	revision	S	G	appd	P N	01.01.12	type
index	sheet	1	2				CUSTOMER Drawing

RoHS COMPLIANT PRODUCT NUMBER
76385-YXXLF

PLATING CODE

RoHS COMPLIANT, SEE NOTE 5

- 3= 0.76µm GOLD/GXT ON CONTACT AREA.
2µm MIN MATTE TIN ON TAILS.
4= 2µm MIN MATTE TIN FULL PLATED

NUMBER OF POSITIONS PER ROW: 02 TO 18

1.27µm Ni MIN UNDERPLATING

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O COLOR: BLACK.
- 2 - TERMINAL MATERIAL: COPPER ALLOY.
- 3 - 2 UP TO 6 POSITIONS PER ROW, PRODUCT PACKED IN PLASTIC BAG.
7 UP TO 18 POSITIONS PER ROW, PRODUCT PACKED IN TUBE.
- 4 - ONLY DASH NUMBER -X02 AND -X03
ALWAYS TEN (10) PRODUCTS MOLDED ASSEMBLY
& DELIVERED TON STRIP ACCORDING PHANTOM LINES.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family DUBOX			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title SHR. HEADER STR DR TMT			
B	F06-0106	LMU	06.01.12	angles	linear .X ±0.3					
C	F06-0228	LMU	06.07.11		linear .XX ±0.15	scale 5:1	dwg no 76385			
D	F07-0147	LMU	07.03.01	dr	linear .XXX ±0.05					
E	F07-0220	JCO	07.06.14	enr	J.COMPAGNON	FCJ	sheet 2 of A3			
F	F08-0147	YOV	08.04.14	chr						
G	B-19286	AMA	14.11.03	appd	JM.C	FCJ	type CUSTOMER Drawing			
sheet	revision									
index	sheet									