



# Dimensions in mm


## MSG63



## MSG63-PA



## MSG63-PR



Test Specification according to standard  
 UL 248-1,14

### Electrical Characteristic

Rated Current	1.0In		2.0In	
	Min.	Max.	Min.	Max.
62.5mA - 3A	4 h	3600 s	5 s	120 s
3.5A - 30A	4 h	3600 s	12 s	120 s

Rated Current	Breaking capacity	Rated Voltage	MSG63-PR/PA		
			UL <sup>us</sup> Listed	JET	
62.5mA	@125V/AC 10KA @250V/AC 35A	125V/250V	○	○	
100mA		125V/250V	○	○	
125mA		125V/250V	○	○	
187.5mA		125V/250V	○	○	
200mA		125V/250V	○	○	
250mA		125V/250V	○	○	
300mA		125V/250V	○	○	
375mA		125V/250V	○	○	
500mA		125V/250V	○	○	
750mA		125V/250V	○	○	
1A	@125V/AC 10KA @250V/AC 100A	125V/250V	○	○	
1.25A		125V/250V	○	○	
1.5A		125V/250V	○	○	
2A		125V/250V	○	○	
2.25A		125V/250V	○	○	
2.5A		125V/250V	○	○	
3A		125V/250V	○	○	
4A		@125V/AC 10KA @250V/AC 200A	125V/250V	○	○
5A			125V/250V	○	○
6A			125V/250V	○	○
7A	125V/250V		○	○	
8A	125V/250V		○	○	
9A	125V/250V		○	○	
10A	@32V/AC,DC 1000A	125V/250V	○	○	
* 12A		32V	○	○	
* 15A		32V	○	○	
* 17.5A		32V	○	○	
* 20A	32V	○	○		

\* PS:12A~20A 32V approvals

## GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. <b>25655</b>	GOLDSUN NO. <b>MSG63a0.250N</b>
Description SLOW BLOW FUSE 250V 250mA SIZE 0.25"x1.25"	
UNIT: mm	SCALE: SHEET 1 OF 1
CAS No: ERN No:	Rev. 1